

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC®

λ/4 First Surface Mirrors



- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Edges:	Fine Ground
--------	----------------------	--------	-------------

Optical Properties

Surface Flatness (P-V):	λ/4	Substrate:	BOROFLOAT®
Surface Quality:	60-40	Coating Type:	Metal

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	λ/4	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#48-404	S\$89.60 Volume Pricing	20+ In Stock
5.00	λ/4	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#48-407	S\$89.60 Volume Pricing	Contact Us
5.00	λ/4	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#48-410	S\$116.90 Volume Pricing	20+ In Stock
5.00	λ/4	-	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-186	S\$107.80 Volume Pricing	1 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#48-405	S\$89.60 Volume Pricing	20+ In Stock
-	λ/4	5.0 x 5.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#48-408	S\$89.60 Volume Pricing	8 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#48-411	S\$116.90 Volume Pricing	8 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-187	S\$107.80 Volume Pricing	8 In Stock
10.00	λ/4	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-598	S\$89.60 Volume Pricing	Contact Us
10.00	λ/4	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-599	S\$89.60 Volume Pricing	Contact Us

10.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-600	S\$116.90 Volume Pricing	Contact Us
10.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-188	S\$107.80 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-722	S\$89.60 Volume Pricing	13 In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-723	S\$89.60 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-724	S\$116.90 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-189	S\$107.80 Volume Pricing	Contact Us
12.50	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-601	S\$89.60 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-602	S\$89.60 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-603	S\$116.90 Volume Pricing	5 In Stock
12.50	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-190	S\$100.10 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-406	S\$89.60 Volume Pricing	Contact Us

-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-409	S\$89.60 Volume Pricing	14 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-412	S\$116.90 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-191	S\$107.80 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#25-746	S\$93.80 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#25-747	S\$93.80 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#25-748	S\$125.30 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#25-749	S\$116.90 Volume Pricing	7 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#25-730	S\$89.60 Volume Pricing	Contact Us
12.70	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#25-731	S\$89.60 Volume Pricing	6 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#25-732	S\$116.90 Volume Pricing	1 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#25-733	S\$107.80 Volume Pricing	Contact Us

15.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#63-162	S\$93.80 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#63-168	S\$93.80 Volume Pricing	Contact Us
15.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#63-174	S\$125.30 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#88-535	S\$116.90 Volume Pricing	Contact Us
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-725	S\$93.80 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-726	S\$93.80 Volume Pricing	Contact Us
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-727	S\$125.30 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-192	S\$116.90 Volume Pricing	Contact Us
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-875	S\$81.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#43-506	S\$93.80 Volume Pricing	7 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-716	S\$93.80 Volume Pricing	12 In Stock

-	$\lambda/4$	16.0 x 23.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-432	S\$125.30 Volume Pricing	16 In Stock
-	$\lambda/4$	16.0 x 23.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-721	S\$116.90 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-163	S\$98.70 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-169	S\$98.70 Volume Pricing	Contact Us
20.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-175	S\$129.50 Volume Pricing	2 In Stock
20.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-536	S\$121.10 Volume Pricing	5 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-728	S\$98.70 Volume Pricing	5 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-729	S\$98.70 Volume Pricing	7 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#45-730	S\$129.50 Volume Pricing	20+ In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-193	S\$121.10 Volume Pricing	Contact Us
-	$\lambda/4$	21.0 x 30.0	R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#32-454	S\$85.40 Volume Pricing	Contact Us

-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#43-507	S\$98.70 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-717	S\$98.70 Volume Pricing	1 In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-742	S\$129.50 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-722	S\$121.10 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#33-510	S\$85.40 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#32-516	S\$98.70 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-718	S\$98.70 Volume Pricing	Contact Us
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-433	S\$129.50 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-723	S\$121.10 Volume Pricing	15 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#45-604	S\$112.00 Volume Pricing	20+ In Stock
25.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#45-605	S\$112.00 Volume Pricing	Contact Us

25.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#45-606	S\$161.00 Volume Pricing	5 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#49-194	S\$135.10 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-286	S\$93.80 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.00	#45-333	S\$112.00 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.00	#45-334	S\$112.00 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.00	#45-335	S\$161.00 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.00	#49-195	S\$125.30 Volume Pricing	3 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#32-513	S\$112.00 Volume Pricing	Contact Us
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-719	S\$112.00 Volume Pricing	3 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-434	S\$161.00 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-724	S\$135.10 Volume Pricing	20+ In Stock

25.40	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#25-734	S\$112.00 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#25-735	S\$112.00 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#25-736	S\$161.00 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#25-737	S\$135.10 Volume Pricing	7 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-164	S\$139.30 Volume Pricing	Contact Us
30.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-170	S\$139.30 Volume Pricing	9 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-176	S\$187.60 Volume Pricing	20+ In Stock
30.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-537	S\$156.80 Volume Pricing	4 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-165	S\$139.30 Volume Pricing	5 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-171	S\$129.50 Volume Pricing	20+ In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#63-177	S\$187.60 Volume Pricing	5 In Stock

-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	5.00	#88-538	S\$156.80 Volume Pricing	20+ In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	5.00	#25-750	S\$173.60 Volume Pricing	2 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	5.00	#25-751	S\$173.60 Volume Pricing	5 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700-10000nm)	5.00	#25-752	S\$250.60 Volume Pricing	1 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	5.00	#25-753	S\$205.80 Volume Pricing	7 In Stock
40.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	4.00	#63-166	S\$165.20 Volume Pricing	20+ In Stock
40.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	4.00	#63-172	S\$165.20 Volume Pricing	Contact Us
40.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700-10000nm)	4.00	#63-178	S\$228.20 Volume Pricing	5 In Stock
40.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	4.00	#88-539	S\$184.80 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	5.00	#63-167	S\$165.20 Volume Pricing	15 In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	5.00	#63-173	S\$165.20 Volume Pricing	20+ In Stock

-	$\lambda/4$	40.0 x 40.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#63-179	S\$228.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#88-540	S\$184.80 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	4.00	#45-607	S\$187.60 Volume Pricing	14 In Stock
50.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#45-608	S\$187.60 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#45-609	S\$273.00 Volume Pricing	Contact Us
50.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#49-196	S\$228.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	50.0 x 50.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	10.00	#45-336	S\$187.60 Volume Pricing	1 In Stock
-	$\lambda/4$	50.0 x 50.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	10.00	#45-337	S\$187.60 Volume Pricing	9 In Stock
-	$\lambda/4$	50.0 x 50.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	10.00	#45-338	S\$273.00 Volume Pricing	Contact Us
-	$\lambda/4$	50.0 x 50.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	10.00	#49-197	S\$228.20 Volume Pricing	10 In Stock
50.80	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	4.00	#25-738	S\$187.60 Volume Pricing	Contact Us

50.80	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#25-739	S\$187.60 Volume Pricing	4 In Stock
50.80	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#25-740	S\$273.00 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#25-741	S\$228.20 Volume Pricing	8 In Stock
51.00	$\lambda/4$	-	R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Protected Aluminum (400- 2000nm)	13.00	#33-511	S\$107.80 Volume Pricing	Contact Us
51.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	13.00	#32-514	S\$187.60 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	13.00	#46-720	S\$175.00 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	13.00	#32-435	S\$273.00 Volume Pricing	20+ In Stock
51.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	13.00	#46-725	S\$228.20 Volume Pricing	3 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	12.00	#45-339	S\$364.00 Volume Pricing	13 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	12.00	#45-340	S\$364.00 Volume Pricing	6 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	12.00	#45-341	S\$488.60 Volume Pricing	4 In Stock

-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	12.00	#88-541	S\$421.40 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	15.00	#45-342	S\$582.40 Volume Pricing	14 In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	15.00	#45-343	S\$582.40 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	15.00	#45-344	S\$805.00 Volume Pricing	5 In Stock
			$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	15.00	#88-542	S\$617.40 Volume Pricing	9 In Stock

Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com