

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Cube Beamsplitters](#)

TECHSPEC® Lateral Displacement Beamsplitters



- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

Common Specifications

Physical & Mechanical Properties


Clear Aperture (%):	80.00	Construction:	Prism
Dimensional Tolerance (mm):	±0.1	Parallelism (arcmin):	<2

Optical Properties


Angle Tolerance (arcsec):	±5	Substrate:	N-BK7
Surface Flatness (P-V):	$\lambda/8$	Surface Quality:	40-20

Technical Information


VIS Non-Polarizing Beamsplitters



632.8nm Polarizing Beamsplitters



NIR Non-Polarizing Beamsplitters



Products

Extinction Ratio	Wavelength Range (nm)	DWL (nm)	Type of Optics	Stock Number	Price	Buy
$ T_p - T_s < 6\%$	430 - 670	-	Non-Polarizing	#47-188	S\$938.00 Volume Pricing	20+ In Stock
$ T_p - T_s < 6\%$	720 - 1080	-	Non-Polarizing	#47-540	S\$938.00 Volume Pricing	9 In Stock
$ T_p - T_s < 6\%$	430 - 670	-	Non-Polarizing	#47-189	S\$1,120.00 Volume Pricing	20+ In Stock
$ T_p - T_s < 6\%$	720 - 1080	-	Non-Polarizing	#47-541	S\$1,120.00 Volume Pricing	14 In Stock
>1000:1	-	632.8	Polarizing	#47-190	S\$938.00 Volume Pricing	3 In Stock
>1000:1	-	632.8	Polarizing	#47-191	S\$1,120.00 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com