

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

High Performance Standard Series Iris Diaphragms



- Corrosion and High Temperature Resistance Housing
- Anti-Reflective (AR) Spring Steel or Burnished Spring Steel Leaf Options Available
- Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting

Technical Information

Products

Type	Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Stock Number	Price	Buy
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-573	S\$158.31 Volume Pricing	20+ In Stock
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-574	S\$158.31 Volume Pricing	20+ In Stock
Unmounted	0.8, Typical	8	14.8	8	#64-507	S\$107.53 Volume Pricing	20+ In Stock
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-575	S\$107.53 Volume Pricing	20+ In Stock
Unmounted	1.0, Typical	18.0	28.0	12.00	#57-576	S\$107.53 Volume Pricing	20+ In Stock
Unmounted	1.2, Typical	20.0	30.0	12.00	#57-577	S\$132.17 Volume Pricing	20+ In Stock
Unmounted	1.5, Typical	25.00	37.0	15.00	#84-131	S\$132.17 Volume Pricing	20+ In Stock
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-578	S\$158.31 Volume Pricing	20+ In Stock
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-579	S\$158.31 Volume Pricing	20+ In Stock
Unmounted	1.0, Typical	8.0	14.8	9	#57-580	S\$107.53 Volume Pricing	3 In Stock
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-581	S\$107.53 Volume Pricing	6 In Stock
Unmounted	1.2, Typical	20.0	30.0	12.00	#64-508	S\$132.17 Volume Pricing	14 In Stock
Unmounted	1.5, Typical	25.0	37.0	15.00	#57-582	S\$132.17 Volume Pricing	13 In Stock
Unmounted	2.5, Typical	37.0	53.0	16.00	#57-583	S\$132.17 Volume Pricing	Contact Us
Unmounted	2.5, Typical	50.0	70.0	18.00	#57-584	S\$273.31 Volume Pricing	5 In Stock
Unmounted	4.0, Typical	60.0	82.0	17.00	#57-585	S\$312.14 Volume Pricing	20+ In Stock

Unmounted	4.0, Typical	75.0	100.0	20.00	#57-586	S\$468.96 Volume Pricing	5 In Stock
Mounted	0.5, Typical	5.0	26.5	8.00	#23-255	S\$182.21 Volume Pricing	7 In Stock
Mounted	0.5, Typical	7.0	26.5	8.00	#23-256	S\$182.21 Volume Pricing	3 In Stock
Mounted	0.8, Typical	8.0	26.5	8.00	#23-257	S\$132.17 Volume Pricing	2 In Stock
Mounted	1.0, Typical	12.0	39.0	11.00	#23-258	S\$132.17 Volume Pricing	Contact Us
Mounted	1.0, Typical	18.0	52.0	12.00	#23-259	S\$132.17 Volume Pricing	1 In Stock
Mounted	1.2, Typical	20.0	52.0	12.00	#23-260	S\$155.32 Volume Pricing	1 In Stock
Mounted	1.5, Typical	25.0	52.0	15.00	#23-261	S\$155.32 Volume Pricing	1 In Stock
Mounted	0.5, Typical	7.0	26.5	8.00	#23-262	S\$182.21 Volume Pricing	1 In Stock
Mounted	1.0, Typical	8.0	26.5	9.00	#23-263	S\$132.17 Volume Pricing	1 In Stock
Mounted	1.0, Typical	12.0	39.0	11.00	#23-264	S\$132.17 Volume Pricing	1 In Stock
Mounted	1.2, Typical	20.0	52.0	12.00	#23-265	S\$155.32 Volume Pricing	1 In Stock
Mounted	1.5, Typical	25.0	52.0	15.00	#23-266	S\$155.32 Volume Pricing	2 In Stock
Mounted	2.5, Typical	50.0	90.0	18.00	#23-267	S\$291.23 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com