

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC® $\lambda/10$ First Surface Mirrors



- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground

Optical Properties

Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	20-10
--------------------------------	--------------	-------------------------	-------

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Thickness (mm)	Coating	Coating Specification	Stock Number	Price	Buy
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450- 650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-007	S\$129.50 Volume Pricing	1 In Stock
5.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250- 700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-307	S\$129.50 Volume Pricing	3 In Stock
5.00	$\lambda/10$	-	2.00	Protected Gold (700- 10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-021	S\$161.00 Volume Pricing	Contact Us
5.00	$\lambda/10$	-	2.00	Protected Silver (450- 10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-321	S\$155.40 Volume Pricing	15 In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (600- 1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-976	S\$152.60 Volume Pricing	14 In Stock
5.00	$\lambda/10$	-	2.00	Ultrafast- Enhanced Silver (800- 1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-006	S\$152.60 Volume Pricing	7 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (450- 650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-008	S\$129.50 Volume Pricing	20+ In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Enhanced Aluminum (250- 700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-308	S\$129.50 Volume Pricing	3 In Stock

-	$\lambda/10$	5.0 x 5.0	2.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-022	S\$161.00 Volume Pricing	Contact Us
-	$\lambda/10$	5.0 x 5.0	2.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-322	S\$155.40 Volume Pricing	Contact Us
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-977	S\$152.60 Volume Pricing	7 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-007	S\$152.60 Volume Pricing	2 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-189	S\$129.50 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-188	S\$129.50 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-186	S\$161.00 Volume Pricing	Contact Us
6.35	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-187	S\$155.40 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-009	S\$129.50 Volume Pricing	20+ In Stock

10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-309	S\$129.50 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-023	S\$161.00 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-323	S\$155.40 Volume Pricing	15 In Stock
10.00	$\lambda/10$	-	2.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-233	S\$156.80 Volume Pricing	17 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-979	S\$152.60 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-009	S\$152.60 Volume Pricing	3 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-010	S\$129.50 Volume Pricing	15 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-310	S\$129.50 Volume Pricing	14 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-024	S\$161.00 Volume Pricing	15 In Stock

-	$\lambda/10$	10.0 x 10.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-324	S\$155.40 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-409	S\$129.50 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-419	S\$129.50 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-429	S\$161.00 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-439	S\$155.40 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-234	S\$161.00 Volume Pricing	5 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-980	S\$152.60 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-010	S\$152.60 Volume Pricing	1 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-410	S\$129.50 Volume Pricing	2 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-420	S\$129.50 Volume Pricing	Contact Us

-	$\lambda/10$	12.5 x 12.5	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-430	S\$161.00 Volume Pricing	13 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-440	S\$155.40 Volume Pricing	5 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-196	S\$126.00 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-195	S\$129.50 Volume Pricing	Contact Us
12.70	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-193	S\$161.00 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-194	S\$155.40 Volume Pricing	11 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-011	S\$139.30 Volume Pricing	7 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-311	S\$139.30 Volume Pricing	4 In Stock
15.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-025	S\$170.80 Volume Pricing	2 In Stock
15.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-325	S\$168.00 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-235	S\$187.60 Volume Pricing	1 In Stock

15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-982	S\$163.80 Volume Pricing	5 In Stock
15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-012	S\$163.80 Volume Pricing	7 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-012	S\$139.30 Volume Pricing	12 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-312	S\$151.20 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-026	S\$170.80 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-326	S\$168.00 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-997	S\$163.80 Volume Pricing	6 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-203	S\$151.20 Volume Pricing	5 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-202	S\$151.20 Volume Pricing	3 In Stock

19.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-200	S\$187.60 Volume Pricing	1 In Stock
19.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-201	S\$175.00 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-013	S\$151.20 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-313	S\$151.20 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-027	S\$187.60 Volume Pricing	15 In Stock
20.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-327	S\$175.00 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-236	S\$182.00 Volume Pricing	7 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-984	S\$175.00 Volume Pricing	10 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-014	S\$175.00 Volume Pricing	2 In Stock

-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-014	S\$151.20 Volume Pricing	13 In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-314	S\$151.20 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-028	S\$187.60 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-328	S\$175.00 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-998	S\$175.00 Volume Pricing	1 In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-015	S\$159.60 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-315	S\$159.60 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-029	S\$219.80 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-329	S\$204.40 Volume Pricing	17 In Stock
25.00	$\lambda/10$	-	4.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-237	S\$210.00 Volume Pricing	Contact Us

25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-985	S\$201.60 Volume Pricing	12 In Stock
25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-015	S\$201.60 Volume Pricing	14 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-016	S\$159.60 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-316	S\$159.60 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-030	S\$219.80 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-330	S\$204.40 Volume Pricing	16 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#25-549	S\$268.80 Volume Pricing	6 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-999	S\$201.60 Volume Pricing	4 In Stock
25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-210	S\$159.60 Volume Pricing	7 In Stock

25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-209	S\$155.40 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-207	S\$219.80 Volume Pricing	14 In Stock
25.40	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-208	S\$204.40 Volume Pricing	17 In Stock
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-411	S\$204.40 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-421	S\$204.40 Volume Pricing	5 In Stock
30.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-431	S\$277.20 Volume Pricing	14 In Stock
30.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-441	S\$219.80 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-238	S\$229.60 Volume Pricing	2 In Stock
30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-987	S\$225.40 Volume Pricing	3 In Stock

30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-017	S\$225.40 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-412	S\$204.40 Volume Pricing	20+ In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-422	S\$204.40 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-432	S\$277.20 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-442	S\$219.80 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-000	S\$225.40 Volume Pricing	1 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-413	S\$228.20 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-423	S\$228.20 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-433	S\$294.00 Volume Pricing	8 In Stock

35.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-443	S\$268.80 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-239	S\$285.60 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-988	S\$264.60 Volume Pricing	7 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#25-546	S\$228.20 Volume Pricing	4 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#25-547	S\$228.20 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#25-548	S\$294.00 Volume Pricing	14 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-031	S\$264.60 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-018	S\$264.60 Volume Pricing	4 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-414	S\$228.20 Volume Pricing	14 In Stock

-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-424	S\$228.20 Volume Pricing	8 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-434	S\$294.00 Volume Pricing	1 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-444	S\$268.80 Volume Pricing	20+ In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-001	S\$264.60 Volume Pricing	4 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-217	S\$245.00 Volume Pricing	3 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-216	S\$245.00 Volume Pricing	20+ In Stock
38.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-214	S\$324.80 Volume Pricing	Contact Us
38.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-215	S\$302.40 Volume Pricing	2 In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-017	S\$245.00 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-317	S\$245.00 Volume Pricing	5 In Stock

40.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-031	S\$324.80 Volume Pricing	1 In Stock
40.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-331	S\$302.40 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-240	S\$326.20 Volume Pricing	12 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-990	S\$295.40 Volume Pricing	5 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-020	S\$295.40 Volume Pricing	3 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-018	S\$245.00 Volume Pricing	20+ In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-318	S\$245.00 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-032	S\$324.80 Volume Pricing	11 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-332	S\$302.40 Volume Pricing	12 In Stock

50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-019	S\$268.80 Volume Pricing	13 In Stock
50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-319	S\$268.80 Volume Pricing	Contact Us
50.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-033	S\$359.80 Volume Pricing	10 In Stock
50.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-333	S\$334.60 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-241	S\$373.80 Volume Pricing	14 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-991	S\$327.60 Volume Pricing	8 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-021	S\$327.60 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-020	S\$268.80 Volume Pricing	13 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-320	S\$268.80 Volume Pricing	20+ In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-034	S\$359.80 Volume Pricing	6 In Stock

-	$\lambda/10$	50.0 x 50.0	5.00	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#68-334	S\$334.60 Volume Pricing	16 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#39-224	S\$268.80 Volume Pricing	5 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#39-223	S\$268.80 Volume Pricing	7 In Stock
50.80	$\lambda/10$	-	9.53	Protected Gold (700-10000nm)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	#39-221	S\$359.80 Volume Pricing	3 In Stock
50.80	$\lambda/10$	-	9.53	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#39-222	S\$334.60 Volume Pricing	Contact Us
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#84-415	S\$554.40 Volume Pricing	4 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#84-425	S\$554.40 Volume Pricing	15 In Stock
75.00	$\lambda/10$	-	7.50	Protected Gold (700-10000nm)	R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm	#84-435	S\$721.00 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Protected Silver (450-10000nm)	R_{avg} >98% @ 450 - 800nm R_{avg} >98.5% @ 2000 - 10,000nm	#84-445	S\$669.20 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (450-650nm)	R_{avg} >95% @ 450 - 650nm	#84-416	S\$554.40 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (250-700nm)	R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm	#84-426	S\$554.40 Volume Pricing	7 In Stock

-	$\lambda/10$	75.0 x 75.0	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-436	S\$721.00 Volume Pricing	2 In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-446	S\$669.20 Volume Pricing	10 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-417	S\$812.00 Volume Pricing	5 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-427	S\$812.00 Volume Pricing	13 In Stock
100.00	$\lambda/10$	-	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-437	S\$1,176.00 Volume Pricing	20+ In Stock
100.00	$\lambda/10$	-	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-447	S\$1,064.00 Volume Pricing	9 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-418	S\$812.00 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-428	S\$812.00 Volume Pricing	5 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-438	S\$1,176.00 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-448	S\$1,064.00 Volume Pricing	20+ In Stock
5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#26-094	S\$126.00 Volume Pricing	Contact Us

5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-098	S\$129.50 Volume Pricing	2 In Stock
5.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-099	S\$161.00 Volume Pricing	3 In Stock
5.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-100	S\$155.40 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-101	S\$129.50 Volume Pricing	1 In Stock
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-102	S\$129.50 Volume Pricing	6 In Stock
10.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-103	S\$161.00 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-104	S\$155.40 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-105	S\$129.50 Volume Pricing	1 In Stock
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-364	S\$129.50 Volume Pricing	4 In Stock
12.50	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-365	S\$161.00 Volume Pricing	16 In Stock
12.50	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-366	S\$155.40 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-367	S\$139.30 Volume Pricing	5 In Stock

15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-368	S\$139.30 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-369	S\$170.80 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-370	S\$162.40 Volume Pricing	Contact Us
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-371	S\$151.20 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-372	S\$151.20 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-373	S\$187.60 Volume Pricing	3 In Stock
20.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-374	S\$175.00 Volume Pricing	Contact Us
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-375	S\$159.60 Volume Pricing	Contact Us
25.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-376	S\$159.60 Volume Pricing	5 In Stock
25.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-377	S\$219.80 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-378	S\$204.40 Volume Pricing	2 In Stock
30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-379	S\$204.40 Volume Pricing	1 In Stock

30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#26-380	S\$204.40 Volume Pricing	4 In Stock
30.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#26-381	S\$277.20 Volume Pricing	3 In Stock
30.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#26-382	S\$219.80 Volume Pricing	3 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-924	S\$1,386.00 Volume Pricing	Contact Us
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-925	S\$1,386.00 Volume Pricing	2 In Stock
125.00	$\lambda/10$	-	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-926	S\$1,589.00 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-927	S\$1,512.00 Volume Pricing	2 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-928	S\$1,386.00 Volume Pricing	4 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-929	S\$1,386.00 Volume Pricing	1 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-930	S\$1,589.00 Volume Pricing	4 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-931	S\$1,512.00 Volume Pricing	8 In Stock

150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-932	S\$2,121.00 Volume Pricing	2 In Stock
150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-933	S\$2,121.00 Volume Pricing	5 In Stock
150.00	$\lambda/10$	-	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-934	S\$2,450.00 Volume Pricing	2 In Stock
150.00	$\lambda/10$	-	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-935	S\$2,282.00 Volume Pricing	Contact Us
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#70-936	S\$2,121.00 Volume Pricing	3 In Stock
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#70-937	S\$2,121.00 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#70-938	S\$2,450.00 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 2000nm $R_{avg} >98\%$ @ 2000 - 10,000nm	#70-939	S\$2,282.00 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com