

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC® Yb:YAG Laser Line Mirrors



- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- Guaranteed High Laser Damage Thresholds
- 10-5 Surface Quality for Reduced Scatter in Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

Common Specifications

Physical & Mechanical Properties

Parallelism (arcmin):	<3	Back Surface:	Commercial Polish
------------------------------	----	----------------------	-------------------

Optical Properties

Surface Quality:	10-5	Reflection at DWL (%):	99.8
Surface Flatness (P-V):	$\lambda/10$	Coating Type:	Dielectric
Substrate:	Fused Silica (Corning 7980)		

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Dimensions (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
339 - 346	343	6.35	-	4.00	45	#38-842	S\$182.21 Volume Pricing	4 In Stock
339 - 346	343	12.70	-	6.35	45	#38-843	S\$201.62 Volume Pricing	1 In Stock
339 - 346	343	19.10	-	6.35	45	#38-844	S\$219.54 Volume Pricing	10 In Stock
339 - 346	343	25.40	-	6.35	45	#38-845	S\$237.47 Volume Pricing	9 In Stock
339 - 346	343	38.10	-	6.35	45	#38-847	S\$280.78 Volume Pricing	1 In Stock
339 - 346	343	50.80	-	9.53	45	#38-849	S\$428.63 Volume Pricing	8 In Stock
339 - 346	343	-	6.35 x 6.35	3.18	45	#39-593	S\$192.66 Volume Pricing	7 In Stock
339 - 346	343	-	9.53 x 6.35	3.18	45	#39-594	S\$201.62 Volume Pricing	12 In Stock
339 - 346	343	-	12.7 x 12.7	6.35	45	#39-596	S\$209.09 Volume Pricing	13 In Stock
339 - 346	343	-	19.1 x 12.7	6.35	45	#39-597	S\$219.54 Volume Pricing	3 In Stock
339 - 346	343	-	25.4 x 25.4	6.35	45	#39-598	S\$244.93 Volume Pricing	5 In Stock
339 - 346	343	-	38.1 x 25.4	6.35	45	#39-599	S\$252.40 Volume Pricing	2 In Stock
339 - 346	343	6.35	-	4.00	0-45	#38-850	S\$201.62 Volume Pricing	9 In Stock
339 - 346	343	12.70	-	6.35	0-45	#38-851	S\$219.54 Volume Pricing	20+ In Stock
339 - 346	343	19.10	-	6.35	0-45	#38-852	S\$237.47 Volume Pricing	20+ In Stock
339 - 346	343	25.40	-	6.35	0-45	#38-853	S\$252.40 Volume Pricing	16 In Stock
339 - 346	343	38.10	-	6.35	0-45	#38-855	S\$295.71 Volume Pricing	8 In Stock
339 - 346	343	50.80	-	9.53	0-45	#38-857	S\$445.06 Volume Pricing	7 In Stock

339 - 346	343	76.20	-	12.70	0-45	#27-034	S\$1,100.71 Volume Pricing	Contact Us
339 - 346	343	-	6.35 x 6.35	3.18	0-45	#39-601	S\$209.09 Volume Pricing	12 In Stock
339 - 346	343	-	9.53 x 6.35	3.18	0-45	#39-603	S\$219.54 Volume Pricing	9 In Stock
339 - 346	343	-	12.7 x 12.7	6.35	0-45	#39-604	S\$228.51 Volume Pricing	14 In Stock
339 - 346	343	-	19.1 x 12.7	6.35	0-45	#39-605	S\$237.47 Volume Pricing	9 In Stock
339 - 346	343	-	25.4 x 25.4	6.35	0-45	#39-607	S\$261.36 Volume Pricing	5 In Stock
339 - 346	343	-	38.1 x 25.4	6.35	0-45	#39-610	S\$271.82 Volume Pricing	Contact Us
509 - 520	515	6.35	-	4.00	45	#38-871	S\$182.21 Volume Pricing	8 In Stock
509 - 520	515	12.70	-	6.35	45	#38-872	S\$201.62 Volume Pricing	20+ In Stock
509 - 520	515	19.10	-	6.35	45	#38-873	S\$219.54 Volume Pricing	20+ In Stock
509 - 520	515	25.40	-	6.35	45	#38-874	S\$237.47 Volume Pricing	10 In Stock
509 - 520	515	38.10	-	6.35	45	#38-876	S\$280.78 Volume Pricing	5 In Stock
509 - 520	515	50.80	-	9.53	45	#38-878	S\$428.63 Volume Pricing	4 In Stock
509 - 520	515	-	6.35 x 6.35	3.18	45	#39-626	S\$192.66 Volume Pricing	6 In Stock
509 - 520	515	-	9.53 x 6.35	3.18	45	#39-627	S\$201.62 Volume Pricing	3 In Stock
509 - 520	515	-	12.7 x 12.7	6.35	45	#39-628	S\$209.09 Volume Pricing	17 In Stock
509 - 520	515	-	19.1 x 12.7	6.35	45	#39-629	S\$219.54 Volume Pricing	13 In Stock
509 - 520	515	-	25.4 x 25.4	6.35	45	#39-630	S\$244.93 Volume Pricing	3 In Stock
509 - 520	515	-	38.1 x 25.4	6.35	45	#39-631	S\$252.40 Volume Pricing	5 In Stock
509 - 520	515	6.35	-	4.00	0-45	#38-879	S\$201.62 Volume Pricing	20+ In Stock

509 - 520	515	12.70	-	6.35	0-45	#38-880	S\$219.54 Volume Pricing	7 In Stock
509 - 520	515	19.10	-	6.35	0-45	#38-881	S\$237.47 Volume Pricing	2 In Stock
509 - 520	515	25.40	-	6.35	0-45	#38-882	S\$252.40 Volume Pricing	4 In Stock
509 - 520	515	38.10	-	6.35	0-45	#38-884	S\$295.71 Volume Pricing	Contact Us
509 - 520	515	50.80	-	9.53	0-45	#38-886	S\$445.06 Volume Pricing	2 In Stock
509 - 520	515	76.20	-	12.70	0-45	#27-035	S\$1,100.71 Volume Pricing	2 In Stock
509 - 520	515	-	6.35 x 6.35	3.18	0-45	#39-632	S\$209.09 Volume Pricing	9 In Stock
509 - 520	515	-	9.53 x 6.35	3.18	0-45	#39-633	S\$219.54 Volume Pricing	20+ In Stock
509 - 520	515	-	12.7 x 12.7	6.35	0-45	#39-634	S\$228.51 Volume Pricing	20+ In Stock
509 - 520	515	-	19.1 x 12.7	6.35	0-45	#39-635	S\$237.47 Volume Pricing	6 In Stock
509 - 520	515	-	25.4 x 25.4	6.35	0-45	#39-636	S\$261.36 Volume Pricing	10 In Stock
509 - 520	515	-	38.1 x 25.4	6.35	0-45	#39-638	S\$271.82 Volume Pricing	7 In Stock
1020 - 1040	1030	6.35	-	4.00	45	#11-291	S\$182.21 Volume Pricing	11 In Stock
1020 - 1040	1030	12.70	-	6.35	45	#11-292	S\$197.14 Volume Pricing	10 In Stock
1020 - 1040	1030	19.10	-	6.35	45	#11-293	S\$219.54 Volume Pricing	14 In Stock
1020 - 1040	1030	25.40	-	6.35	45	#11-294	S\$237.47 Volume Pricing	14 In Stock
1020 - 1040	1030	38.10	-	6.35	45	#11-295	S\$280.78 Volume Pricing	9 In Stock
1020 - 1040	1030	50.80	-	9.53	45	#11-296	S\$428.63 Volume Pricing	7 In Stock
1020 - 1040	1030	-	6.35 x 6.35	3.18	45	#11-297	S\$192.66 Volume Pricing	15 In Stock
1020 - 1040	1030	-	9.53 x 6.35	3.18	45	#11-298	S\$201.62 Volume Pricing	14 In Stock

1020 - 1040	1030	-	12.7 x 12.7	6.35	45	#11-299	S\$209.09 Volume Pricing	5 In Stock
1020 - 1040	1030	-	19.1 x 12.7	6.35	45	#11-300	S\$219.54 Volume Pricing	20+ In Stock
1020 - 1040	1030	-	25.4 x 25.4	6.35	45	#11-301	S\$244.93 Volume Pricing	20+ In Stock
1020 - 1040	1030	-	38.1 x 25.4	6.35	45	#11-302	S\$252.40 Volume Pricing	5 In Stock
1020 - 1040	1030	4.00	-	3.00	0-45	#12-628	S\$173.25 Volume Pricing	11 In Stock
1020 - 1040	1030	6.35	-	4.00	0-45	#11-303	S\$201.62 Volume Pricing	15 In Stock
1020 - 1040	1030	12.70	-	6.35	0-45	#11-304	S\$219.54 Volume Pricing	12 In Stock
1020 - 1040	1030	19.10	-	6.35	0-45	#11-305	S\$237.47 Volume Pricing	20+ In Stock
1020 - 1040	1030	25.40	-	6.35	0-45	#11-306	S\$252.40 Volume Pricing	20+ In Stock
1020 - 1040	1030	38.10	-	6.35	0-45	#11-307	S\$295.71 Volume Pricing	3 In Stock
1020 - 1040	1030	50.80	-	9.53	0-45	#11-308	S\$445.06 Volume Pricing	7 In Stock
1020 - 1040	1030	76.20	-	12.70	0-45	#27-036	S\$1,100.71 Volume Pricing	7 In Stock
1020 - 1040	1030	-	6.35 x 6.35	3.18	0-45	#11-309	S\$209.09 Volume Pricing	20+ In Stock
1020 - 1040	1030	-	9.53 x 6.35	3.18	0-45	#11-310	S\$219.54 Volume Pricing	2 In Stock
1020 - 1040	1030	-	12.7 x 12.7	6.35	0-45	#11-311	S\$228.51 Volume Pricing	14 In Stock
1020 - 1040	1030	-	19.1 x 12.7	6.35	0-45	#11-312	S\$237.47 Volume Pricing	10 In Stock
1020 - 1040	1030	-	25.4 x 25.4	6.35	0-45	#11-313	S\$261.36 Volume Pricing	20+ In Stock
1020 - 1040	1030	-	38.1 x 25.4	6.35	0-45	#11-314	S\$271.82 Volume Pricing	8 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com