

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

ZEISS A-Plan Plan Achromat Infinity Corrected Objectives See

More by [ZEISS](#)




- Ideal for Brightfield and Fluorescence Applications
- Excellent Color Correction and Flatness of Field
- Oil Immersion Options Available

Common Specifications

General			
Compatible Tube Lens Focal Length (mm):		Focal Length: 164.50mm	Typical Applications: Fluorescence, BrightField
Manufacturer:		Zeiss	
Physical & Mechanical Properties			
Maximum Diameter (mm):		30	
Optical Properties			
Compatible Cover Glass Thickness (mm):		0.17	Wavelength Range (nm): 480 - 650
Field Number (mm):		23	Parfocal Length (mm): 45.06
Threading & Mounting			
Mounting Threads:		M27 x 0.75	
Environmental & Durability Factors			
Operating Temperature (°C):		+10 to +40	
Operating Humidity:		75% at 35°C	

Technical Information



Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
2.5X	0.06	23	65.80	421020-9900-000	10.4	#13-814	S\$576.38	2 In Stock
5X	0.12	23	33.00	421030-9900-000	10.1	#13-815	S\$421.14	5 In Stock
10X	0.25	23	16.50	421040-9900-000	4.5	#13-816	S\$308.94	13 In Stock
20X	0.45	23	8.20	421050-9900-000	0.46	#13-817	S\$461.10	13 In Stock
40X	0.65	23	4.10	421060-9900-000	0.45	#13-818	S\$667.06	1 In Stock
63X	0.8	23	2.60	421080-9900-000	0.3	#13-819	S\$945.26	1 In Stock
100X	0.8	23	1.60	421090-9800-000	0.97	#13-820	S\$883.78	Contact Us
100X	1.25	23	1.60	421090-9902-000	0.22	#13-821	S\$1,152.75	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com