

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus X-Line Extended Apochromat Infinity Corrected Objectives

See More by [Olympus](#)



- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Common Specifications

General

Compatible Tube Lens Focal Length (mm):	Focal Length: 180mm	Manufacturer:	Olympus
---	---------------------	---------------	---------

Optical Properties

Wavelength Range (nm):	400 - 1000	Field Number (mm):	26.5
------------------------	------------	--------------------	------

Threading & Mounting

Mounting Threads:	RMS / 20.32mm x 36 TPI
-------------------	------------------------

Technical Information

Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
4X	0.16	26.5	45.00	UPLXAPO4X	13.0	#14-905	S\$3,556.00	5 In Stock
10X	0.40	26.5	18.00	UPLXAPO10X	3.1	#14-906	S\$4,879.00	Contact Us
20X	0.80	26.5	9.00	UPLXAPO20X	0.61	#14-907	S\$6,342.00	3 In Stock
40X	0.95	26.5	4.50	UPLXAPO40X	0.18	#14-908	S\$8,232.00	1 In Stock
40X	1.40	26.5	4.50	UPLXAPO40XO	0.13	#73-283	S\$12,362.00	1 In Stock
#74-022 New								
New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
60X	1.20	26.5	3.00	UPLXAPO60XW	0.28		S\$12,852.00	Contact Us
60X	1.42	26.5	3.00	UPLXAPO60XO	0.15	#14-909	S\$13,174.00	4 In Stock
100X	1.45	26.5	1.80	UPLXAPO100XO	0.135	#14-910	S\$13,384.00	1 In Stock

