

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

TECHSPEC® Unmounted OD 4.0 Bandpass Filters



- Center Wavelengths from 365 to 1550nm
- 10, 25, or 50nm Full-Width Half Maximum Options
- High Transmission and Deep Blocking
- Mounted OD 4.0 [5nm](#), [10nm](#), [25nm](#) and [50nm](#) Bandpass Filters Also Available

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	3.30 ±0.20	Construction:	Unmounted
Physical Durability:	Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2	Bevel:	Protective as needed

Optical Properties

Angle of Incidence (°):	0	Optical Density OD (Average):	≥4.0
Substrate:	Optical Glass	Coating:	Hard Coated
Surface Quality:	80-50		

Environmental & Durability Factors

Environmental Durability:	Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
----------------------------------	---

Technical Information

Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Minimum Transmission (%)	Blocking Wavelength Range (nm)	Stock Number	Price	Buy
12.50	365.00	10.00	≥85	200 - 1200	#15-116	S\$278.60 Volume Pricing	20+ In Stock
25.00	365.00	10.00	≥85	200 - 1200	#15-131	S\$413.00 Volume Pricing	3 In Stock
12.50	405.00	10.00	≥85	200 - 1200	#15-117	S\$259.00 Volume Pricing	Contact Us
25.00	405.00	10.00	≥85	200 - 1200	#15-132	S\$392.00 Volume Pricing	10 In Stock
12.50	430.00	10.00	≥85	200 - 1200	#15-118	S\$259.00 Volume Pricing	1 In Stock
25.00	430.00	10.00	≥85	200 - 1200	#15-133	S\$392.00 Volume Pricing	20+ In Stock
12.50	450.00	10.00	≥85	200 - 1200	#15-119	S\$259.00 Volume Pricing	3 In Stock
25.00	450.00	10.00	≥85	200 - 1200	#15-134	S\$392.00 Volume Pricing	Contact Us
12.50	450.00	25.00	≥90	200 - 1200	#15-146	S\$259.00 Volume Pricing	20+ In Stock
25.00	450.00	25.00	≥90	200 - 1200	#15-151	S\$392.00 Volume Pricing	20+ In Stock
12.50	450.00	50.00	≥90	200 - 1200	#15-156	S\$259.00 Volume Pricing	20+ In Stock
25.00	450.00	50.00	≥90	200 - 1200	#15-164	S\$392.00 Volume Pricing	20+ In Stock
12.50	520.00	10.00	≥85	200 - 1200	#15-120	S\$259.00 Volume Pricing	20+ In Stock
25.00	520.00	10.00	≥85	200 - 1200	#15-135	S\$392.00 Volume Pricing	3 In Stock
12.50	525.00	25.00	≥90	200 - 1200	#15-147	S\$259.00 Volume Pricing	4 In Stock
25.00	525.00	25.00	≥90	200 - 1200	#15-152	S\$392.00 Volume Pricing	2 In Stock
12.50	525.00	50.00	≥90	200 - 1200	#15-157	S\$259.00 Volume Pricing	9 In Stock

25.00	525.00	50.00	≥90	200 - 1200	#15-165	S\$392.00 Volume Pricing	20+ In Stock
12.50	532.00	10.00	≥85	200 - 1200	#15-121	S\$259.00 Volume Pricing	20+ In Stock
25.00	532.00	10.00	≥85	200 - 1200	#15-136	S\$392.00 Volume Pricing	20+ In Stock
12.50	550.00	10.00	≥85	200 - 1200	#15-122	S\$259.00 Volume Pricing	3 In Stock
25.00	550.00	10.00	≥85	200 - 1200	#15-137	S\$392.00 Volume Pricing	Contact Us
12.50	550.00	25.00	≥90	200 - 1200	#15-148	S\$259.00 Volume Pricing	20+ In Stock
25.00	550.00	25.00	≥90	200 - 1200	#15-153	S\$392.00 Volume Pricing	2 In Stock
12.50	550.00	50.00	≥90	200 - 1200	#15-158	S\$259.00 Volume Pricing	20+ In Stock
25.00	550.00	50.00	≥90	200 - 1200	#15-166	S\$392.00 Volume Pricing	20+ In Stock
12.50	589.00	10.00	≥85	200 - 1200	#15-123	S\$259.00 Volume Pricing	20+ In Stock
25.00	589.00	10.00	≥85	200 - 1200	#15-138	S\$392.00 Volume Pricing	4 In Stock
12.50	632.00	10.00	≥85	200 - 1200	#15-124	S\$259.00 Volume Pricing	5 In Stock
25.00	632.00	10.00	≥85	200 - 1200	#15-139	S\$392.00 Volume Pricing	9 In Stock
12.50	640.00	10.00	≥85	200 - 1200	#15-125	S\$259.00 Volume Pricing	20+ In Stock
25.00	640.00	10.00	≥85	200 - 1200	#15-140	S\$392.00 Volume Pricing	1 In Stock
12.50	650.00	25.00	≥90	200 - 1200	#15-149	S\$259.00 Volume Pricing	4 In Stock
25.00	650.00	25.00	≥90	200 - 1200	#15-154	S\$392.00 Volume Pricing	3 In Stock
12.50	650.00	50.00	≥90	200 - 1200	#15-159	S\$259.00 Volume Pricing	13 In Stock
25.00	650.00	50.00	≥90	200 - 1200	#15-167	S\$392.00 Volume Pricing	5 In Stock
12.50	660.00	10.00	≥85	200 - 1200	#15-126	S\$259.00 Volume Pricing	13 In Stock

25.00	660.00	10.00	≥85	200 - 1200	#15-141	S\$392.00 Volume Pricing	Contact Us
12.50	850.00	10.00	≥85	200 - 1200	#15-127	S\$278.60 Volume Pricing	1 In Stock
25.00	850.00	10.00	≥85	200 - 1200	#15-142	S\$413.00 Volume Pricing	1 In Stock
12.50	850.00	50.00	≥90	200 - 1200	#15-160	S\$278.60 Volume Pricing	2 In Stock
25.00	850.00	50.00	≥90	200 - 1200	#15-168	S\$413.00 Volume Pricing	14 In Stock
12.50	900.00	50.00	≥90	200 - 1200	#15-161	S\$278.60 Volume Pricing	14 In Stock
25.00	900.00	50.00	≥90	200 - 1200	#15-169	S\$413.00 Volume Pricing	20+ In Stock
12.50	905.00	10.00	≥85	200 - 1200	#15-128	S\$278.60 Volume Pricing	2 In Stock
25.00	905.00	10.00	≥85	200 - 1200	#15-143	S\$413.00 Volume Pricing	20+ In Stock
12.50	940.00	10.00	≥85	200 - 1200	#15-129	S\$278.60 Volume Pricing	1 In Stock
25.00	940.00	10.00	≥85	200 - 1200	#15-144	S\$413.00 Volume Pricing	3 In Stock
12.50	950.00	50.00	≥90	200 - 1200	#15-162	S\$278.60 Volume Pricing	2 In Stock
25.00	950.00	50.00	≥90	200 - 1200	#15-170	S\$413.00 Volume Pricing	1 In Stock
12.50	1,064.00	10.00	≥85	200 - 1200	#15-130	S\$278.60 Volume Pricing	8 In Stock
25.00	1,064.00	10.00	≥85	200 - 1200	#15-145	S\$413.00 Volume Pricing	20+ In Stock
12.50	1,550.00	25.00	≥90	200 - 1800	#15-150	S\$336.00 Volume Pricing	Contact Us
25.00	1,550.00	25.00	≥90	200 - 1800	#15-155	S\$504.00 Volume Pricing	2 In Stock
12.50	1,550.00	50.00	≥90	200 - 1800	#15-163	S\$336.00 Volume Pricing	Contact Us
25.00	1,550.00	50.00	≥90	200 - 1800	#15-171	S\$504.00 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com