

[All Products](#) / [Imaging Lenses](#) / [Cinema Production and Advanced Photography](#)

MikroMak™ PetzVex™ Prime Probe Lenses



- Arthouse Design for the Petzval Look
- Use from Macro to Infinity with Excellent Sharpness over Depth of Field
- Ideal for Cinema Production and Creative Photographic Applications
- [MikroMak™ Prime Probe Lenses](#) Also Available

Common Specifications

Physical & Mechanical Properties

Maximum Diameter (mm):	48.00
------------------------	-------

Optical Properties

Maximum Image Circle (mm):	43.30
----------------------------	-------

Sensor

Maximum Sensor Format:	35mm (43.3mm Image Circle)
------------------------	----------------------------

Threading & Mounting

Mount:	M42 x 0.75 (T-Mount)
--------	----------------------

Technical Information

Products

Title	Stock Number	Price	Buy
40mm PetzVex™ MikroMak™ CINE Prime Probe Lens	#17-660	S\$4,851.00	1 In Stock
50mm PetzVex™ MikroMak™ CINE Prime Probe Lens	#17-661	S\$4,851.00	1 In Stock
40mm PetzVex™ MikroMak™ Prime Probe Lens	#16-135	S\$4,515.00	1 In Stock
50mm PetzVex™ MikroMak™ Prime Probe Lens	#16-134	S\$4,515.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com