

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#)

Preloaded Norland Optical Adhesive Syringes See More by [Norland](#)



- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Technical Information

Products

Norland Number	Size (oz)	Bonding Type	Glass Bonding	Metal Bonding	Index of Refraction (n _d)	Stock Number	Price	Buy
60	0.1	Glass to Glass	Good	Good	1.56	#55-154	S\$39.15 Volume Pricing	3 In Stock
60	0.34	Glass to Glass	Good	Good	1.56	#55-084	S\$48.21 Volume Pricing	4 In Stock
61	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-155	S\$39.15 Volume Pricing	14 In Stock
61	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-085	S\$48.21 Volume Pricing	Contact Us
63	0.1	Glass to Glass	Good	Good	1.56	#55-156	S\$39.15 Volume Pricing	4 In Stock
63	0.34	Glass to Glass	Good	Good	1.56	#55-086	S\$48.21 Volume Pricing	3 In Stock
65	0.1	Glass to Glass/Metal	Good	Good	1.52	#55-157	S\$39.15 Volume Pricing	Contact Us
65	0.34	Glass to Glass/Metal	Good	Good	1.52	#55-087	S\$48.21 Volume Pricing	5 In Stock
68	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#55-158	S\$39.15 Volume Pricing	5 In Stock
68	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#55-088	S\$48.21 Volume Pricing	7 In Stock
68T	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-390	S\$39.15 Volume Pricing	2 In Stock
68T	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-391	S\$48.21 Volume Pricing	1 In Stock
68TH	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-789	S\$39.15 Volume Pricing	5 In Stock
68TH	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-790	S\$56.19 Volume Pricing	5 In Stock
72	0.1	Plastic to Plastic/Glass	Excellent	Good	1.56	#17-386	S\$39.15 Volume Pricing	2 In Stock
72	0.34	Plastic to Plastic/Glass	Excellent	Good	1.56	#17-365	S\$56.19 Volume Pricing	4 In Stock
73	0.1	Glass to Glass	Excellent	Good	1.56	#17-387	S\$39.15 Volume Pricing	1 In Stock

73	0.34	Glass to Glass	Excellent	Good	1.56	#17-366	S\$56.19 Volume Pricing	1 In Stock
74	0.1	Plastic to Plastic/Glass	Excellent	Good	1.52	#17-388	S\$39.15 Volume Pricing	Contact Us
74	0.34	Plastic to Plastic/Glass	Excellent	Good	1.52	#17-367	S\$56.19 Volume Pricing	1 In Stock
76	0.1	Glass to Plastic	Excellent	Good	1.51	#17-389	S\$39.15 Volume Pricing	Contact Us
76	0.34	Glass to Plastic	Excellent	Good	1.51	#17-368	S\$56.19 Volume Pricing	3 In Stock
78	0.1	Plastic to Plastic/Glass	Excellent	Good	1.50	#17-390	S\$39.15 Volume Pricing	2 In Stock
78	0.34	Plastic to Plastic/Glass	Excellent	Good	1.50	#17-369	S\$56.19 Volume Pricing	1 In Stock
81	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-159	S\$39.15 Volume Pricing	4 In Stock
81	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-089	S\$48.21 Volume Pricing	5 In Stock
86H	0.1	Glass to Glass/Plastic	Excellent	Good	1.55	#12-846	S\$39.15 Volume Pricing	Contact Us
86H	0.34	Glass to Glass/Plastic	Excellent	Good	1.55	#12-847	S\$48.21 Volume Pricing	Contact Us
86TH	0.1	Glass to Glass/Plastic	Excellent	Good	1.54	#17-391	S\$39.15 Volume Pricing	Contact Us
86TH	0.34	Glass to Glass/Plastic	Excellent	Good	1.54	#17-370	S\$56.19 Volume Pricing	Contact Us
86TLH	0.1	Glass to Glass/Metal	Excellent	Excellent	1.55	#14-795	S\$39.15 Volume Pricing	Contact Us
86TLH	0.34	Glass to Glass/Metal	Excellent	Excellent	1.55	#14-796	S\$56.19 Volume Pricing	Contact Us
87	0.1	Glass to Glass/Plastic	Excellent	Good	1.52	#17-392	S\$39.15 Volume Pricing	3 In Stock
87	0.34	Glass to Glass/Plastic	Excellent	Good	1.52	#17-371	S\$56.19 Volume Pricing	Contact Us
88	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#14-839	S\$39.15 Volume Pricing	5 In Stock
88	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#14-840	S\$56.19 Volume Pricing	4 In Stock
89H	0.1	Glass to Glass	Excellent	Good	1.51	#17-393	S\$39.15 Volume Pricing	2 In Stock

89H	0.34	Glass to Glass	Excellent	Good	1.51	#17-372	S\$56.19 Volume Pricing	3 In Stock
UVS 91	0.1	Liquid Crystal Displays	Excellent	Good	N/A	#17-406	S\$39.15 Volume Pricing	2 In Stock
UVS 91	0.34	Liquid Crystal Displays	Excellent	Good	N/A	#17-385	S\$56.19 Volume Pricing	2 In Stock
108H	0.1	Glass to Metal	Excellent	Excellent	1.51	#17-405	S\$39.15 Volume Pricing	2 In Stock
108H	0.34	Glass to Metal	Excellent	Excellent	1.51	#17-384	S\$56.19 Volume Pricing	2 In Stock
139	0.1	Glass to Glass	Excellent	Good	1.39	#15-694	S\$56.19 Volume Pricing	2 In Stock
139	0.34	Glass to Glass	Excellent	Good	1.39	#15-695	S\$162.40 Volume Pricing	2 In Stock
144	0.1	Glass to Glass	Excellent	Good	1.44	#17-400	S\$39.15 Volume Pricing	1 In Stock
144	0.34	Glass to Glass	Excellent	Good	1.44	#17-379	S\$81.92 Volume Pricing	1 In Stock
146H	0.1	Plastic to Plastic/Glass	Excellent	Good	1.46	#12-864	S\$39.15 Volume Pricing	1 In Stock
146H	0.34	Plastic to Plastic/Glass	Excellent	Good	1.46	#12-865	S\$48.21 Volume Pricing	1 In Stock
148	0.1	Glass to Glass	Excellent	Good	1.48	#17-401	S\$39.15 Volume Pricing	3 In Stock
148	0.34	Glass to Glass	Excellent	Good	1.48	#17-380	S\$56.19 Volume Pricing	1 In Stock
160	0.1	Glass to Glass	Excellent	Good	1.60	#12-858	S\$39.15 Volume Pricing	1 In Stock
160	0.34	Glass to Glass	Excellent	Good	1.60	#12-859	S\$48.21 Volume Pricing	2 In Stock
165H	0.1	Glass to Glass	Excellent	Excellent	1.65	#17-404	S\$39.15 Volume Pricing	2 In Stock
165H	0.34	Glass to Glass	Excellent	Excellent	1.65	#17-383	S\$56.19 Volume Pricing	2 In Stock
170	0.1	Glass to Glass	Excellent	Good	1.70	#12-849	S\$59.81 Volume Pricing	3 In Stock
170	0.34	Glass to Glass	Excellent	Good	1.70	#12-850	S\$145.00 Volume Pricing	4 In Stock
170F	0.1	Glass to Glass	Excellent	Good	1.70	#14-792	S\$65.25 Volume Pricing	2 In Stock

170F	0.34	Glass to Glass	Excellent	Good	1.70	#14-793	S\$153.70 Volume Pricing	2 In Stock
1348	0.1	Glass to Glass	Good	Good	1.348	#12-855	S\$56.19 Volume Pricing	2 In Stock
1348	0.34	Glass to Glass	Good	Good	1.348	#12-856	S\$162.40 Volume Pricing	1 In Stock
1369	0.1	Glass to Glass	Good	Good	1.369	#17-394	S\$73.22 Volume Pricing	1 In Stock
1369	0.34	Glass to Glass	Good	Good	1.369	#17-373	S\$175.45 Volume Pricing	2 In Stock
1375	0.1	Glass to Glass	Excellent	Good	1.375	#17-395	S\$39.15 Volume Pricing	1 In Stock
1375	0.34	Glass to Glass	Excellent	Good	1.375	#17-374	S\$81.92 Volume Pricing	1 In Stock
1422	0.1	Glass to Glass	Excellent	Good	1.422	#17-399	S\$73.22 Volume Pricing	2 In Stock
1422	0.34	Glass to Glass	Excellent	Good	1.422	#17-378	S\$175.45 Volume Pricing	2 In Stock
1622H	0.1	Glass to Glass	Excellent	Excellent	1.622	#17-402	S\$39.15 Volume Pricing	Contact Us
1622H	0.34	Glass to Glass	Excellent	Excellent	1.622	#17-381	S\$81.92 Volume Pricing	Contact Us
1639H	0.1	Glass to Glass	Excellent	Excellent	1.639	#17-403	S\$39.15 Volume Pricing	Contact Us
1639H	0.34	Glass to Glass	Excellent	Excellent	1.639	#17-382	S\$81.92 Volume Pricing	Contact Us
1665	0.1	Glass to Glass	Excellent	Good	1.665	#12-861	S\$39.15 Volume Pricing	2 In Stock
1665	0.34	Glass to Glass	Excellent	Good	1.665	#12-862	S\$81.92 Volume Pricing	1 In Stock
13685	0.1	Glass to Glass	Excellent	Good	1.3685	#12-852	S\$39.15 Volume Pricing	2 In Stock
13685	0.34	Glass to Glass	Excellent	Good	1.3685	#12-853	S\$81.92 Volume Pricing	2 In Stock
13775	0.1	Glass to Glass	Good	Good	1.3775	#17-396	S\$73.22 Volume Pricing	2 In Stock
13775	0.34	Glass to Glass	Good	Good	1.3775	#17-375	S\$175.45 Volume Pricing	1 In Stock
13825	0.1	Glass to Glass	Good	Good	1.3825	#17-397	S\$73.22 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com