

[All Products](#) / [Laser Optics](#) / [Laser Optical Assemblies](#) / [F-Theta Lenses](#)

Jenoptik JENar™ F-Theta Scanning Lenses See More by [Jenoptik](#)



- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Common Specifications

General

Manufacturer:	Jenoptik
---------------	----------

Threading & Mounting

Mounting Threads:	M85 x 1
-------------------	---------

Technical Information

Products

Wavelength Range (nm)	Scan Angle (°)	Scan Field (mm)	Type	FL (mm)	Stock Number	Price	Buy
515 - 540	52.1	165 x 165	JENar F-Theta	255.00	#16-773	S\$2,961.00	Contact Us
515 - 540	57.6	245 x 245	JENar F-Theta	330.00	#16-774	S\$1,922.00	5 In Stock
515 - 540	40	53 x 53	JENar F-Theta	108.00	#17-023	S\$3,850.00	5 In Stock
1030 - 1080	53.2	169 x 169	JENar F-Theta	255.00	#16-772	S\$1,998.00	5 In Stock
500 - 680, 1030 - 1080	37.2	57 x 57	JENar F-Theta	125.00	#17-024	S\$1,821.00	5 In Stock
500 - 680, 1030 - 1080	53.2	169 x 169	JENar F-Theta	255.00	#17-025	S\$2,533.00	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com