


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

SCHOTT D263® T eco Windows

See More by [SCHOTT Optical Components](#)



- Thin 0.4mm SCHOTT D263® T eco Substrates
- Excellent Glass Alternative to Plastic Optics
- Ideal for Weight and Space Sensitive Applications

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Clear Aperture (%):	90
Thickness (mm):	0.40 ±0.05	Poisson's Ratio:	0.21
Young's Modulus (GPa):	72.9		


Optical Properties

Coating:	Uncoated		
Index of Refraction (n_d):	1.523	Surface Quality:	80-50
Wavelength Range (nm):	350 - 2000		

Material Properties

Density (g/cm³):	2.51
Transformation Temperature (°C):	557

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
12.50	-	0.40	Uncoated	#18-298	S\$36.75 Volume Pricing	8 In Stock
25.00	-	0.40	Uncoated	#18-299	S\$39.90 Volume Pricing	4 In Stock
50.00	-	0.40	Uncoated	#18-300	S\$57.40 Volume Pricing	8 In Stock
-	25.00 x 25.00	0.40	Uncoated	#18-301	S\$39.90 Volume Pricing	20+ In Stock
-	50.00 x 50.00	0.40	Uncoated	#18-302	S\$57.40 Volume Pricing	20+ In Stock
-	100.00 x 100.00	0.40	Uncoated	#18-303	S\$70.00 Volume Pricing	Contact Us
5.00	-	0.40	Uncoated	#29-358	S\$28.00 Volume Pricing	15 In Stock
10.00	-	0.40	Uncoated	#29-359	S\$31.85 Volume Pricing	6 In Stock
3.00	-	0.40	Uncoated	#29-360	S\$43.40 Volume Pricing	20+ In Stock
40.00	-	0.40	Uncoated	#29-361	S\$47.60 Volume Pricing	15 In Stock
75.00	-	0.40	Uncoated	#29-362	S\$63.35 Volume Pricing	Contact Us
-	75.00 x 75.00	0.40	Uncoated	#29-363	S\$63.35 Volume Pricing	20+ In Stock
100.00	-	0.40	Uncoated	#29-364	S\$71.40 Volume Pricing	6 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com