

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

Advanced Illumination Medium Intensity Linear Backlights

See More by [Advanced Illumination](#)



- Intense, Diffuse Output up to 226,000 Lux
- Full Range of Wavelengths Available
- UltraSeal Washdown Backlights for Harsh Environments Also Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Common Specifications

General

LED Lifetime (hours):	50000	Type of Illumination:	LED Illuminator
Note:	Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Manufacturer:	Advanced Illumination
Geometry:	Backlight	Illumination Mode:	Constant

Electrical

Minimum Input Current:	0.8A
-------------------------------	------

Hardware & Interface Connectivity

Connector:	Flying Leads	
Input Voltage (V):	24V	Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855

Environmental & Durability Factors

Operating Temperature (°C):	0 - 50	Environmental Rating:	IP50
------------------------------------	--------	------------------------------	------

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
<u>#18-644 Clearance</u>					
216.4 x 32.2 x 21.7	IR	940		Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	S\$1,792.00 1 In Stock
<u>#18-640 Clearance</u>					
267.2 x 32.2 x 21.7	Blue	455		Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	S\$1,379.00 1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com