

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Filters](#) / [Color Filters](#)

Mounted Machine Vision Filters



- Optimized for Use with Popular LEDs
- Multiple Mounting Sizes and Threads Available to Ease System Compatibility
- $\geq 85\%$ Transmission
- [TECHSPEC® High Performance Mounted Machine Vision Filters](#) and [Mounted Color Filters](#) Also Available

Common Specifications

Physical & Mechanical Properties

Construction:

Mounted in Black Anodized Ring

Technical Information

Products

Filter Thread	Color	CWL (nm)	FWHM (nm)	Stock Number	Price	Buy
M77 x 0.75	NUV	324.00	105.00	#21-400	S\$700.00 Volume Pricing	1 In Stock
-	NUV	324.00	105.00	#70-534	S\$184.80 Volume Pricing	6 In Stock
-	Blue	470.00	85.00	#70-535	S\$184.80 Volume Pricing	6 In Stock
-	Cyan	505.00	90.00	#70-536	S\$184.80 Volume Pricing	5 In Stock
-	Green	525.00	80.00	#70-537	S\$184.80 Volume Pricing	7 In Stock
-	-	530.00	120.00	#70-538	S\$184.80 Volume Pricing	1 In Stock
-	VIS	550.00	300.00	#70-539	S\$169.40 Volume Pricing	1 In Stock
-	Orange	590.00	70.00	#70-540	S\$184.80 Volume Pricing	5 In Stock
-	Light Red	635.00	60.00	#70-541	S\$169.40 Volume Pricing	3 In Stock
-	Dark Red	660.00	70.00	#70-542	S\$169.40 Volume Pricing	9 In Stock
-	NIR-IR	800.00	315.00	#70-543	S\$169.40 Volume Pricing	1 In Stock
-	SWIR	1,000.00	150.00	#70-544	S\$361.20 Volume Pricing	5 In Stock
-	SWIR	1,550.00	190.00	#70-545	S\$558.60 Volume Pricing	5 In Stock
M77 x 0.75	Blue	470.00	85.00	#21-401	S\$700.00 Volume Pricing	1 In Stock
M77 x 0.75	Cyan	505.00	90.00	#21-402	S\$700.00 Volume Pricing	1 In Stock
M77 x 0.75	Green	525.00	80.00	#21-403	S\$700.00 Volume Pricing	1 In Stock
M77 x 0.75	Vis	550.00	300.00	#21-404	S\$631.40 Volume Pricing	1 In Stock

M77 x 0.75	Orange	590.00	75.00	#21-405	S\$700.00 Volume Pricing	1 In Stock
M77 x 0.75	Light Red	635.00	60.00	#21-406	S\$631.40 Volume Pricing	1 In Stock
M77 x 0.75	Dark Red	660.00	60.00	#21-407	S\$631.40 Volume Pricing	1 In Stock
M77 x 0.75	IR	850.00	160.00	#21-408	S\$631.40 Volume Pricing	1 In Stock
M39 x 0.50	NUV	324.00	105.00	#21-417	S\$302.40 Volume Pricing	1 In Stock
M39 x 0.50	Blue	470.00	85.00	#21-418	S\$302.40 Volume Pricing	2 In Stock
M39 x 0.50	Cyan	505.00	90.00	#21-419	S\$302.40 Volume Pricing	1 In Stock
M39 x 0.50	Green	525.00	80.00	#21-420	S\$302.40 Volume Pricing	2 In Stock
M39 x 0.50	Vis	550.00	300.00	#21-421	S\$273.00 Volume Pricing	1 In Stock
M39 x 0.50	Orange	590.00	75.00	#21-422	S\$302.40 Volume Pricing	2 In Stock
M39 x 0.50	Light Red	635.00	60.00	#21-423	S\$273.00 Volume Pricing	2 In Stock
M39 x 0.50	Dark Red	660.00	60.00	#21-424	S\$273.00 Volume Pricing	1 In Stock
M39 x 0.50	IR	850.00	160.00	#21-425	S\$273.00 Volume Pricing	Contact Us
M49 x 0.75	NUV	324.00	105.00	#21-434	S\$341.60 Volume Pricing	1 In Stock
M49 x 0.75	Blue	470.00	85.00	#21-435	S\$341.60 Volume Pricing	3 In Stock
M49 x 0.75	Cyan	505.00	90.00	#21-436	S\$341.60 Volume Pricing	1 In Stock
M49 x 0.75	Green	525.00	80.00	#21-437	S\$341.60 Volume Pricing	Contact Us
M49 x 0.75	Vis	550.00	300.00	#21-438	S\$306.60 Volume Pricing	1 In Stock
M49 x 0.75	Orange	590.00	75.00	#21-439	S\$341.60 Volume Pricing	1 In Stock

M49 x 0.75	Light Red	635.00	60.00	#21-440	S\$306.60 Volume Pricing	2 In Stock
M49 x 0.75	Dark Red	660.00	60.00	#21-441	S\$306.60 Volume Pricing	5 In Stock
M49 x 0.75	IR	850.00	160.00	#21-442	S\$306.60 Volume Pricing	1 In Stock
M67 x 0.75	NUV	324.00	105.00	#21-451	S\$548.80 Volume Pricing	1 In Stock
M67 x 0.75	Blue	470.00	85.00	#21-452	S\$548.80 Volume Pricing	1 In Stock
M67 x 0.75	Cyan	505.00	90.00	#21-453	S\$548.80 Volume Pricing	1 In Stock
M67 x 0.75	Green	525.00	80.00	#21-454	S\$548.80 Volume Pricing	1 In Stock
M67 x 0.75	Vis	550.00	300.00	#21-455	S\$492.80 Volume Pricing	1 In Stock
M67 x 0.75	Orange	590.00	75.00	#21-456	S\$548.80 Volume Pricing	1 In Stock
M67 x 0.75	Light Red	635.00	60.00	#21-457	S\$492.80 Volume Pricing	1 In Stock
M67 x 0.75	Dark Red	660.00	60.00	#21-458	S\$492.80 Volume Pricing	1 In Stock
M67 x 0.75	IR	850.00	160.00	#21-459	S\$492.80 Volume Pricing	1 In Stock
M52 x 0.75	NUV	324.00	105.00	#21-468	S\$351.40 Volume Pricing	1 In Stock
M52 x 0.75	Blue	470.00	85.00	#21-469	S\$351.40 Volume Pricing	2 In Stock
M52 x 0.75	Cyan	505.00	90.00	#21-470	S\$351.40 Volume Pricing	Contact Us
M52 x 0.75	Green	525.00	80.00	#21-471	S\$351.40 Volume Pricing	1 In Stock
M52 x 0.75	Vis	550.00	300.00	#21-472	S\$316.40 Volume Pricing	2 In Stock
M52 x 0.75	Orange	590.00	75.00	#21-473	S\$351.40 Volume Pricing	1 In Stock
M52 x 0.75	Light Red	635.00	60.00	#21-474	S\$316.40 Volume Pricing	1 In Stock

M52 x 0.75	Dark Red	660.00	60.00	#21-475	S\$316.40 Volume Pricing	Contact Us
M52 x 0.75	IR	850.00	160.00	#21-476	S\$316.40 Volume Pricing	Contact Us
M55 x 0.75	NUV	324.00	105.00	#21-485	S\$366.80 Volume Pricing	1 In Stock
M55 x 0.75	Blue	470.00	85.00	#21-486	S\$366.80 Volume Pricing	1 In Stock
M55 x 0.75	Cyan	505.00	90.00	#21-487	S\$366.80 Volume Pricing	1 In Stock
M55 x 0.75	Green	525.00	80.00	#21-488	S\$366.80 Volume Pricing	1 In Stock
M55 x 0.75	Vis	550.00	300.00	#21-489	S\$331.80 Volume Pricing	Contact Us
M55 x 0.75	Orange	590.00	75.00	#21-490	S\$366.80 Volume Pricing	1 In Stock
M55 x 0.75	Light Red	635.00	60.00	#21-491	S\$331.80 Volume Pricing	Contact Us
M55 x 0.75	Dark Red	660.00	60.00	#21-492	S\$331.80 Volume Pricing	Contact Us
M55 x 0.75	IR	850.00	160.00	#21-493	S\$331.80 Volume Pricing	2 In Stock
M55 x 0.75	SWIR	940.00	55.00	#28-794	S\$393.40	1 In Stock
M55 x 0.75	SWIR	1,000.00	150.00	#28-805	S\$677.60	1 In Stock
M55 x 0.75	SWIR	1,070.00	-	#28-860	S\$533.40	1 In Stock
M55 x 0.75	SWIR	1,300.00	35.00	#28-827	S\$730.80	1 In Stock
M55 x 0.75	SWIR	1,450.00	35.00	#28-838	S\$730.80	1 In Stock
M55 x 0.75	SWIR	1,475.00	-	#28-871	S\$476.00	1 In Stock
M55 x 0.75	SWIR	1,550.00	190.00	#28-816	S\$847.00	1 In Stock
M55 x 0.75	SWIR	1,550.00	35.00	#28-849	S\$730.80	1 In Stock
M86 x 0.75	NUV	324.00	105.00	#21-502	S\$945.00 Volume Pricing	1 In Stock
M86 x 0.75	Blue	470.00	85.00	#21-503	S\$945.00 Volume Pricing	1 In Stock
M86 x 0.75	Cyan	505.00	90.00	#21-504	S\$945.00 Volume Pricing	1 In Stock

M86 x 0.75	Green	525.00	80.00	#21-505	S\$945.00 Volume Pricing	1 In Stock
M86 x 0.75	Vis	550.00	300.00	#21-506	S\$854.00 Volume Pricing	1 In Stock
M86 x 0.75	Orange	590.00	75.00	#21-507	S\$945.00 Volume Pricing	1 In Stock
M86 x 0.75	Light Red	635.00	60.00	#21-508	S\$854.00 Volume Pricing	1 In Stock
M86 x 0.75	Dark Red	660.00	60.00	#21-509	S\$854.00 Volume Pricing	1 In Stock
M86 x 0.75	IR	850.00	160.00	#21-510	S\$854.00 Volume Pricing	1 In Stock
M22 x 0.75	NUV	324.00	105.00	#21-519	S\$274.40 Volume Pricing	1 In Stock
M22 x 0.75	Blue	470.00	85.00	#21-520	S\$274.40 Volume Pricing	1 In Stock
M22 x 0.75	Cyan	505.00	90.00	#21-521	S\$274.40 Volume Pricing	1 In Stock
M22 x 0.75	Green	525.00	80.00	#21-522	S\$274.40 Volume Pricing	1 In Stock
M22 x 0.75	Vis	550.00	300.00	#21-523	S\$252.00 Volume Pricing	1 In Stock
M22 x 0.75	Orange	590.00	75.00	#21-524	S\$274.40 Volume Pricing	1 In Stock
M22 x 0.75	Light Red	635.00	60.00	#21-525	S\$252.00 Volume Pricing	1 In Stock
M22 x 0.75	Dark Red	660.00	60.00	#21-526	S\$252.00 Volume Pricing	1 In Stock
M22 x 0.75	IR	850.00	160.00	#21-527	S\$252.00 Volume Pricing	1 In Stock
M22.5 x 0.50	NUV	324.00	105.00	#21-536	S\$219.80 Volume Pricing	1 In Stock
M22.5 x 0.50	Blue	470.00	85.00	#21-537	S\$219.80 Volume Pricing	Contact Us
M22.5 x 0.50	Cyan	505.00	90.00	#21-538	S\$219.80 Volume Pricing	1 In Stock
M22.5 x 0.50	Green	525.00	80.00	#21-539	S\$219.80 Volume Pricing	1 In Stock
M22.5 x 0.50	Vis	550.00	300.00	#21-540	S\$197.40 Volume Pricing	Contact Us

M22.5 x 0.50	Orange	590.00	75.00	#21-541	S\$219.80 Volume Pricing	1 In Stock
M22.5 x 0.50	Light Red	635.00	60.00	#21-542	S\$197.40 Volume Pricing	2 In Stock
M22.5 x 0.50	Dark Red	660.00	60.00	#21-543	S\$197.40 Volume Pricing	2 In Stock
M22.5 x 0.50	IR	850.00	160.00	#21-544	S\$197.40 Volume Pricing	1 In Stock
M37 x 0.75	NUV	324.00	105.00	#21-553	S\$274.40 Volume Pricing	1 In Stock
M37 x 0.75	Blue	470.00	85.00	#21-554	S\$274.40 Volume Pricing	1 In Stock
M37 x 0.75	Cyan	505.00	90.00	#21-555	S\$274.40 Volume Pricing	1 In Stock
M37 x 0.75	Green	525.00	80.00	#21-556	S\$274.40 Volume Pricing	2 In Stock
M37 x 0.75	Vis	550.00	300.00	#21-557	S\$246.40 Volume Pricing	1 In Stock
M37 x 0.75	Orange	590.00	75.00	#21-558	S\$274.40 Volume Pricing	1 In Stock
M37 x 0.75	Light Red	635.00	60.00	#21-559	S\$246.40 Volume Pricing	3 In Stock
M37 x 0.75	Dark Red	660.00	60.00	#21-560	S\$246.40 Volume Pricing	Contact Us
M37 x 0.75	IR	850.00	160.00	#21-561	S\$246.40 Volume Pricing	5 In Stock
M37 x 0.75	SWIR	940.00	55.00	#28-790	S\$294.00	1 In Stock
M37 x 0.75	SWIR	1,000.00	150.00	#28-801	S\$525.00	1 In Stock
M37 x 0.75	SWIR	1,070.00	-	#28-856	S\$362.60	Contact Us
M37 x 0.75	SWIR	1,300.00	35.00	#28-823	S\$518.00	1 In Stock
M37 x 0.75	SWIR	1,450.00	35.00	#28-834	S\$518.00	1 In Stock
M37 x 0.75	SWIR	1,475.00	-	#28-867	S\$305.20	1 In Stock
M37 x 0.75	SWIR	1,550.00	190.00	#28-812	S\$694.40	1 In Stock
M37 x 0.75	SWIR	1,550.00	35.00	#28-845	S\$518.00	2 In Stock
M35.5 x 0.50	NUV	324.00	105.00	#21-570	S\$257.60 Volume Pricing	1 In Stock

M35.5 x 0.50	Blue	470.00	85.00	#21-571	S\$257.60 Volume Pricing	1 In Stock
M35.5 x 0.50	Cyan	505.00	90.00	#21-572	S\$257.60 Volume Pricing	1 In Stock
M35.5 x 0.50	Green	525.00	80.00	#21-573	S\$257.60 Volume Pricing	1 In Stock
M35.5 x 0.50	Vis	550.00	300.00	#21-574	S\$232.40 Volume Pricing	1 In Stock
M35.5 x 0.50	Orange	590.00	75.00	#21-575	S\$257.60 Volume Pricing	5 In Stock
M35.5 x 0.50	Light Red	635.00	60.00	#21-576	S\$232.40 Volume Pricing	1 In Stock
M35.5 x 0.50	Dark Red	660.00	60.00	#21-577	S\$232.40 Volume Pricing	1 In Stock
M35.5 x 0.50	IR	850.00	160.00	#21-578	S\$232.40 Volume Pricing	1 In Stock
M35.5 x 0.50	SWIR	940.00	55.00	#28-789	S\$275.80	1 In Stock
M35.5 x 0.50	SWIR	1,000.00	150.00	#28-800	S\$483.00	1 In Stock
M35.5 x 0.50	SWIR	1,070.00	-	#28-855	S\$323.40	1 In Stock
M35.5 x 0.50	SWIR	1,300.00	35.00	#28-822	S\$502.60	1 In Stock
M35.5 x 0.50	SWIR	1,450.00	35.00	#28-833	S\$502.60	1 In Stock
M35.5 x 0.50	SWIR	1,475.00	-	#28-866	S\$267.40	1 In Stock
M35.5 x 0.50	SWIR	1,550.00	190.00	#28-811	S\$651.00	1 In Stock
M35.5 x 0.50	SWIR	1,550.00	35.00	#28-844	S\$502.60	1 In Stock
M72 x 0.75	NUV	324.00	105.00	#21-587	S\$613.20 Volume Pricing	1 In Stock
M72 x 0.75	Blue	470.00	85.00	#21-588	S\$613.20 Volume Pricing	Contact Us
M72 x 0.75	Cyan	505.00	90.00	#21-589	S\$613.20 Volume Pricing	1 In Stock
M72 x 0.75	Green	525.00	80.00	#21-590	S\$613.20 Volume Pricing	Contact Us
M72 x 0.75	Vis	550.00	300.00	#21-591	S\$553.00 Volume Pricing	Contact Us
M72 x 0.75	Orange	590.00	75.00	#21-592	S\$613.20 Volume Pricing	1 In Stock

M72 x 0.75	Light Red	635.00	60.00	#21-593	S\$553.00 Volume Pricing	2 In Stock
M72 x 0.75	Dark Red	660.00	60.00	#21-594	S\$553.00 Volume Pricing	1 In Stock
M72 x 0.75	IR	850.00	160.00	#21-595	S\$553.00 Volume Pricing	2 In Stock
M72 x 0.75	SWIR	940.00	55.00	#28-796	S\$656.60	1 In Stock
M72 x 0.75	SWIR	1,000.00	150.00	#28-807	S\$947.80	Contact Us
M72 x 0.75	SWIR	1,070.00	-	#28-862	S\$1,050.00	1 In Stock
M72 x 0.75	SWIR	1,300.00	35.00	#28-829	S\$1,106.00	1 In Stock
M72 x 0.75	SWIR	1,450.00	35.00	#28-840	S\$1,106.00	1 In Stock
M72 x 0.75	SWIR	1,475.00	-	#28-873	S\$723.80	2 In Stock
M72 x 0.75	SWIR	1,550.00	190.00	#28-818	S\$1,120.00	1 In Stock
M72 x 0.75	SWIR	1,550.00	35.00	#28-851	S\$1,106.00	Contact Us
M105 x 1.00	NUV	324.00	105.00	#21-604	S\$1,435.00 Volume Pricing	1 In Stock
M105 x 1.00	Blue	470.00	85.00	#21-605	S\$1,435.00 Volume Pricing	1 In Stock
M105 x 1.00	Cyan	505.00	90.00	#21-606	S\$1,435.00 Volume Pricing	1 In Stock
M105 x 1.00	Green	525.00	80.00	#21-607	S\$1,435.00 Volume Pricing	1 In Stock
M105 x 1.00	Vis	550.00	300.00	#21-608	S\$1,295.00 Volume Pricing	1 In Stock
M105 x 1.00	Orange	590.00	75.00	#21-609	S\$1,435.00 Volume Pricing	1 In Stock
M105 x 1.00	Light Red	635.00	60.00	#21-610	S\$1,295.00 Volume Pricing	1 In Stock
M105 x 1.00	Dark Red	660.00	60.00	#21-611	S\$1,295.00 Volume Pricing	1 In Stock
M105 x 1.00	IR	850.00	160.00	#21-612	S\$1,295.00 Volume Pricing	1 In Stock
M62 x 0.75	NUV	324.00	105.00	#21-621	S\$478.80 Volume Pricing	1 In Stock

M62 x 0.75	Blue	470.00	85.00	#21-622	S\$478.80 Volume Pricing	1 In Stock
M62 x 0.75	Cyan	505.00	90.00	#21-623	S\$478.80 Volume Pricing	1 In Stock
M62 x 0.75	Green	525.00	80.00	#21-624	S\$478.80 Volume Pricing	Contact Us
M62 x 0.75	Vis	550.00	300.00	#21-625	S\$429.80 Volume Pricing	1 In Stock
M62 x 0.75	Orange	590.00	75.00	#21-626	S\$478.80 Volume Pricing	1 In Stock
M62 x 0.75	Light Red	635.00	60.00	#21-627	S\$429.80 Volume Pricing	1 In Stock
M62 x 0.75	Dark Red	660.00	60.00	#21-628	S\$429.80 Volume Pricing	1 In Stock
M62 x 0.75	IR	850.00	160.00	#21-629	S\$429.80 Volume Pricing	1 In Stock
M46 x 0.75	NUV	324.00	105.00	#21-638	S\$330.40 Volume Pricing	1 In Stock
M46 x 0.75	Blue	470.00	85.00	#21-639	S\$330.40 Volume Pricing	1 In Stock
M46 x 0.75	Cyan	505.00	90.00	#21-640	S\$330.40 Volume Pricing	1 In Stock
M46 x 0.75	Green	525.00	80.00	#21-641	S\$330.40 Volume Pricing	1 In Stock
M46 x 0.75	Vis	550.00	300.00	#21-642	S\$296.80 Volume Pricing	3 In Stock
M46 x 0.75	Orange	590.00	75.00	#21-643	S\$330.40 Volume Pricing	1 In Stock
M46 x 0.75	Light Red	635.00	60.00	#21-644	S\$296.80 Volume Pricing	1 In Stock
M46 x 0.75	Dark Red	660.00	60.00	#21-645	S\$296.80 Volume Pricing	Contact Us
M46 x 0.75	IR	850.00	160.00	#21-646	S\$296.80 Volume Pricing	Contact Us
M46 x 0.75	SWIR	940.00	55.00	#28-793	S\$352.80	1 In Stock
M46 x 0.75	SWIR	1,000.00	150.00	#28-804	S\$634.20	1 In Stock
M46 x 0.75	SWIR	1,070.00	-	#28-859	S\$476.00	1 In Stock
M46 x 0.75	SWIR	1,300.00	35.00	#28-826	S\$609.00	1 In Stock

M46 x 0.75	SWIR	1,450.00	35.00	#28-837	S\$609.00	1 In Stock
M46 x 0.75	SWIR	1,475.00	-	#28-870	S\$418.60	1 In Stock
M46 x 0.75	SWIR	1,550.00	190.00	#28-815	S\$805.00	1 In Stock
M46 x 0.75	SWIR	1,550.00	35.00	#28-848	S\$609.00	1 In Stock
M40.5 x 0.50	NUV	324.00	105.00	#21-655	S\$302.40 Volume Pricing	1 In Stock
M40.5 x 0.50	Blue	470.00	85.00	#21-656	S\$302.40 Volume Pricing	1 In Stock
M40.5 x 0.50	Cyan	505.00	90.00	#21-657	S\$302.40 Volume Pricing	1 In Stock
M40.5 x 0.50	Green	525.00	80.00	#21-658	S\$302.40 Volume Pricing	1 In Stock
M40.5 x 0.50	Vis	550.00	300.00	#21-659	S\$273.00 Volume Pricing	1 In Stock
M40.5 x 0.50	Orange	590.00	75.00	#21-660	S\$302.40 Volume Pricing	1 In Stock
M40.5 x 0.50	Light Red	635.00	60.00	#21-661	S\$273.00 Volume Pricing	1 In Stock
M40.5 x 0.50	Dark Red	660.00	60.00	#21-662	S\$273.00 Volume Pricing	1 In Stock
M40.5 x 0.50	IR	850.00	160.00	#21-663	S\$273.00 Volume Pricing	1 In Stock
M40.5 x 0.50	SWIR	940.00	55.00	#28-791	S\$323.40	1 In Stock
M40.5 x 0.50	SWIR	1,000.00	150.00	#28-802	S\$575.40	1 In Stock
M40.5 x 0.50	SWIR	1,070.00	-	#28-857	S\$400.40	Contact Us
M40.5 x 0.50	SWIR	1,300.00	35.00	#28-824	S\$593.60	1 In Stock
M40.5 x 0.50	SWIR	1,450.00	35.00	#28-835	S\$593.60	1 In Stock
M40.5 x 0.50	SWIR	1,475.00	-	#28-868	S\$343.00	1 In Stock
M40.5 x 0.50	SWIR	1,550.00	190.00	#28-813	S\$744.80	1 In Stock
M40.5 x 0.50	SWIR	1,550.00	35.00	#28-846	S\$593.60	1 In Stock
M37.5 x 0.50	NUV	324.00	105.00	#21-672	S\$274.40 Volume Pricing	1 In Stock
M37.5 x 0.50	Blue	470.00	85.00	#21-673	S\$274.40 Volume Pricing	2 In Stock

M37.5 x 0.50	Cyan	505.00	90.00	#21-674	S\$274.40 Volume Pricing	1 In Stock
M37.5 x 0.50	Green	525.00	80.00	#21-675	S\$274.40 Volume Pricing	1 In Stock
M37.5 x 0.50	Vis	550.00	300.00	#21-676	S\$246.40 Volume Pricing	2 In Stock
M37.5 x 0.50	Orange	590.00	75.00	#21-677	S\$274.40 Volume Pricing	1 In Stock
M37.5 x 0.50	Light Red	635.00	60.00	#21-678	S\$246.40 Volume Pricing	1 In Stock
M37.5 x 0.50	Dark Red	660.00	60.00	#21-679	S\$246.40 Volume Pricing	1 In Stock
M37.5 x 0.50	IR	850.00	160.00	#21-680	S\$246.40 Volume Pricing	2 In Stock
M43 x 0.75	NUV	324.00	105.00	#21-689	S\$302.40 Volume Pricing	1 In Stock
M43 x 0.75	Blue	470.00	85.00	#21-690	S\$302.40 Volume Pricing	1 In Stock
M43 x 0.75	Cyan	505.00	90.00	#21-691	S\$302.40 Volume Pricing	Contact Us
M43 x 0.75	Green	525.00	80.00	#21-692	S\$302.40 Volume Pricing	1 In Stock
M43 x 0.75	Vis	550.00	300.00	#21-693	S\$273.00 Volume Pricing	1 In Stock
M43 x 0.75	Orange	590.00	75.00	#21-694	S\$302.40 Volume Pricing	1 In Stock
M43 x 0.75	Light Red	635.00	60.00	#21-695	S\$273.00 Volume Pricing	1 In Stock
M43 x 0.75	Dark Red	660.00	60.00	#21-696	S\$273.00 Volume Pricing	1 In Stock
M43 x 0.75	IR	850.00	160.00	#21-697	S\$273.00 Volume Pricing	3 In Stock
M43 x 0.75	SWIR	940.00	55.00	#28-792	S\$323.40	1 In Stock
M43 x 0.75	SWIR	1,000.00	150.00	#28-803	S\$575.40	1 In Stock
M43 x 0.75	SWIR	1,070.00	-	#28-858	S\$438.20	1 In Stock
M43 x 0.75	SWIR	1,300.00	35.00	#28-825	S\$609.00	2 In Stock
M43 x 0.75	SWIR	1,450.00	35.00	#28-836	S\$609.00	Contact Us

M43 x 0.75	SWIR	1,475.00	-	#28-869	S\$380.80	1 In Stock
M43 x 0.75	SWIR	1,550.00	190.00	#28-814	S\$744.80	1 In Stock
M43 x 0.75	SWIR	1,550.00	35.00	#28-847	S\$609.00	1 In Stock
M34 x 0.50	NUV	324.00	105.00	#21-706	S\$257.60 Volume Pricing	1 In Stock
M34 x 0.50	Blue	470.00	85.00	#21-707	S\$257.60 Volume Pricing	1 In Stock
M34 x 0.50	Cyan	505.00	90.00	#21-708	S\$257.60 Volume Pricing	1 In Stock
M34 x 0.50	Green	525.00	80.00	#21-709	S\$257.60 Volume Pricing	2 In Stock
M34 x 0.50	Vis	550.00	300.00	#21-710	S\$232.40 Volume Pricing	2 In Stock
M34 x 0.50	Orange	590.00	75.00	#21-711	S\$257.60 Volume Pricing	Contact Us
M34 x 0.50	Light Red	635.00	60.00	#21-712	S\$232.40 Volume Pricing	1 In Stock
M34 x 0.50	Dark Red	660.00	60.00	#21-713	S\$232.40 Volume Pricing	1 In Stock
M34 x 0.50	IR	850.00	160.00	#21-714	S\$232.40 Volume Pricing	2 In Stock
M34 x 0.50	SWIR	940.00	55.00	#28-788	S\$275.80	1 In Stock
M34 x 0.50	SWIR	1,000.00	150.00	#28-799	S\$483.00	1 In Stock
M34 x 0.50	SWIR	1,070.00	-	#28-854	S\$323.40	Contact Us
M34 x 0.50	SWIR	1,300.00	35.00	#28-821	S\$502.60	2 In Stock
M34 x 0.50	SWIR	1,450.00	35.00	#28-832	S\$502.60	Contact Us
M34 x 0.50	SWIR	1,475.00	-	#28-865	S\$267.40	1 In Stock
M34 x 0.50	SWIR	1,550.00	190.00	#28-810	S\$651.00	2 In Stock
M34 x 0.50	SWIR	1,550.00	35.00	#28-843	S\$502.60	1 In Stock
M58 x 0.75	NUV	324.00	105.00	#21-723	S\$383.60 Volume Pricing	1 In Stock
M58 x 0.75	Blue	470.00	85.00	#21-724	S\$383.60 Volume Pricing	1 In Stock

M58 x 0.75	Cyan	505.00	90.00	#21-725	S\$383.60 Volume Pricing	1 In Stock
M58 x 0.75	Green	525.00	80.00	#21-726	S\$383.60 Volume Pricing	1 In Stock
M58 x 0.75	Vis	550.00	300.00	#21-727	S\$345.80 Volume Pricing	1 In Stock
M58 x 0.75	Orange	590.00	75.00	#21-728	S\$383.60 Volume Pricing	1 In Stock
M58 x 0.75	Light Red	635.00	60.00	#21-729	S\$345.80 Volume Pricing	1 In Stock
M58 x 0.75	Dark Red	660.00	60.00	#21-730	S\$345.80 Volume Pricing	1 In Stock
M58 x 0.75	IR	850.00	160.00	#21-731	S\$345.80 Volume Pricing	7 In Stock
M58 x 0.75	SWIR	940.00	55.00	#28-795	S\$410.20	1 In Stock
M58 x 0.75	SWIR	1,000.00	150.00	#28-806	S\$702.80	1 In Stock
M58 x 0.75	SWIR	1,070.00	-	#28-861	S\$533.40	1 In Stock
M58 x 0.75	SWIR	1,300.00	35.00	#28-828	S\$730.80	Contact Us
M58 x 0.75	SWIR	1,450.00	35.00	#28-839	S\$730.80	1 In Stock
M58 x 0.75	SWIR	1,475.00	-	#28-872	S\$476.00	1 In Stock
M58 x 0.75	SWIR	1,550.00	190.00	#28-817	S\$870.80	1 In Stock
M58 x 0.75	SWIR	1,550.00	35.00	#28-850	S\$730.80	1 In Stock
M25.5 x 0.50	NUV	324.00	105.00	#21-740	S\$219.80 Volume Pricing	1 In Stock
M25.5 x 0.50	Blue	470.00	85.00	#21-741	S\$219.80 Volume Pricing	Contact Us
M25.5 x 0.50	Cyan	505.00	90.00	#21-742	S\$219.80 Volume Pricing	1 In Stock
M25.5 x 0.50	Green	525.00	80.00	#21-743	S\$219.80 Volume Pricing	2 In Stock
M25.5 x 0.50	Vis	550.00	300.00	#21-744	S\$197.40 Volume Pricing	6 In Stock
M25.5 x 0.50	Orange	590.00	75.00	#21-745	S\$219.80 Volume Pricing	1 In Stock

M25.5 x 0.50	Light Red	635.00	60.00	#21-746	S\$197.40 Volume Pricing	1 In Stock
M25.5 x 0.50	Dark Red	660.00	60.00	#21-747	S\$197.40 Volume Pricing	1 In Stock
M25.5 x 0.50	IR	850.00	160.00	#21-748	S\$197.40 Volume Pricing	7 In Stock
M25.5 x 0.50	SWIR	940.00	55.00	#28-786	S\$235.20	1 In Stock
M25.5 x 0.50	SWIR	1,000.00	150.00	#28-797	S\$422.80	1 In Stock
M25.5 x 0.50	SWIR	1,070.00	-	#28-852	S\$285.60	Contact Us
M25.5 x 0.50	SWIR	1,300.00	35.00	#28-819	S\$418.60	1 In Stock
M25.5 x 0.50	SWIR	1,450.00	35.00	#28-830	S\$418.60	1 In Stock
M25.5 x 0.50	SWIR	1,475.00	-	#28-863	S\$229.60	2 In Stock
M25.5 x 0.50	SWIR	1,550.00	190.00	#28-808	S\$592.20	3 In Stock
M25.5 x 0.50	SWIR	1,550.00	35.00	#28-841	S\$418.60	2 In Stock
M30.5 x 0.50	NUV	324.00	105.00	#21-757	S\$236.60 Volume Pricing	1 In Stock
M30.5 x 0.50	Blue	470.00	85.00	#21-758	S\$236.60 Volume Pricing	1 In Stock
M30.5 x 0.50	Cyan	505.00	90.00	#21-759	S\$236.60 Volume Pricing	1 In Stock
M30.5 x 0.50	Green	525.00	80.00	#21-760	S\$236.60 Volume Pricing	Contact Us
M30.5 x 0.50	Vis	550.00	300.00	#21-761	S\$212.80 Volume Pricing	1 In Stock
M30.5 x 0.50	Orange	590.00	75.00	#21-762	S\$236.60 Volume Pricing	1 In Stock
M30.5 x 0.50	Light Red	635.00	60.00	#21-763	S\$212.80 Volume Pricing	1 In Stock
M30.5 x 0.50	Dark Red	660.00	60.00	#21-764	S\$212.80 Volume Pricing	2 In Stock
M30.5 x 0.50	IR	850.00	160.00	#21-765	S\$212.80 Volume Pricing	1 In Stock
M30.5 x 0.50	SWIR	940.00	55.00	#28-787	S\$252.00	1 In Stock
M30.5 x 0.50	SWIR	1,000.00	150.00	#28-798	S\$448.00	1 In Stock

M30.5 x 0.50	SWIR	1,070.00	-	#28-853	S\$305.20	1 In Stock
M30.5 x 0.50	SWIR	1,300.00	35.00	#28-820	S\$457.80	1 In Stock
M30.5 x 0.50	SWIR	1,450.00	35.00	#28-831	S\$457.80	1 In Stock
M30.5 x 0.50	SWIR	1,475.00	-	#28-864	S\$247.80	1 In Stock
M30.5 x 0.50	SWIR	1,550.00	190.00	#28-809	S\$617.40	1 In Stock
M30.5 x 0.50	SWIR	1,550.00	35.00	#28-842	S\$457.80	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com