

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Flat Dome Lights](#)

Effilux Flat Dome Lights



- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Common Specifications

General

Type of Illumination:	LED Illuminator	Manufacturer:	Effilux
Geometry:	Flat Dome Light	Illumination Mode:	Constant

Hardware & Interface Connectivity

Input Voltage (V):	24	Power Supply:	Power Supply Required and Sold Separately: USA: #15-874 Europe: #15-875 Japan: #73-409 Korea: #73-409 China: #15-874
---------------------------	----	----------------------	---

Technical Information

Products

Color	Active Area (mm)	Stock Number	Price	Buy
Red	200 x 200	#22-106	S\$1,166.00	Contact Us
Blue	200 x 200	#22-107	S\$1,166.00	Contact Us
White	300 x 300	#22-108	S\$1,979.00	2 In Stock
Red	300 x 300	#22-109	S\$1,979.00	Contact Us
Blue	300 x 300	#22-110	S\$1,979.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com