

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

Effilux High Power LED Backlights



- >90% Uniformity
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light

Common Specifications

General

Type of Illumination:	LED illumination	Uniformity (%):	>90%
Manufacturer:	Effilux	Geometry:	Backlight
Illumination Mode:	Continuous with AIC (Analog Intensity Control)		

Hardware & Interface Connectivity

Power Supply Required and Sold Separately:
USA: [#15-874](#)
Europe: [#15-875](#)
Japan: [#73-409](#)
Korea: [#73-409](#)
China: [#15-874](#)

Environmental & Durability Factors

Operating Temperature (°C): 0 - 50

Technical Information

Products

Color	Active Area (mm)	Stock Number	Price	Buy
White	200 x 200	#22-098	S\$1,071.00	2 In Stock
Red	200 x 200	#22-099	S\$1,071.00	1 In Stock
Blue	200 x 200	#22-100	S\$1,071.00	Contact Us
White	300 x 300	#22-101	S\$1,733.00	2 In Stock
Red	300 x 300	#22-102	S\$1,733.00	Contact Us
Blue	300 x 300	#22-103	S\$1,733.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com