

[All Products](#) /
 [Imaging Lenses](#) /
 [Zoom & Variable Magnification Lenses](#) /
 [Zoom Lenses](#)

Motorized Telephoto Varifocal Lenses



- 9-36mm Focal Length Range with Fields of View Between 10 and 39°
- NIR Corrected for Multi-Spectral and Day/Night Applications
- Manual, P-Iris and DC Auto-Iris Models Available

Common Specifications

Physical & Mechanical Properties

Iris Option:	Motorized	Length (mm):	62.50
Maximum Diameter (mm):	54.00	Weight (g):	68.00

Optical Properties

Horizontal Field of View @ Max Sensor Format:	39° - 10°	Focal Length Range (mm):	9.0-36.0
Working Distance (mm):	2500 - ∞	Aperture (f/#):	f/1.5 - Closed

Sensor

Maximum Sensor Format:	1/2.3"
-------------------------------	--------

Threading & Mounting

Mount:	CS-Mount
---------------	----------

Technical Information

Products

Title	Stock Number	Price	Buy
9.0 - 36.0mm FL, CS-Mount, P-Iris, IR Cut, Telephoto Lens	#22-822	S\$706.00	1 In Stock
9.0 - 36.0mm FL, CS-Mount, P-Iris, IR Cut, PI Telephoto Lens	#22-824	S\$719.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com