

[All Products](#) / [Optics](#) / [Fiber Optics](#)

Single Mode Fiber Optic Patchcords



- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 450 – 1650nm
- 1m, 2m and 5m Standardized Lengths Available

Common Specifications

Physical & Mechanical Properties

Jacket Material:

900µm Yellow Hytrel® Tubing

Optical Properties

Numerical Aperture NA:

0.13

Technical Information

Products

Wavelength Range (nm)	Mode Field Diameter (nm)	NA	Connector	Length (m)	Stock Number	Price	Buy
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	1	#25-928	S\$63.80 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	2	#25-929	S\$66.70 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	5	#71-136	S\$71.05	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	1	#25-930	S\$98.60 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	2	#25-931	S\$107.30 Volume Pricing	2 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	5	#71-137	S\$120.35	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	1	#25-932	S\$130.50 Volume Pricing	7 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	2	#25-933	S\$140.65 Volume Pricing	4 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	5	#71-138	S\$156.60	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	1	#25-934	S\$102.95 Volume Pricing	2 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	2	#25-935	S\$105.85 Volume Pricing	1 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC	5	#71-139	S\$110.20	1 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	1	#25-936	S\$116.00 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	2	#25-937	S\$124.70 Volume Pricing	6 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC	5	#71-140	S\$137.75	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	1	#25-938	S\$100.05 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	2	#25-939	S\$102.95 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	5	#71-141	S\$107.30	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	1	#25-940	S\$162.40 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	2	#25-941	S\$169.65 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	5	#71-142	S\$181.25	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	1	#25-942	S\$168.20 Volume Pricing	5 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	2	#25-943	S\$176.90 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	5	#71-143	S\$189.95	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	1	#25-944	S\$136.30 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	2	#25-945	S\$139.20 Volume Pricing	2 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/APC	5	#71-144	S\$143.55	2 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	1	#25-946	S\$150.80 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	2	#25-947	S\$156.60 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/APC	5	#71-145	S\$165.30	2 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	1	#25-948	S\$82.65 Volume Pricing	5 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	5	#71-146	S\$89.90	5 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	1	#25-949	S\$145.00 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	5	#71-147	S\$166.75	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	1	#25-950	S\$153.70 Volume Pricing	3 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	5	#71-148	S\$179.80	3 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC to FC/APC	1	#25-951	S\$126.15 Volume Pricing	1 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC to FC/APC	5	#71-149	S\$133.40	1 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC to FC/APC	1	#25-952	S\$142.10 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC to FC/APC	5	#71-150	S\$163.85	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com