

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Metrology Lasers](#)

Coherent® Surelock™ Mini-Benchtop Laser Systems [See More](#)

by [Coherent®](#)



- Narrow 0.07nm FWHM Spectral Linewidth
- Extreme Temperature Insensitivity
- Ultra-Compact, Easy-to-Use Turnkey Laser System

Common Specifications

General

Note:	Recommended Fiber Patchcord: #23-706
-------	--

Physical & Mechanical Properties

Dimensions (mm):	150 x 150 x 50
Weight (kg):	1.00

Optical Properties

Numerical Aperture NA:	0.22
Spectral Line Width (nm):	0.07

Electrical

Input Current (A):	1.00
--------------------	------

Hardware & Interface Connectivity

Connector:	FC/PC	Input Voltage (V):	90 - 240 (AC)
------------	-------	--------------------	---------------

Environmental & Durability Factors

Operating Temperature (°C):	+10 to +35	Storage Temperature (°C):	-10 to +60
-----------------------------	------------	---------------------------	------------

Technical Information

Products

Title	Stock Number	Price	Buy
638nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-754	S\$8,510.78	1 In Stock
785nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-755	S\$8,358.53	1 In Stock
830nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-756	S\$8,663.03	1 In Stock
1064nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-757	S\$9,135.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com