

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#)

Positive Meniscus Lenses



- Positive Meniscus Lens Designs
- Minimize Spherical Aberration and Reduce Spot Sizes
- 350 – 2,200nm Wavelength Range

Common Specifications

Physical & Mechanical Properties

Diameter (mm):	25.40 +0.00/-0.10	Centering (arcmin):	<3
Clear Aperture CA (mm):	22.86		

Optical Properties

Substrate:	N-BK7		
Coating:	Uncoated	Design Wavelength DWL (nm):	587.6
Surface Quality:	40-20	Power (P-V) @ 632.8nm:	3 Rings
Irregularity (P-V) @ 632.8nm:	0.5 Rings		

Technical Information

Products

Title	Stock Number	Price	Buy
25.4mm Dia x 100mm FL, Uncoated Meniscus Lens	#72-430	S\$39.20 Volume Pricing	15 In Stock
25.4mm Dia x 125mm FL, Uncoated Meniscus Lens	#72-431	S\$39.20 Volume Pricing	1 In Stock
25.4mm Dia x 150mm FL, Uncoated Meniscus Lens	#72-432	S\$39.20 Volume Pricing	20+ In Stock
25.4mm Dia x 200mm FL, Uncoated Meniscus Lens	#72-433	S\$39.20 Volume Pricing	20+ In Stock
25.4mm Dia x 300mm FL, Uncoated Meniscus Lens	#72-434	S\$39.20 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com