

4.5" Angle Mirror Mount



4.5" Angle Mirror Mount

Stock **#36-482** **20+ In Stock**

-

1

+

S\$529²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$529.20 each
Qty 5-9	S\$494.48 each
Qty 10-25	S\$470.68 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Adjustable - Tip-Tilt

Type:

Type of Optics:

Square or Rectangular	
	Number of Adjustment Screws:
3	
Physical & Mechanical Properties	
	Weight (lbs):
2.0	
	Construction:
Black Anodized Aluminum, Stainless Steel	
	Fine Tilt Angle (°):
8	
	Resolution (inches):
0.015	
	Fine Tip Angle (°):
8	
	Adjustment Screw Pitch (inches):
0.015	
Threading & Mounting	
	Size of Compatible Optics (mm):
12.7 - 114.3	
	Mounting Plate Size (inches):
4.5 Sq.	
	Mounting Plate Screw Holes:
(49) ¼-20 on 0.5" Center	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 240:
Compliant	

PRODUCT DETAILS

- 3.0", 4.5", or 6.0" Square Mounting Surface
- Fine Adjustment Screws (64-Pitch) Allow for Tilting
- Mounting Plate with ¼-20 Threaded Holes

Medium and Large Angle Mirror Mounts are available with a range of mounting plate sizes for mounting optical mirrors. These optical mirror mounts feature 64-pitch fine adjustment screws, allowing for precision tilting in two directions. Both square and rectangular optics can be mounted into these black anodized aluminum and stainless-steel mounts. Medium and Large Angle Mirror Mounts have two ¼-20 through holes on their angle bases for easy mounting to optical tables or breadboards. These mounts are available in 3", 4.5", and 6" sizes.

TECHNICAL INFORMATION

