

[All Products](#) / [Lasers](#) / [Laser Safety](#) / [Laser Safety Glasses and Goggles](#)

Laser Safety Glasses and Goggles



- CE Certified Laser Radiation Protection
- Designs for Ultraviolet, Visible, and Infrared Lasers
- Available in Goggles, Glasses, or Comfort Glasses Styles

Technical Information

Products

Filter	Optical Density OD (Average)	Visible Light Transmission VLT (%)	Style	Stock Number	Price	Buy
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Adjustable Temples Wrap Around	#12-730	S\$187.05	3 In Stock
LS02	>7 @ 180 - 532nm	48	Adjustable Temples Wrap Around	#12-731	S\$204.45	5 In Stock
#75-528 New						
						
LS02	>7 @ 180 - 532nm	48	Rx Flip Up	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$152.25	1 In Stock

[#75-550 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

LS02	>7 @ 180 - 532nm	48	Vented Fit Over		S\$152.25	4 In Stock
------	---------------------	----	--------------------	--	-----------	------------

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Adjustable Temples Wrap Around	#12-732	S\$348.00 Volume Pricing	5 In Stock
------	---	----	---	-------------------------	---	------------

LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Adjustable Temples Wrap Around	#12-733	S\$261.00	5 In Stock
------	--	----	---	-------------------------	-----------	------------

LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Adjustable Temples Wrap Around	#12-734	S\$308.85	3 In Stock
------	--	----	---	-------------------------	-----------	------------

LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Adjustable Temples Wrap Around	#12-735	S\$339.30	4 In Stock
------	---	----	---	-------------------------	-----------	------------

LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Adjustable Temples Wrap Around	#12-736	S\$261.00	1 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Adjustable Temples Wrap Around	#12-737	S\$290.00	Contact Us
LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Adjustable Temples Wrap Around	#12-738	S\$339.30	2 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Adjustable Temples Wrap Around	#12-739	S\$261.00	1 In Stock

LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Adjustable Temples Wrap Around	#12-740	S\$290.00	1 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Adjustable Temples Wrap Around	#12-741	S\$406.00 Volume Pricing	2 In Stock
LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Adjustable Temples Wrap Around	#12-742	S\$290.00	1 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Adjustable Temples Wrap Around	#12-743	S\$326.25	Contact Us
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Adjustable Temples Wrap Around	#12-744	S\$461.10 Volume Pricing	4 In Stock

LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Adjustable Temples Wrap Around	#12-745	S\$406.00 Volume Pricing	1 In Stock
LS17	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm	75	Adjustable Temples Wrap Around	#12-746	S\$507.50	1 In Stock
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Fit Over Rx Glasses	#12-713	S\$187.05	6 In Stock
LS02	>7 @ 180 - 532nm	48	Fit Over Rx Glasses	#12-714	S\$204.45	2 In Stock
LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Fit Over Rx Glasses	#12-715	S\$348.00 Volume Pricing	3 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Fit Over Rx Glasses	#12-716	S\$275.50	3 In Stock

LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Fit Over Rx Glasses	#12-717	S\$308.85	2 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Fit Over Rx Glasses	#12-718	S\$326.25	2 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Fit Over Rx Glasses	#12-719	S\$261.00	Contact Us
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Fit Over Rx Glasses	#12-720	S\$359.60 Volume Pricing	2 In Stock
LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Fit Over Rx Glasses	#12-721	S\$339.30	3 In Stock

LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Fit Over Rx Glasses	#12-722	S\$261.00	3 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Fit Over Rx Glasses	#12-723	S\$290.00	5 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Fit Over Rx Glasses	#12-724	S\$297.25	1 In Stock
LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Fit Over Rx Glasses	#12-725	S\$290.00	Contact Us

LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Fit Over Rx Glasses	#12-726	S\$326.25	1 In Stock
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Fit Over Rx Glasses	#12-727	S\$461.10 Volume Pricing	Contact Us
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Fit Over Rx Glasses	#12-728	S\$406.00 Volume Pricing	2 In Stock
LS17	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm	75	Fit Over Rx Glasses	#12-729	S\$507.50	3 In Stock
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Goggles	#12-696	S\$187.05	2 In Stock
LS02	>7 @ 180 - 532nm	48	Goggles	#12-697	S\$204.45	3 In Stock

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Goggles	#12-698	S\$348.00 Volume Pricing	2 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Goggles	#12-699	S\$275.50	2 In Stock
LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Goggles	#12-700	S\$308.85	2 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Goggles	#12-701	S\$326.25	1 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Goggles	#12-702	S\$261.00	2 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Goggles	#12-703	S\$290.00	2 In Stock

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Goggles	#12-704	S\$261.00	3 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Goggles	#12-705	S\$261.00	3 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Goggles	#12-706	S\$290.00	Contact Us
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Goggles	#12-707	S\$406.00 Volume Pricing	1 In Stock

LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Goggles	#12-708	S\$290.00	4 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Goggles	#12-709	S\$326.25	1 In Stock
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Goggles	#12-710	S\$461.10 Volume Pricing	Contact Us
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Goggles	#12-711	S\$406.00 Volume Pricing	8 In Stock
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Adjustable Bridge Wrap Around	#18-346	S\$187.05	1 In Stock
LS02	>7 @ 180 - 532nm	48	Adjustable Bridge Wrap Around	#18-347	S\$204.45	1 In Stock

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Adjustable Bridge Wrap Around	#18-348	S\$348.00 Volume Pricing	2 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Adjustable Bridge Wrap Around	#18-349	S\$275.50	4 In Stock
LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Adjustable Bridge Wrap Around	#18-350	S\$308.85	2 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Adjustable Bridge Wrap Around	#18-351	S\$336.40	3 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Adjustable Bridge Wrap Around	#18-352	S\$261.00	1 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Adjustable Bridge Wrap Around	#18-353	S\$290.00	3 In Stock

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Adjustable Bridge Wrap Around	#18-354	S\$339.30	1 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Adjustable Bridge Wrap Around	#18-355	S\$290.00	1 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Adjustable Bridge Wrap Around	#18-356	S\$290.00	3 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Adjustable Bridge Wrap Around	#18-357	S\$384.25 Volume Pricing	3 In Stock

LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Adjustable Bridge Wrap Around	#18-358	S\$290.00	2 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Adjustable Bridge Wrap Around	#18-359	S\$326.25	Contact Us
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Adjustable Bridge Wrap Around	#18-360	S\$461.10 Volume Pricing	5 In Stock
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Adjustable Bridge Wrap Around	#18-361	S\$406.00 Volume Pricing	4 In Stock

[#75-523 New](#)



LS17 and LS02	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm >7 @ 180 - 532nm	75 and 48	1 + 1 Flip Up	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$558.25	1 In Stock
---------------------	---	-----------	------------------	---	-----------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Adjustable Temples Wrap Around	#17-641	S\$362.50	1 In Stock
------	---	----	---	-------------------------	-----------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Fit Over Rx Glasses	#17-645	S\$362.50	3 In Stock
------	---	----	---------------------------	-------------------------	-----------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Adjustable Bridge Wrap Around	#17-649	S\$362.50	3 In Stock
------	---	----	--	-------------------------	-----------	------------

LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Adjustable Temples Wrap Around	#17-639	S\$394.40 Volume Pricing	1 In Stock
------	--	----	---	-------------------------	---	------------

LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Fit Over Rx Glasses	#17-643	S\$394.40 Volume Pricing	2 In Stock
------	--	----	---------------------------	-------------------------	---	------------

LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Adjustable Bridge Wrap Around	#17-647	S\$394.40 Volume Pricing	1 In Stock
LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Adjustable Temples Wrap Around	#17-640	S\$420.50	Contact Us

LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Fit Over Rx Glasses	#17-644	S\$420.50	5 In Stock
LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Adjustable Bridge Wrap Around	#17-648	S\$420.50	2 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Adjustable Temples Wrap Around	#17-642	S\$326.25	3 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Fit Over Rx Glasses	#17-646	S\$319.00	1 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Adjustable Bridge Wrap Around	#17-650	S\$326.25	4 In Stock

[#74-518 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Vented Adjustable Temples		S\$121.80 Volume Pricing	2 In Stock
------	---	----	---------------------------------	--	---	------------

[#74-512 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

LS02	>7 @ 180 - 532nm	48	Vented Adjustable Temples		S\$134.85 Volume Pricing	7 In Stock
------	---------------------	----	---------------------------------	--	---	------------

[#74-522 New](#)



LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$211.70 Volume Pricing	2 In Stock
------	--	----	---------------------------------	---	---	------------

[#90-857 New](#)



LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$261.00	2 In Stock
------	---	----	---------------------------------	---	-----------	------------

[#90-864 New](#)



New

LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Vented Adjustable Temples	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$275.50	2 In Stock
------	---	----	---------------------------------	--	-----------	------------

[#74-526 New](#)



New

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Vented Adjustable Temples	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$232.00 Volume Pricing	1 In Stock
------	--	----	---------------------------------	--	---	------------

[#90-867 New](#)

LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Vented Adjustable Temples	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$253.75	2 In Stock
------	--	----	---------------------------	--	-----------	------------

[#90-868 New](#)

LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Vented Adjustable Temples	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$297.25	2 In Stock
------	--	----	---------------------------	--	-----------	------------

[#74-527 New](#)



LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$232.00 Volume Pricing	1 In Stock
------	---	----	---------------------------------	---	---	------------

[#74-521 New](#)



LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$290.00 Volume Pricing	1 In Stock
------	--	----	---------------------------------	---	---	------------

LS19	>5 @	23	Vented Adjustable Temples	#90-873 New  New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$304.50	2 In Stock
	1025 -					
	1075nm					
	>6 @					
	1035 -					
	1070nm					
	>7 @					
	1045 -					
	1065nm					
	>2 @					
	1450 -					
	1650nm					
	>3 @					
	1651 -					
	1775nm					
	>4 @					
	1776 -					
	3000nm					
	>5 @					
	1980 -					
	2550nm					
	>5 @					
	5200 -					
	11,000nm					
	>6 @					
	9000 -					
	10,600nm					

[#90-832 New](#)

LS01	>7 @ 190	93	Vented Fit Over	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$137.75	2 In Stock
	- 398nm					
	>7 @					
	9000 -					
	11,000nm					

[#90-833 New](#)



New

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$268.25	2 In Stock
------	---	----	--------------------	--	-----------	------------

[#90-834 New](#)



New

LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$239.25	Contact Us
------	--	----	--------------------	--	-----------	------------

[#90-835 New](#)



LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$239.25	2 In Stock
------	--	----	--------------------	---	-----------	------------

[#90-836 New](#)



LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$261.00	2 In Stock
------	---	----	--------------------	---	-----------	------------

[#90-838 New](#)



LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$261.00	2 In Stock
------	---	----	--------------------	---	-----------	------------

[#90-839 New](#)



LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$275.50	2 In Stock
------	---	----	--------------------	---	-----------	------------

[#90-841 New](#)



LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$261.00	2 In Stock
------	--	----	--------------------	---	-----------	------------

[#90-843 New](#)



LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$253.75	2 In Stock
------	---	----	--------------------	---	-----------	------------

[#90-844 New](#)



New

LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$290.00	2 In Stock
------	---	----	--------------------	--	-----------	------------

[#90-845 New](#)



New

LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$297.25	2 In Stock
------	---	----	--------------------	--	-----------	------------

[#90-847 New](#)



LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$261.00	2 In Stock
------	---	----	--------------------	---	-----------	------------

[#90-848 New](#)



LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$326.25	1 In Stock
------	--	----	--------------------	---	-----------	------------

[#90-851 New](#)



LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$348.00	1 In Stock
------	--	----	--------------------	---	-----------	------------

[#90-852 New](#)



LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$297.25	Contact Us
------	---	----	--------------------	---	-----------	------------

[#90-853 New](#)



LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$362.50	Contact Us
------	---	----	--------------------	---	-----------	------------

[#90-854 New](#)



LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	S\$304.50	2 In Stock
------	--	----	--------------------	---	-----------	------------

[#90-855 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

S\$420.50

Contact Us

>8 @ 190
- 532nm
>5 @ 730
- 1110nm
>7 @ 745
- 1100nm
>9 @ 753
- 765nm
>10 @
765 -
880 -

LS20

13

Vented Fit
Over



>10 @
1065nm

Copyright 2021, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com

[#90-856 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

S\$282.75

1 In Stock

>6 @ 180
- 400nm
>5 @ 720
- 1090nm
>7 @ 750
- 1064nm

LS21

25

Vented Fit
Over