

[All Products](#) / [Optics](#) / [SCHOTT Optical Components](#)

SCHOTT Colored Glass Longpass Filters See More by [SCHOTT Optical Components](#)





- 27 Standard SCHOTT Color Glass Types
- Cut-On Wavelengths in the UV, Visible, or NIR
- Standard Circular and Square Sizes with 1, 2, or 3mm Thickness


Common Specifications
Optical Properties

Coating:	Uncoated
----------	----------

Technical Information



SCHOTT IR Longpass Filters



Products

Dimensions (mm)	Dia. (mm)	Glass/Filter Number	Cut-On Wavelength (nm)	Thickness (mm)	Stock Number	Price	Buy
-	12.50	SCHOTT WG280	280.00	1.00	#16-403	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT WG280	280.00	2.00	#16-430	S\$51.80 Volume Pricing	7 In Stock
-	12.50	SCHOTT WG280	285.00	3.00	#64-509	S\$51.80 Volume Pricing	9 In Stock
-	25.40	SCHOTT WG280	285.00	3.00	#64-510	S\$64.40 Volume Pricing	5 In Stock
-	50.00	SCHOTT WG280	285.00	3.00	#66-071	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT WG280	280.00	1.00	#14-460	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT WG280	280.00	2.00	#14-461	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT WG280	280.00	3.00	#14-462	S\$129.50 Volume Pricing	9 In Stock
#64-511 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
50.8 x 50.8	-	SCHOTT WG280	285.00	3.00		S\$83.30	3 In Stock
-	12.50	SCHOTT WG295	295.00	1.00	#16-404	S\$51.80 Volume Pricing	2 In Stock
-	12.50	SCHOTT WG295	295.00	2.00	#16-431	S\$51.80 Volume Pricing	5 In Stock

-	12.50	SCHOTT WG295	300.00	3.00	#46-416	S\$51.80 Volume Pricing	2 In Stock
-	25.40	SCHOTT WG295	300.00	3.00	#46-417	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT WG295	300.00	3.00	#66-072	S\$147.00 Volume Pricing	6 In Stock
50.0 x 50.0	-	SCHOTT WG295	295.00	1.00	#14-463	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT WG295	295.00	2.00	#14-464	S\$129.50 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT WG295	295.00	3.00	#14-465	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT WG305	305.00	1.00	#16-405	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT WG305	305.00	2.00	#16-432	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT WG305	309.00	3.00	#54-646	S\$51.80 Volume Pricing	13 In Stock
-	25.40	SCHOTT WG305	309.00	3.00	#45-066	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT WG305	309.00	3.00	#66-073	S\$147.00 Volume Pricing	11 In Stock
50.0 x 50.0	-	SCHOTT WG305	305.00	1.00	#14-466	S\$129.50 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT WG305	305.00	2.00	#14-467	S\$129.50 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT WG305	305.00	3.00	#14-468	S\$129.50 Volume Pricing	6 In Stock
-	12.50	SCHOTT WG320	320.00	1.00	#16-406	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT WG320	320.00	2.00	#16-433	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT WG320	320.00	3.00	#46-419	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT WG320	320.00	3.00	#46-420	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT WG320	320.00	3.00	#66-074	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT WG320	320.00	1.00	#14-469	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT WG320	320.00	2.00	#14-470	S\$129.50 Volume Pricing	8 In Stock

50.0 x 50.0	-	SCHOTT WG320	320.00	3.00	#14-471	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT GG395	395.00	1.00	#16-407	S\$51.80 Volume Pricing	3 In Stock
-	12.50	SCHOTT GG395	395.00	2.00	#16-434	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT GG395	395.00	3.00	#54-648	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT GG395	395.00	3.00	#46-055	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT GG395	395.00	3.00	#66-077	S\$147.00 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT GG395	395.00	1.00	#14-472	S\$129.50 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG395	395.00	2.00	#14-473	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT GG395	395.00	3.00	#14-474	S\$129.50 Volume Pricing	8 In Stock
50.8 x 50.8	-	SCHOTT GG395	395.00	3.00	#46-056	S\$147.00 Volume Pricing	Contact Us
-	12.50	SCHOTT GG400	400.00	1.00	#16-408	S\$51.80 Volume Pricing	7 In Stock
-	12.50	SCHOTT GG400	400.00	2.00	#16-435	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT GG400	400.00	3.00	#46-422	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT GG400	400.00	3.00	#46-423	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT GG400	400.00	3.00	#66-078	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG400	400.00	1.00	#14-475	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT GG400	400.00	2.00	#14-476	S\$129.50 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG400	400.00	3.00	#14-477	S\$129.50 Volume Pricing	15 In Stock
-	12.50	SCHOTT GG420	420.00	1.00	#16-409	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT GG420	420.00	2.00	#16-436	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT GG420	420.00	3.00	#46-425	S\$51.80 Volume Pricing	20+ In Stock

-	25.40	SCHOTT GG420	420.00	3.00	#46-426	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT GG420	420.00	3.00	#66-079	S\$147.00 Volume Pricing	16 In Stock
50.0 x 50.0	-	SCHOTT GG420	420.00	1.00	#14-478	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT GG420	420.00	2.00	#14-479	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT GG420	420.00	3.00	#14-480	S\$129.50 Volume Pricing	7 In Stock
50.8 x 50.8	-	SCHOTT GG420	420.00	3.00	#46-427	S\$147.00 Volume Pricing	20+ In Stock
-	12.50	SCHOTT GG435	435.00	1.00	#16-410	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT GG435	435.00	2.00	#16-437	S\$51.80 Volume Pricing	1 In Stock
-	12.50	SCHOTT GG435	435.00	3.00	#54-649	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT GG435	435.00	3.00	#32-752	S\$64.40 Volume Pricing	12 In Stock
-	50.00	SCHOTT GG435	435.00	3.00	#66-080	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG435	435.00	1.00	#14-481	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT GG435	435.00	2.00	#14-482	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT GG435	435.00	3.00	#14-483	S\$129.50 Volume Pricing	7 In Stock
50.8 x 50.8	-	SCHOTT GG435	435.00	3.00	#32-762	S\$147.00 Volume Pricing	20+ In Stock
-	12.50	SCHOTT GG455	455.00	1.00	#16-411	S\$51.80 Volume Pricing	1 In Stock
-	12.50	SCHOTT GG455	455.00	2.00	#16-438	S\$51.80 Volume Pricing	20+ In Stock
-	12.50	SCHOTT GG455	455.00	3.00	#54-650	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT GG455	455.00	3.00	#45-068	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT GG455	455.00	3.00	#66-081	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG455	455.00	1.00	#14-484	S\$129.50 Volume Pricing	8 In Stock

50.0 x 50.0	-	SCHOTT GG455	455.00	2.00	#14-485	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT GG455	455.00	3.00	#14-486	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT GG475	475.00	1.00	#16-412	S\$51.80 Volume Pricing	8 In Stock
-	12.50	SCHOTT GG475	475.00	2.00	#16-439	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT GG475	475.00	3.00	#54-651	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT GG475	475.00	3.00	#46-057	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT GG475	475.00	3.00	#66-082	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG475	475.00	1.00	#14-487	S\$129.50 Volume Pricing	13 In Stock
50.0 x 50.0	-	SCHOTT GG475	475.00	2.00	#14-488	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT GG475	475.00	3.00	#14-489	S\$129.50 Volume Pricing	16 In Stock
-	12.50	SCHOTT GG495	495.00	1.00	#16-413	S\$51.80 Volume Pricing	20+ In Stock
-	12.50	SCHOTT GG495	495.00	2.00	#16-440	S\$51.80 Volume Pricing	20+ In Stock
-	12.50	SCHOTT GG495	495.00	3.00	#54-652	S\$51.80 Volume Pricing	3 In Stock
-	25.40	SCHOTT GG495	495.00	3.00	#32-753	S\$64.40 Volume Pricing	17 In Stock
-	50.00	SCHOTT GG495	495.00	3.00	#66-083	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT GG495	495.00	1.00	#14-490	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT GG495	495.00	2.00	#14-491	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT GG495	495.00	3.00	#14-492	S\$129.50 Volume Pricing	11 In Stock
-	12.50	SCHOTT OG515	515.00	1.00	#16-414	S\$51.80 Volume Pricing	11 In Stock
-	12.50	SCHOTT OG515	515.00	2.00	#16-441	S\$51.80 Volume Pricing	8 In Stock
-	12.50	SCHOTT OG515	515.00	3.00	#54-653	S\$51.80 Volume Pricing	20+ In Stock

-	25.40	SCHOTT OG515	515.00	3.00	#45-069	S\$64.40 Volume Pricing	16 In Stock
-	50.00	SCHOTT OG515	515.00	3.00	#66-085	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT OG515	515.00	1.00	#14-493	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT OG515	515.00	2.00	#14-494	S\$129.50 Volume Pricing	6 In Stock
50.0 x 50.0	-	SCHOTT OG515	515.00	3.00	#14-495	S\$129.50 Volume Pricing	8 In Stock
-	12.50	SCHOTT OG530	530.00	1.00	#16-415	S\$51.80 Volume Pricing	8 In Stock
-	12.50	SCHOTT OG530	530.00	2.00	#16-442	S\$51.80 Volume Pricing	8 In Stock
-	12.50	SCHOTT OG530	530.00	3.00	#54-654	S\$51.80 Volume Pricing	2 In Stock
-	25.40	SCHOTT OG530	530.00	3.00	#46-059	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT OG530	530.00	3.00	#66-086	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT OG530	530.00	1.00	#14-496	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT OG530	530.00	2.00	#14-497	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT OG530	530.00	3.00	#14-498	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT OG550	550.00	1.00	#16-416	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT OG550	550.00	2.00	#16-443	S\$51.80 Volume Pricing	7 In Stock
-	12.50	SCHOTT OG550	550.00	3.00	#54-655	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT OG550	550.00	3.00	#32-754	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT OG550	550.00	3.00	#66-088	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT OG550	550.00	1.00	#14-499	S\$129.50 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT OG550	550.00	2.00	#14-500	S\$129.50 Volume Pricing	15 In Stock
50.0 x 50.0	-	SCHOTT OG550	550.00	3.00	#14-502	S\$129.50 Volume Pricing	9 In Stock

-	12.50	SCHOTT OG570	570.00	1.00	#16-417	S\$51.80 Volume Pricing	1 In Stock
-	12.50	SCHOTT OG570	570.00	2.00	#16-444	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT OG570	570.00	3.00	#54-656	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT OG570	570.00	3.00	#46-061	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT OG570	570.00	3.00	#66-090	S\$147.00 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT OG570	570.00	1.00	#14-505	S\$129.50 Volume Pricing	14 In Stock
50.0 x 50.0	-	SCHOTT OG570	570.00	2.00	#14-506	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT OG570	570.00	3.00	#14-507	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT OG590	590.00	1.00	#16-418	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT OG590	590.00	2.00	#16-445	S\$51.80 Volume Pricing	10 In Stock
-	12.50	SCHOTT OG590	590.00	3.00	#54-657	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT OG590	590.00	3.00	#46-063	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT OG590	590.00	3.00	#66-092	S\$147.00 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT OG590	590.00	1.00	#14-508	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT OG590	590.00	2.00	#14-509	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT OG590	590.00	3.00	#14-510	S\$129.50 Volume Pricing	6 In Stock
50.8 x 50.8	-	SCHOTT OG590	590.00	3.00	#46-064	S\$147.00 Volume Pricing	20+ In Stock
-	12.50	SCHOTT RG610	610.00	1.00	#16-419	S\$51.80 Volume Pricing	2 In Stock
-	12.50	SCHOTT RG610	610.00	2.00	#16-446	S\$51.80 Volume Pricing	4 In Stock
-	12.50	SCHOTT RG610	610.00	3.00	#46-428	S\$51.80 Volume Pricing	16 In Stock
-	25.40	SCHOTT RG610	610.00	3.00	#46-429	S\$64.40 Volume Pricing	20+ In Stock

-	50.00	SCHOTT RG610	610.00	3.00	#66-094	S\$147.00 Volume Pricing	2 In Stock
50.0 x 50.0	-	SCHOTT RG610	610.00	1.00	#14-511	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT RG610	610.00	2.00	#14-512	S\$129.50 Volume Pricing	12 In Stock
50.0 x 50.0	-	SCHOTT RG610	610.00	3.00	#14-513	S\$129.50 Volume Pricing	16 In Stock
-	12.50	SCHOTT RG630	630.00	1.00	#16-420	S\$51.80 Volume Pricing	1 In Stock
-	12.50	SCHOTT RG630	630.00	2.00	#16-447	S\$51.80 Volume Pricing	9 In Stock
-	12.50	SCHOTT RG630	630.00	3.00	#54-658	S\$51.80 Volume Pricing	13 In Stock
-	25.40	SCHOTT RG630	630.00	3.00	#32-755	S\$46.20 Volume Pricing	8 In Stock
-	50.00	SCHOTT RG630	630.00	3.00	#66-096	S\$147.00 Volume Pricing	13 In Stock
50.0 x 50.0	-	SCHOTT RG630	630.00	1.00	#14-514	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT RG630	630.00	2.00	#14-515	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT RG630	630.00	3.00	#14-516	S\$129.50 Volume Pricing	1 In Stock
-	12.50	SCHOTT RG645	645.00	1.00	#16-421	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT RG645	645.00	2.00	#16-448	S\$51.80 Volume Pricing	20+ In Stock
-	12.50	SCHOTT RG645	645.00	3.00	#64-512	S\$51.80 Volume Pricing	5 In Stock
-	25.40	SCHOTT RG645	645.00	3.00	#64-513	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG645	645.00	3.00	#66-097	S\$147.00 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT RG645	645.00	1.00	#14-517	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT RG645	645.00	2.00	#14-518	S\$129.50 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT RG645	645.00	3.00	#14-519	S\$129.50 Volume Pricing	12 In Stock

[#64-514 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.8 x 50.8

-

SCHOTT
RG645

645.00

3.00

S\$83.30

Contact Us

-	12.50	SCHOTT RG665	665.00	1.00	#16-422	S\$51.80 Volume Pricing	3 In Stock
-	12.50	SCHOTT RG665	665.00	2.00	#16-449	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT RG665	665.00	3.00	#54-659	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT RG665	665.00	3.00	#45-070	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG665	665.00	3.00	#66-099	S\$147.00 Volume Pricing	5 In Stock
50.0 x 50.0	-	SCHOTT RG665	665.00	1.00	#14-520	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT RG665	665.00	2.00	#14-521	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT RG665	665.00	3.00	#14-522	S\$129.50 Volume Pricing	6 In Stock
-	12.50	SCHOTT RG695	695.00	1.00	#16-423	S\$51.80 Volume Pricing	10 In Stock
-	12.50	SCHOTT RG695	695.00	2.00	#16-450	S\$51.80 Volume Pricing	6 In Stock
-	12.50	SCHOTT RG695	695.00	3.00	#54-660	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT RG695	695.00	3.00	#32-756	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG695	695.00	3.00	#66-100	S\$147.00 Volume Pricing	17 In Stock

50.0 x 50.0	-	SCHOTT RG695	695.00	1.00	#14-523	S\$129.50 Volume Pricing	13 In Stock
50.0 x 50.0	-	SCHOTT RG695	695.00	2.00	#14-524	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT RG695	695.00	3.00	#14-525	S\$129.50 Volume Pricing	9 In Stock
-	12.50	SCHOTT RG715	715.00	1.00	#16-424	S\$51.80 Volume Pricing	Contact Us
-	12.50	SCHOTT RG715	715.00	2.00	#16-451	S\$51.80 Volume Pricing	7 In Stock
-	12.50	SCHOTT RG715	715.00	3.00	#54-661	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT RG715	715.00	3.00	#46-065	S\$73.50 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG715	715.00	3.00	#66-101	S\$147.00 Volume Pricing	17 In Stock
50.0 x 50.0	-	SCHOTT RG715	715.00	1.00	#14-526	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT RG715	715.00	2.00	#14-527	S\$129.50 Volume Pricing	7 In Stock
50.0 x 50.0	-	SCHOTT RG715	715.00	3.00	#14-528	S\$129.50 Volume Pricing	20+ In Stock
-	12.50	SCHOTT RG9	726.00	1.00	#16-425	S\$51.80 Volume Pricing	3 In Stock
-	12.50	SCHOTT RG9	726.00	2.00	#16-452	S\$51.80 Volume Pricing	15 In Stock
-	12.50	SCHOTT RG9	726.00	3.00	#16-457	S\$51.80 Volume Pricing	8 In Stock
-	25.40	SCHOTT RG9	726.00	3.00	#84-903	S\$49.00 Volume Pricing	10 In Stock
-	50.00	SCHOTT RG9	726.00	3.00	#16-458	S\$147.00 Volume Pricing	12 In Stock
50.0 x 50.0	-	SCHOTT RG9	726.00	1.00	#14-529	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT RG9	726.00	2.00	#14-530	S\$129.50 Volume Pricing	9 In Stock
50.0 x 50.0	-	SCHOTT RG9	726.00	3.00	#14-531	S\$129.50 Volume Pricing	10 In Stock
-	12.50	SCHOTT RG780	780.00	1.00	#16-426	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT RG780	780.00	2.00	#16-453	S\$51.80 Volume Pricing	16 In Stock

-	12.50	SCHOTT RG780	780.00	3.00	#54-662	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT RG780	780.00	3.00	#32-757	S\$73.50 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG780	780.00	3.00	#66-104	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT RG780	780.00	1.00	#14-532	S\$129.50 Volume Pricing	10 In Stock
50.0 x 50.0	-	SCHOTT RG780	780.00	2.00	#14-533	S\$129.50 Volume Pricing	6 In Stock
50.0 x 50.0	-	SCHOTT RG780	780.00	3.00	#14-534	S\$129.50 Volume Pricing	6 In Stock
50.8 x 50.8	-	SCHOTT RG780	780.00	3.00	#32-767	S\$147.00 Volume Pricing	20+ In Stock
-	12.50	SCHOTT RG830	830.00	1.00	#16-427	S\$51.80 Volume Pricing	3 In Stock
-	12.50	SCHOTT RG830	830.00	2.00	#16-454	S\$51.80 Volume Pricing	5 In Stock
-	12.50	SCHOTT RG830	830.00	3.00	#54-663	S\$51.80 Volume Pricing	20+ In Stock
-	25.40	SCHOTT RG830	830.00	3.00	#32-758	S\$46.20 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG830	830.00	3.00	#66-106	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT RG830	830.00	1.00	#14-535	S\$129.50 Volume Pricing	13 In Stock
50.0 x 50.0	-	SCHOTT RG830	830.00	2.00	#14-536	S\$129.50 Volume Pricing	13 In Stock
50.0 x 50.0	-	SCHOTT RG830	830.00	3.00	#14-537	S\$129.50 Volume Pricing	7 In Stock
-	12.50	SCHOTT RG850	850.00	1.00	#16-428	S\$51.80 Volume Pricing	9 In Stock
-	12.50	SCHOTT RG850	850.00	2.00	#16-455	S\$51.80 Volume Pricing	10 In Stock
-	12.50	SCHOTT RG850	850.00	3.00	#54-664	S\$51.80 Volume Pricing	Contact Us
-	25.40	SCHOTT RG850	850.00	3.00	#32-759	S\$91.00 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG850	850.00	3.00	#66-107	S\$147.00 Volume Pricing	20+ In Stock
50.0 x 50.0	-	SCHOTT RG850	850.00	1.00	#14-538	S\$133.00 Volume Pricing	8 In Stock

50.0 x 50.0	-	SCHOTT RG850	850.00	2.00	#14-539	S\$133.00 Volume Pricing	12 In Stock
50.0 x 50.0	-	SCHOTT RG850	850.00	3.00	#14-540	S\$133.00 Volume Pricing	9 In Stock
-	12.50	SCHOTT RG1000	1,000.00	1.00	#16-429	S\$51.80 Volume Pricing	13 In Stock
-	12.50	SCHOTT RG1000	1,000.00	2.00	#16-456	S\$51.80 Volume Pricing	9 In Stock
-	12.50	SCHOTT RG1000	1,000.00	3.00	#54-665	S\$51.80 Volume Pricing	16 In Stock
-	25.40	SCHOTT RG1000	1,000.00	3.00	#32-760	S\$64.40 Volume Pricing	20+ In Stock
-	50.00	SCHOTT RG1000	1,000.00	3.00	#66-108	S\$147.00 Volume Pricing	3 In Stock
50.0 x 50.0	-	SCHOTT RG1000	1,000.00	1.00	#14-541	S\$129.50 Volume Pricing	11 In Stock
50.0 x 50.0	-	SCHOTT RG1000	1,000.00	2.00	#14-542	S\$129.50 Volume Pricing	8 In Stock
50.0 x 50.0	-	SCHOTT RG1000	1,000.00	3.00	#14-543	S\$129.50 Volume Pricing	8 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com