


[All Products](#) / [Optics](#) / [Fiber Optics](#)

Optical Grade Fiber Optics



- Superior Light Transmission
- ESKA® Fiber Strands
- Step Index

Common Specifications

Physical & Mechanical Properties


Length (ft):	Cut to Order, Minimum 10	Diameter Tolerance (%):	± 6
Optical Properties			
Substrate:	Acrylic	Index of Refraction (n_d) - Cladding:	1.402
Attenuation (dB/km):	150 - 300 (@ 650nm)	Numerical Aperture (NA) Tolerance:	± 0.03

Environmental & Durability Factors


Operating Temperature (°C):	-55 to +70
------------------------------------	------------


Technical Information

Optical Grade (Typical)



Optical Grade (Typical)





Products

Title	Stock Number	Price	Buy
250µm with 1 Fiber, Optical Grade Plastic Light Guide	#57-096	S\$2.45	20+ In Stock
265µm with 16 Fiber, Optical Grade Plastic Light Guide	#02-537	S\$4.20	20+ In Stock
265µm with 64 Fiber, Optical Grade Plastic Light Guide	#02-540	S\$5.25	20+ In Stock
500µm with 1 Fiber, Optical Grade Plastic Light Guide	#57-097	S\$3.15	20+ In Stock
1000µm with 1 Fiber, Optical Grade Plastic Light Guide	#02-536	S\$5.60	20+ In Stock
1500µm with 1 Fiber, Optical Grade Plastic Light Guide	#02-550	S\$5.95	20+ In Stock
2000µm with 1 Fiber, Optical Grade Plastic Light Guide	#02-551	S\$7.70	20+ In Stock
250µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-531	S\$1.40	20+ In Stock
500µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-532	S\$2.10	20+ In Stock
750µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-533	S\$2.45	20+ In Stock
1000µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-534	S\$2.80	Contact Us
1500µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-535	S\$3.85	20+ In Stock
2000µm, Optical Grade Plastic Optical Fiber Unjacketed	#02-549	S\$5.60	20+ In Stock
3000µm, Optical Grade Plastic Optical Fiber Unjacketed	#53-833	S\$6.65	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com