

[All Products](#) / [Optics](#) / [Prisms](#) / [Specialty Prisms](#)

TECHSPEC® 45° Rod Mirrors




- Protected Aluminum Coating
- Reflect Light at 90°

Common Specifications

General			
Note:		Coating on Elliptical Surface	
Physical & Mechanical Properties			
Bevel:		Protective as needed	
Length Tolerance (mm):		±0.1	
Optical Properties			
Coating:		Protected Aluminum (400-700nm)	
Substrate:		N-BK7	Surface Quality: 40-20
Angle Tolerance (arcmin):		±10	Ray Deviation (°): 90
Wavelength Range (nm):		400 - 700	Coating Type: Metal
Damage Threshold, By Design:		0.3 J/cm ² @ 532nm & 1064nm, 10ns	

Technical Information



Products

Length (mm)	Coating	Dia. (mm)	Ray Deviation (°)	Stock Number	Price	Buy
2.00	Protected Aluminum (400- 700nm)	1.00	90	#47-628	S\$228.20 Volume Pricing	20+ In Stock
4.00	Protected Aluminum (400- 700nm)	2.00	90	#54-092	S\$169.40 Volume Pricing	20+ In Stock
6.00	Protected Aluminum (400- 700nm)	3.00	90	#54-094	S\$169.40 Volume Pricing	20+ In Stock
8.00	Protected Aluminum (400- 700nm)	4.00	90	#54-096	S\$198.80 Volume Pricing	20+ In Stock
10.00	Protected Aluminum (400- 700nm)	5.00	90	#54-098	S\$203.00 Volume Pricing	Contact Us
12.00	Protected Aluminum (400- 700nm)	6.00	90	#49-399	S\$211.40 Volume Pricing	Contact Us
16.00	Protected Aluminum (400- 700nm)	8.00	90	#49-400	S\$217.00 Volume Pricing	10 In Stock
15.00	Protected Aluminum (400- 700nm)	10.00	90	#45-944	S\$221.20 Volume Pricing	Contact Us
20.00	Protected Aluminum (400- 700nm)	12.00	90	#45-945	S\$242.20 Volume Pricing	20+ In Stock
30.00	Protected Aluminum (400- 700nm)	15.00	90	#49-401	S\$254.80 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com