

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC[®]

Mounted Achromatic Lens Pairs



- 15mm and 30mm Diameter Options
- AR Coated Lenses
- Mounted Achromatic Pairs Kits Available

Common Specifications



Physical & Mechanical Properties

Construction:	Achromat Pair in Anodized Aluminum Housing
---------------	--

Optical Properties

Surface Quality:	40-20	Coating Specification: $R_{avg} \leq 1.75\%$ @ 400 - 700nm
Coating:	MgF ₂ (400-700nm)	
Wavelength Range (nm):	400 - 700	

Technical Information



Products

Substrate	Coating	EFL A (mm)	EFL B (mm)	Housing Diameter (mm)	Magnification	Stock Number	Price	Buy
N-BAF10 / N-SF5 / N-BAF10 / N-SF5	MgF ₂ (400-700nm)	14.00	14.00	15	1:1	#43-992	S\$292.60 Volume Pricing	5 In Stock
N-BAF10 / N-SF5 / S-BAH11 / N-SF10	MgF ₂ (400-700nm)	14.00	20.00	15	1:1.43	#43-993	S\$292.60 Volume Pricing	3 In Stock
N-BAF10 / N-SF5 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	14.00	25.00	15	1:1.78	#43-994	S\$292.60 Volume Pricing	3 In Stock
N-BAF10 / N-SF5 / N-SSK8 / N-SF10	MgF ₂ (400-700nm)	14.00	30.00	15	1:2.14	#43-995	S\$283.77 Volume Pricing	4 In Stock
S-BAH11 / N-SF10 / S-BAH11 / N-SF10	MgF ₂ (400-700nm)	20.00	20.00	15	1:1	#55-270	S\$292.60 Volume Pricing	Contact Us
S-BAH11 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	20.00	25.00	15	1:1.25	#43-996	S\$292.60 Volume Pricing	10 In Stock
S-BAH11 / N-SF10 / N-SSK8 / N-SF10	MgF ₂ (400-700nm)	20.00	30.00	15	1:1.5	#43-997	S\$292.60 Volume Pricing	8 In Stock
N-BAF10 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	25.00	25.00	15	1:1	#55-271	S\$283.77 Volume Pricing	2 In Stock
N-BAF10 / N-SF10 / N-SSK8 / N-SF10	MgF ₂ (400-700nm)	25.00	30.00	15	1:1.2	#43-998	S\$292.60 Volume Pricing	3 In Stock
N-BAF10 / N-SF10 / N-SK11 / N-SF5	MgF ₂ (400-700nm)	25.00	35.00	15	1:1.4	#55-273	S\$283.77 Volume Pricing	4 In Stock
N-SSK8 / N-SF10 / N-SSK8 / N-SF10	MgF ₂ (400-700nm)	30.00	30.00	15	1:1	#43-999	S\$292.60 Volume Pricing	1 In Stock

N-SSK8 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	30.00	40.00	15	1:1.33	#55-274	S\$292.60 Volume Pricing	2 In Stock
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	40.00	40.00	15	1:1	#46-000	S\$283.77 Volume Pricing	Contact Us
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	40.00	50.00	15	1:1.25	#55-275	S\$292.60 Volume Pricing	Contact Us
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	40.00	60.00	15	1:1.5	#46-001	S\$292.60 Volume Pricing	2 In Stock
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	50.00	50.00	15	1:1	#55-272	S\$292.60 Volume Pricing	9 In Stock
N-BAF10 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	30.00	30.00	30	1:1	#46-002	S\$369.60 Volume Pricing	Contact Us
N-BAF10 / N-SF10 / S-BAH11 / N-SF10	MgF ₂ (400-700nm)	30.00	40.00	30	1:1.33	#46-003	S\$369.60 Volume Pricing	1 In Stock
N-BAF10 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	30.00	50.00	30	1:1.67	#46-004	S\$369.60 Volume Pricing	Contact Us
N-BAF10 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	30.00	75.00	30	1:2.50	#46-005	S\$369.60 Volume Pricing	Contact Us
N-BAF10 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	30.00	100.00	30	1:3.33	#46-006	S\$369.60 Volume Pricing	Contact Us
S-BAH11 / N-SF10 / S-BAH11 / N-SF10	MgF ₂ (400-700nm)	40.00	40.00	30	1:1	#46-007	S\$369.60 Volume Pricing	1 In Stock
S-BAH11 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	40.00	50.00	30	1:1.25	#46-008	S\$369.60 Volume Pricing	1 In Stock

S-BAH11 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	40.00	75.00	30	1:1.88	#46-009	S\$369.60 Volume Pricing	Contact Us
S-BAH11 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	40.00	100.00	30	1:2.50	#46-010	S\$369.60 Volume Pricing	1 In Stock
N-BAF10 / N-SF10 / N-BAF10 / N-SF10	MgF ₂ (400-700nm)	50.00	50.00	30	1:1	#46-011	S\$369.60 Volume Pricing	Contact Us
N-BAF10 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	50.00	75.00	30	1:1.50	#46-012	S\$369.60 Volume Pricing	1 In Stock
N-SSK8 / N-SF10 / N-SSK8 / N-SF10	MgF ₂ (400-700nm)	60.00	60.00	30	1:1	#55-276	S\$369.60 Volume Pricing	2 In Stock
N-SSK8 / N-SF10 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	60.00	75.00	30	1:1.25	#55-279	S\$369.60 Volume Pricing	1 In Stock
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	75.00	75.00	30	1:1	#55-277	S\$369.60 Volume Pricing	3 In Stock
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	75.00	100.00	30	1:1.33	#55-280	S\$352.47 Volume Pricing	1 In Stock
N-BK7 / N-SF5 / N-BK7 / N-SF5	MgF ₂ (400-700nm)	100.00	100.00	30	1:1	#55-278	S\$369.60 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com