

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® Achromatic Lens Kits



- Kits Available for 12.5mm and 25mm Diameter Lenses
- MgF₂, VIS 0°, and VIS-NIR Coating Options
- Compatible with [Tube](#) and [Optical Cage System](#) Mechanics
- Note: Potential change of packaging

Common Specifications

General

Contents of Kit:


Achromatic Lens Kit

Technical Information

VIS 0° Coating

$R_{avg} \leq 0.4\%$ @ 425-675nm


Typ. Energy Density Limit: 5 J/cm² @ 532nm, 10ns



VIS-NIR Coating

$R_{avg} \leq 0.25\%$ @ 880nm, $R_{avg} \leq 1.25\%$ @ 400-1000nm


Typ. Energy Density Limit: 5 J/cm² @ 532nm, 10ns



MgF2 Coating

$R_{avg} \leq 1.75\%$ @ 400-700nm

Typ. Energy Density Limit: 10 J/cm² @ 532nm, 10ns



Products

Dia. (mm)	Coating	Number of Lenses	Contents of Kit	Contents of Kit	Stock Number	Price	Buy
12.50	MgF ₂ (400- 700nm)	13	Achromatic Lens Kit	Achromatic Lens Kit	#54-673	S\$911.04	Contact Us
12.50	VIS 0° (425- 675nm)	13.00	Achromatic Lens Kit	Achromatic Lens Kit	#48-540	S\$948.37	2 In Stock
12.50	VIS-NIR (400- 1000nm)	13.00	Achromatic Lens Kit	Achromatic Lens Kit	#65-984	S\$978.24	Contact Us
25.00	MgF ₂ (400- 700nm)	17.00	Achromatic Lens Kit	Achromatic Lens Kit	#52-306	S\$1,627.92	Contact Us
25.00	VIS 0° (425- 675nm)	17.00	Achromatic Lens Kit	Achromatic Lens Kit	#48-615	S\$1,650.32	2 In Stock
25.00	VIS-NIR (400- 1000nm)	17.00	Achromatic Lens Kit	Achromatic Lens Kit	#65-985	S\$1,695.12	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com