


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Interferometry Windows](#)

TECHSPEC® Single Surface Optical Flats



- Sizes Ranging from 1/2" Diameter to 14" Diameter
- Each $\lambda/20$ Flat 76.2mm and Larger Includes a Certificate of Calibration
- Available with Standard Metallic Mirror Coatings: [\$\lambda/10\$ and \$\lambda/20\$ Mirrors](#)

Common Specifications

Optical Properties

Coating:

Uncoated

Surface Quality:

60-40

Technical Information

Products

Surface Flatness (P-V)	Dia. (mm)	Thickness (mm)	Substrate	Stock Number	Price	Buy
λ/20	12.70	3.20	Fused Silica	#43-400-000	S\$189.00 Volume Pricing	Contact Us
λ/20	12.70	3.20	ZERODUR®	#43-404-000	S\$217.00 Volume Pricing	20+ In Stock
λ/10	12.70	3.20	Fused Silica	#43-319-000	S\$133.00 Volume Pricing	20+ In Stock
λ/10	12.70	3.20	ZERODUR®	#43-327-000	S\$147.00 Volume Pricing	6 In Stock
λ/20	25.40	12.70	Fused Silica	#43-408-000	S\$294.00 Volume Pricing	9 In Stock
λ/20	25.40	12.70	ZERODUR®	#43-412-000	S\$308.00 Volume Pricing	20+ In Stock
λ/10	25.40	12.70	Fused Silica	#01-913-000	S\$196.00 Volume Pricing	Contact Us
λ/10	25.40	12.70	ZERODUR®	#32-195-000	S\$224.00 Volume Pricing	20+ In Stock
λ/20	50.80	12.70	Fused Silica	#43-416-000	S\$441.00 Volume Pricing	20+ In Stock
λ/20	50.80	12.70	ZERODUR®	#43-420-000	S\$511.00 Volume Pricing	20+ In Stock
λ/10	50.80	12.70	Fused Silica	#01-914-000	S\$329.00 Volume Pricing	Contact Us
λ/10	50.80	12.70	ZERODUR®	#32-199-000	S\$364.00 Volume Pricing	20+ In Stock
λ/20	76.20	19.05	Fused Silica	#47-573-000	S\$840.00 Volume Pricing	20+ In Stock
λ/20	76.20	19.05	ZERODUR®	#48-117-000	S\$1,225.00 Volume Pricing	20+ In Stock
λ/10	76.20	19.05	Fused Silica	#01-915-000	S\$735.00 Volume Pricing	Contact Us
λ/10	76.20	19.05	ZERODUR®	#31-391-000	S\$938.00 Volume Pricing	20+ In Stock

λ/20	101.60	19.05	Fused Silica	#47-574-000	S\$1,393.00 Volume Pricing	20+ In Stock
λ/20	101.60	19.05	ZERODUR®	#48-118-000	S\$1,512.00 Volume Pricing	20+ In Stock
λ/10	101.60	19.05	Fused Silica	#01-611-000	S\$1,288.00 Volume Pricing	Contact Us
λ/10	101.60	19.05	ZERODUR®	#31-392-000	S\$1,323.00 Volume Pricing	15 In Stock
λ/10	127.00	25.40	Fused Silica (Corning 7980)	#71-130-000	S\$2,219.00 Volume Pricing	Contact Us
λ/20	127.00	25.40	Fused Silica (Corning 7980)	#71-131-000	S\$3,241.00 Volume Pricing	2 In Stock
λ/20	152.40	25.40	Fused Silica	#47-575-000	S\$4,165.00 Volume Pricing	9 In Stock
λ/20	152.40	25.40	ZERODUR®	#48-119-000	S\$4,690.00 Volume Pricing	6 In Stock
λ/10	152.40	25.40	Fused Silica	#01-612-000	S\$2,898.00 Volume Pricing	Contact Us
λ/10	152.40	25.40	ZERODUR®	#31-393-000	S\$3,108.00 Volume Pricing	20+ In Stock
λ/20	203.20	38.10	Fused Silica	#49-048-000	S\$7,434.00 Volume Pricing	7 In Stock
λ/20	203.20	38.10	ZERODUR®	#49-049-000	S\$7,658.00 Volume Pricing	5 In Stock
λ/10	203.20	38.10	Fused Silica	#31-390-000	S\$6,006.00 Volume Pricing	11 In Stock
λ/10	203.20	38.10	ZERODUR®	#31-394-000	S\$6,370.00 Volume Pricing	7 In Stock
λ/10	254.00	38.10	Fused Silica	#46-715-000	S\$9,100.00 Volume Pricing	20+ In Stock
λ/10	254.00	38.10	ZERODUR®	#71-108-000	S\$9,170.00 Volume Pricing	1 In Stock
λ/20	254.00	38.10	ZERODUR®	#71-110-000	S\$13,454.00 Volume Pricing	5 In Stock
λ/20	254.00	38.10	Fused Silica	#65-879-000	S\$13,573.00 Volume Pricing	9 In Stock
λ/10	304.80	38.10	Fused Silica	#69-921-000	S\$11,795.00 Volume Pricing	9 In Stock

λ/10	304.80	38.10	ZERODUR®	#71-109-000	S\$11,844.00 Volume Pricing	1 In Stock
λ/20	304.80	38.10	Fused Silica	#65-880-000	S\$18,312.00 Volume Pricing	11 In Stock
λ/20	304.80	38.10	ZERODUR®	#71-111-000	S\$18,340.00 Volume Pricing	1 In Stock
λ/10	355.60	88.90	Fused Silica	#71-247-000	S\$20,650.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com