

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

Long Working Distance Optimized Imaging Lenses



- Up to 2/3", S-Mount Lens
- Wide Field of View Board Camera Lens
- 1.68mm to 50mm Focal Length

Common Specifications

General

Series: Long Working Distance Optimized Imaging Lenses

Physical & Mechanical Properties

Iris Option: Fixed

Optical Properties

Working Distance (mm): 400 - ∞


Sensor

Pixel Size (μm): 3.45


Threading & Mounting

Mount: S-Mount (M12 x 0.5)

Technical Information



Infinite Conjugate M12 Imaging Lenses



C-Mount Adapter (#53-675)

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	IR Cut Filter	Stock Number	Price	Buy
1.68	f/2.5	1/4"	400 - ∞	No	#59-776	S\$89.90 Volume Pricing	20+ In Stock
1.68	f/2.5	1/4"	400 - ∞	Yes	#66-880	S\$88.45 Volume Pricing	20+ In Stock
#56-774 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
1.74	f/2.8	1/4"	400 - ∞	No		S\$60.83	20+ In Stock

[#66-881 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

1.74	f/2.8	1/4"	400 - ∞	Yes		S\$46.40	Contact Us
------	-------	------	------------	-----	--	----------	------------

1.80	f/2	1/4"	400 - ∞	No	#36-182	S\$88.45 Volume Pricing	20+ In Stock
------	-----	------	------------	----	-------------------------	--	--------------

1.80	f/2	1/4"	400 - ∞	Yes	#36-183	S\$88.45 Volume Pricing	20+ In Stock
------	-----	------	------------	-----	-------------------------	--	--------------

[#64-106 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

1.90	f/2	1/4"	400 - ∞	No		S\$86.27 Volume Pricing	20+ In Stock
------	-----	------	------------	----	--	--	--------------

2.10	f/2	1/3"	400 - ∞	No	#55-569	S\$89.90 Volume Pricing	20+ In Stock
------	-----	------	------------	----	-------------------------	--	--------------

2.10	f/2	1/3"	400 - ∞	Yes	#66-883	S\$88.45 Volume Pricing	20+ In Stock
2.50	f/2.5	1/3"	400 - ∞	No	#57-681	S\$89.90 Volume Pricing	20+ In Stock
2.50	f/2.5	1/3"	400 - ∞	Yes	#66-884	S\$88.45 Volume Pricing	20+ In Stock
2.50	f/2	1/2.8"	400 - ∞	No	#34-711	S\$110.20 Volume Pricing	13 In Stock

[#55-570 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

2.90	f/2	1/3"	400 - ∞	No		S\$59.81	20+ In Stock
------	-----	------	------------	----	--	----------	--------------

[#66-885 Clearance](#)



Clearance

Availability
is limited, so
buy before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive up
to 80% off
select
products.

2.90	f/2	1/3"	400 - ∞	Yes		S\$60.83	20+ In Stock
------	-----	------	------------	-----	--	----------	--------------

3.00	f/2	1/3"	400 - ∞	No	#59-778	S\$89.90 Volume Pricing	20+ In Stock
------	-----	------	------------	----	-------------------------	--	--------------

3.00	f/2	1/3"	400 - ∞	Yes	#66-886	S\$88.45 Volume Pricing	Contact Us
------	-----	------	------------	-----	-------------------------	--	------------

3.00	f/2	1/2.8"	400 - ∞	No	#88-587	S\$110.20 Volume Pricing	Contact Us
------	-----	--------	------------	----	-------------------------	---	------------

3.50	f/2.5	1/2.8"	400 - ∞	No	#88-588	S\$110.20 Volume Pricing	20+ In Stock
------	-------	--------	------------	----	-------------------------	---	--------------

3.74	f/1.6	1/1.8"	400 - ∞	No	#17-157	S\$110.20 Volume Pricing	5 In Stock
------	-------	--------	------------	----	-------------------------	---	------------

3.74	f/1.6	1/2"	400 - ∞	Yes	#11-323	S\$110.20 Volume Pricing	13 In Stock
------	-------	------	------------	-----	-------------------------	---	-------------

4.00	f/1.8	1/2"	400 - ∞	No	#17-158	S\$110.20 Volume Pricing	2 In Stock
------	-------	------	------------	----	-------------------------	---	------------

4.00	f/1.8	1/1.8"	400 - ∞	Yes	#11-324	S\$110.20 Volume Pricing	20+ In Stock
------	-------	--------	------------	-----	-------------------------	---	--------------

4.00	f/2	1/2.7"	400 - ∞	No	#88-589	S\$110.20 Volume Pricing	20+ In Stock
------	-----	--------	------------	----	-------------------------	---	--------------

4.30	f/2	1/2.7"	400 - ∞	No	#88-590	S\$110.20 Volume Pricing	Contact Us
------	-----	--------	------------	----	-------------------------	---	------------

4.60	f/2	1/2.8"	400 - ∞	No	#88-591	S\$110.20 Volume Pricing	5 In Stock
------	-----	--------	------------	----	-------------------------	---	------------

4.61	f/1.6	1/2"	400 - ∞	No	#17-159	S\$101.50	20+ In Stock
4.61	f/1.6	1/2"	400 - ∞	Yes	#11-325	S\$110.20 Volume Pricing	4 In Stock
5.60	f/2	1/2.8"	400 - ∞	No	#88-592	S\$110.20 Volume Pricing	20+ In Stock
6.00	f/2	1/2.7"	400 - ∞	No	#89-750	S\$110.20 Volume Pricing	20+ In Stock
6.00	f/1.8	1/3"	400 - ∞	No	#57-684	S\$89.90 Volume Pricing	20+ In Stock
6.00	f/1.8	1/3"	400 - ∞	Yes	#66-890	S\$88.45 Volume Pricing	20+ In Stock
6.40	f/2.4	1/3"	400 - ∞	No	#55-573	S\$89.90 Volume Pricing	20+ In Stock
6.40	f/2.4	1/3"	400 - ∞	Yes	#66-891	S\$88.45 Volume Pricing	20+ In Stock
6.96	f/1.6	1/2"	400 - ∞	No	#17-160	S\$110.20 Volume Pricing	Contact Us
6.96	f/1.6	1/1.8"	400 - ∞	Yes	#11-326	S\$110.20 Volume Pricing	20+ In Stock
8.00	f/2	1/2.7"	400 - ∞	No	#89-751	S\$110.20 Volume Pricing	Contact Us
8.00	f/2.5	1/3"	400 - ∞	No	#55-574	S\$89.90 Volume Pricing	20+ In Stock
8.00	f/2.5	1/3"	400 - ∞	Yes	#66-892	S\$88.45 Volume Pricing	20+ In Stock
10.10	f/2.8	1/2"	400 - ∞	No	#63-762	S\$88.45 Volume Pricing	20+ In Stock
10.10	f/2.8	1/2"	400 - ∞	Yes	#59-779	S\$88.45 Volume Pricing	20+ In Stock
10.40	f/2.8	1/2"	400 - ∞	No	#65-251	S\$88.45 Volume Pricing	Contact Us
10.40	f/2.8	1/2"	400 - ∞	Yes	#64-107	S\$88.45 Volume Pricing	20+ In Stock
12.00	f/2	1/3"	400 - ∞	No	#56-775	S\$89.90 Volume Pricing	20+ In Stock
12.00	f/2	1/3"	400 - ∞	Yes	#66-893	S\$88.45 Volume Pricing	20+ In Stock

12.00	f/2	1/2.7"	400 - ∞	No	#89-752	S\$110.20 Volume Pricing	20+ In Stock
16.00	f/2	1/3"	400 - ∞	No	#64-108	S\$88.45 Volume Pricing	20+ In Stock
16.00	f/4	1/3"	400 - ∞	No	#83-107	S\$88.45 Volume Pricing	20+ In Stock
16.00	f/2	1/3"	400 - ∞	Yes	#66-894	S\$88.45 Volume Pricing	20+ In Stock
25.00	f/2.5	1/3"	400 - ∞	No	#56-776	S\$104.40 Volume Pricing	Contact Us
25.00	f/2.5	1/3"	400 - ∞	Yes	#66-895	S\$104.40 Volume Pricing	20+ In Stock
35.00	f/2	2/3"	400 - ∞	No	#59-780	S\$104.40 Volume Pricing	20+ In Stock
35.00	f/2	2/3"	400 - ∞	Yes	#66-896	S\$104.40 Volume Pricing	20+ In Stock
50.00	f/2.5	1/2"	400 - ∞	No	#59-781	S\$110.20 Volume Pricing	20+ In Stock
50.00	f/2.5	1/2"	400 - ∞	Yes	#66-897	S\$110.20 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com