

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Concave \(DCV\) Lenses](#)

TECHSPEC® UV Fused Silica Double-Concave (DCV) Lenses



- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Wavelength Range of 200 - 2200nm
- Popular UV-AR Coating Option Available

Common Specifications

General

Note:

Max. Flat Annulus is 0.3mm

Physical & Mechanical Properties



Centering (arcmin):

<1

Optical Properties

Substrate: Fused Silica (Corning 7980)	Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±2	Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ	Irregularity (P-V) @ 632.8nm: λ/4

Technical Information



UV FS Transmission Curve

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
12.00	-20.00	-20.67	Uncoated	Fused Silica	#48-054	S\$187.60 Volume Pricing	20+ In Stock
12.00	-20.00	-20.67	UV-AR (250-425nm)	Fused Silica	#48-058	S\$224.00 Volume Pricing	3 In Stock
12.00	-30.00	-30.68	Uncoated	Fused Silica	#48-055	S\$187.60 Volume Pricing	1 In Stock
12.00	-30.00	-30.68	UV-AR (250-425nm)	Fused Silica	#48-059	S\$224.00 Volume Pricing	5 In Stock
12.00	-35.00	-35.68	Uncoated	Fused Silica	#48-056	S\$187.60 Volume Pricing	20+ In Stock
12.00	-35.00	-35.68	UV-AR (250-425nm)	Fused Silica	#48-060	S\$224.00 Volume Pricing	Contact Us
12.00	-45.00	-45.68	Uncoated	Fused Silica	#48-057	S\$187.60 Volume Pricing	20+ In Stock
12.00	-45.00	-45.68	UV-AR (250-425nm)	Fused Silica	#48-061	S\$224.00 Volume Pricing	4 In Stock
25.00	-50.00	-50.85	Uncoated	Fused Silica	#48-327	S\$203.00 Volume Pricing	20+ In Stock
25.00	-50.00	-50.85	UV-AR (250-425nm)	Fused Silica	#48-330	S\$239.40 Volume Pricing	5 In Stock
25.00	- 100.00	- 100.85	Uncoated	Fused Silica	#48-328	S\$203.00 Volume Pricing	20+ In Stock
25.00	- 100.00	- 100.85	UV-AR (250-425nm)	Fused Silica	#48-331	S\$239.40 Volume Pricing	10 In Stock
25.00	- 125.00	- 125.85	Uncoated	Fused Silica	#48-329	S\$203.00 Volume Pricing	11 In Stock
25.00	- 125.00	- 125.85	UV-AR (250-425nm)	Fused Silica	#48-332	S\$239.40 Volume Pricing	11 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com