


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Longpass Filters](#)

TECHSPEC® OD 2.0 Longpass Filters



- Sharp Cut-On Wavelength
- High Rejection/Transmission Efficiency
- Precision Fused Silica Substrate
- Variety of [OD 2.0 Longpass Filter Kits](#) are Available

Common Specifications


Physical & Mechanical Properties




Clear Aperture (%):	80
---------------------	----

Optical Properties


Angle of Incidence (°):	0		
Substrate:	Fused Silica (Corning 7980)	Coating:	Traditional Coated
Surface Quality:	40-20	Transmitted Wavefront, P-V:	λ/4
Cut-On Tolerance (%):	±2	Slope Factor (%):	3.00

Technical Information





Products

Dia. (mm)	Cut-On Wavelength (nm)	Thickness (mm)	Rejection Wavelength (nm)	Transmission Wavelength (nm)	Wavelength Range (nm)	Stock Number	Price	Buy
12.50	400.00	1.50	200 - 375	420 - 2000	200 - 2000	#49-024	S\$137.20 Volume Pricing	20+ In Stock
25.00	400.00	3.00	200 - 375	420 - 2000	200 - 2000	#47-614	S\$210.00 Volume Pricing	20+ In Stock
12.50	425.00	1.50	200 - 405	445 - 2000	200 - 2000	#64-616	S\$137.20 Volume Pricing	20+ In Stock
25.00	425.00	3.00	200 - 405	445 - 2000	200 - 2000	#64-624	S\$210.00 Volume Pricing	20+ In Stock
50.00	425.00	5.00	200 - 405	445 - 2000	200 - 2000	#64-632	S\$336.00 Volume Pricing	20+ In Stock
12.50	450.00	1.50	200 - 430	470 - 2000	200 - 2000	#49-025	S\$137.20 Volume Pricing	20+ In Stock
25.00	450.00	3.00	200 - 430	470 - 2000	200 - 2000	#47-615	S\$210.00 Volume Pricing	14 In Stock
50.00	450.00	5.00	200 - 430	470 - 2000	200 - 2000	#64-698	S\$336.00 Volume Pricing	20+ In Stock
12.50	475.00	1.50	200 - 455	495 - 2000	200 - 2000	#64-617	S\$137.20 Volume Pricing	Contact Us
50.00	500.00	5.00	200 - 480	520 - 2000	200 - 2000	#64-699	S\$336.00 Volume Pricing	20+ In Stock
12.50	525.00	1.50	200 - 505	545 - 2000	200 - 2000	#64-618	S\$137.20 Volume Pricing	20+ In Stock
25.00	525.00	3.00	200 - 505	545 - 2000	200 - 2000	#64-626	S\$210.00 Volume Pricing	20+ In Stock
#14-665 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
35.00	525.00	5.00	200 - 505	545 - 2000	200 - 2000		S\$70.00 Volume Pricing	20+ In Stock

[#64-634 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	525.00	5.00	200 - 505	545 - 2000	200 - 2000		SS\$301.00 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	--	--	--------------

12.50	550.00	1.50	415 - 515	575 - 2000	415 - 2000	#49-027	SS\$137.20 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	-------------------------	--	--------------

25.00	550.00	3.00	415 - 515	575 - 2000	415 - 2000	#47-617	SS\$210.00 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	-------------------------	--	--------------

[#64-619 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	575.00	1.50	440 - 540	600 - 2000	440 - 2000		SS\$126.00 Volume Pricing	13 In Stock
-------	--------	------	-----------	------------	------------	--	--	-------------

12.50	600.00	1.50	460 - 570	625 - 2000	460 - 2000	#49-028	SS\$137.20 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	-------------------------	--	--------------

[#64-620 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	625.00	1.50	485 - 595	650 - 2000	485 - 2000	S\$126.00 Volume Pricing	8 In Stock
-------	--------	------	-----------	------------	------------	---	------------

[#64-621 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	675.00	1.50	520 - 635	700 - 2000	520 - 2000	S\$126.00 Volume Pricing	3 In Stock
-------	--------	------	-----------	------------	------------	---	------------

[#64-637 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00 675.00 5.00 520 - 635 700 - 2000 520 - 2000

S\$301.00
[Volume Pricing](#)

3 In Stock

[#49-031 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50 750.00 1.50 565 - 715 780 - 2000 565 - 2000

S\$126.00
[Volume Pricing](#)

10 In Stock

[#64-623 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	775.00	1.50	590 - 740	805 - 2000	590 - 2000	SS\$126.00 Volume Pricing	3 In Stock
-------	--------	------	-----------	------------	------------	--	------------

[#64-676 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	825.00	1.50	625 - 785	855 - 2000	625 - 2000	SS\$126.00 Volume Pricing	12 In Stock
-------	--------	------	-----------	------------	------------	--	-------------

[#64-683 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.00 825.00 3.00 625 - 785 855 - 2000 625 - 2000

SS\$182.00
[Volume Pricing](#)

16 In Stock

[#64-690 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00 825.00 5.00 625 - 785 855 - 2000 625 - 2000

SS\$336.00
[Volume Pricing](#)

20+ In Stock

[#64-677 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	875.00	1.50	660 - 830	910 - 2000	660 - 2000		S\$126.00 Volume Pricing	12 In Stock
-------	--------	------	-----------	------------	------------	--	---	-------------

25.00	875.00	3.00	660 - 830	910 - 2000	660 - 2000	#64-684	S\$210.00 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	-------------------------	---	--------------

50.00	900.00	5.00	675 - 855	935 - 2000	675 - 2000	#64-707	S\$336.00 Volume Pricing	20+ In Stock
-------	--------	------	-----------	------------	------------	-------------------------	---	--------------

12.50	925.00	1.50	700 - 880	960 - 2000	700 - 2000	#64-678	S\$137.20 Volume Pricing	Contact Us
-------	--------	------	-----------	------------	------------	-------------------------	---	------------

[#64-685 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.00	925.00	3.00	700 - 880	960 - 2000	700 - 2000		S\$182.00 Volume Pricing	14 In Stock
-------	--------	------	-----------	------------	------------	--	---	-------------

[#64-692 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

50.00	925.00	5.00	700 - 880	960 - 2000	700 - 2000		<p>S\$301.00 Volume Pricing</p>	8 In Stock
-------	--------	------	-----------	------------	------------	--	---	------------

12.50	950.00	1.50	715 - 900	985 - 2000	715 - 2000	#49-035	<p>S\$137.20 Volume Pricing</p>	3 In Stock
-------	--------	------	-----------	------------	------------	-------------------------	---	------------

[#48-562 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

25.00	950.00	3.00	715 - 900	985 - 2000	715 - 2000		<p>S\$182.00 Volume Pricing</p>	4 In Stock
-------	--------	------	-----------	------------	------------	--	---	------------

[#64-708 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	950.00	5.00	715 - 900	985 - 2000	715 - 2000	<div>SS\$301.00 Volume Pricing</div>	3 In Stock
-------	--------	------	-----------	------------	------------	--	------------

[#64-679 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	975.00	1.50	735 - 925	1010 - 2000	735 - 2000	<div>SS\$126.00 Volume Pricing</div>	10 In Stock
-------	--------	------	-----------	-------------	------------	--	-------------

[#64-686 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.00	975.00	3.00	735 - 925	1010 - 2000	735 - 2000	S\$182.00 Volume Pricing	4 In Stock
-------	--------	------	-----------	-------------	------------	---	------------

[#64-693 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	975.00	5.00	735 - 925	1010 - 2000	735 - 2000	S\$301.00 Volume Pricing	11 In Stock
-------	--------	------	-----------	-------------	------------	---	-------------

12.50	1,000.00	1.50	750 - 950	1035 - 2000	750 - 2000	#49-036 S\$137.20 Volume Pricing	5 In Stock
-------	----------	------	-----------	-------------	------------	--	------------

[#64-694 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	1,025.00	5.00	780 - 975	1060 - 2000	780 - 2000	S\$301.00 Volume Pricing	15 In Stock
-------	----------	------	-----------	-------------	------------	---	-------------

[#49-037 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.50	1,050.00	1.50	790 - 1000	1085 - 2000	790 - 2000	S\$126.00 Volume Pricing	17 In Stock
-------	----------	------	------------	-------------	------------	---	-------------

[#64-710 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	1,050.00	5.00	790 - 1000	1085 - 2000	709 - 2000		S\$301.00 Volume Pricing	4 In Stock
-------	----------	------	------------	-------------	------------	--	---	------------

12.50	1,075.00	1.50	820 - 1025	1110 - 2000	820 - 2000	#64-681	S\$137.20 Volume Pricing	10 In Stock
-------	----------	------	------------	-------------	------------	-------------------------	---	-------------

[#64-695 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

50.00	1,075.00	5.00	820 - 1025	1110 - 2000	820 - 2000		S\$301.00 Volume Pricing	5 In Stock
-------	----------	------	------------	-------------	------------	--	---	------------



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com