


[All Products](#) / [Optics](#) / [Prisms](#) / [Light Pipes and Homogenizing Rods](#)

TECHSPEC® N-BK7 Light Pipe Homogenizing Rods



- Homogenizes Non-Uniform Light Sources
- Hexagonal Entrance Aperture
- Uncoated and VIS-EXT Coated Options Available
- Ideal for OEM Illumination
- Additional [Light Pipe Homogenizing Rods](#) Available

Common Specifications

Physical & Mechanical Properties

Parallelism (arcmin):	<5.00
-----------------------	-------

Optical Properties


Substrate:	N-BK7
------------	-----------------------

Surface Quality:	60-40
------------------	-------

Aperture Tolerance (mm):	±0.10
--------------------------	-------

Image Orientation:	Light Homogenization
--------------------	----------------------

Technical Information



Products

Entrance and Exit Aperture (mm)	Wavelength Range (nm)	Length (mm)	Stock Number	Price	Buy
2.00	350 - 2200	25.00	#48-582	S\$232.40 Volume Pricing	20+ In Stock
2.00	350 - 2200	50.00	#63-080	S\$240.80 Volume Pricing	20+ In Stock
2.00	350 - 2200	75.00	#63-081	S\$289.80 Volume Pricing	3 In Stock
4.00	350 - 2200	25.00	#63-082	S\$182.00 Volume Pricing	Contact Us
4.00	350 - 2200	50.00	#49-402	S\$204.40 Volume Pricing	20+ In Stock
4.00	350 - 2200	100.00	#63-083	S\$240.80 Volume Pricing	17 In Stock
5.00	350 - 2200	30.00	#63-084	S\$196.00 Volume Pricing	20+ In Stock
5.00	350 - 2200	60.00	#48-583	S\$218.40 Volume Pricing	20+ In Stock
5.00	350 - 2200	120.00	#63-085	S\$263.20 Volume Pricing	20+ In Stock
6.00	350 - 2200	50.00	#63-086	S\$204.40 Volume Pricing	20+ In Stock
6.00	350 - 2200	75.00	#49-403	S\$232.40 Volume Pricing	20+ In Stock
6.00	350 - 2200	150.00	#63-087	S\$277.20 Volume Pricing	15 In Stock
8.00	350 - 2200	50.00	#63-088	S\$232.40 Volume Pricing	17 In Stock
8.00	350 - 2200	100.00	#49-404	S\$254.80 Volume Pricing	16 In Stock
10.00	350 - 2200	75.00	#63-090	S\$263.20 Volume Pricing	20+ In Stock
10.00	350 - 2200	125.00	#48-584	S\$289.80 Volume Pricing	20+ In Stock
10.00	350 - 2200	175.00	#63-091	S\$312.20 Volume Pricing	Contact Us

12.5	350 - 2200	75.00	#84-529	S\$277.20 Volume Pricing	20+ In Stock
12.5	350 - 2200	150.00	#84-530	S\$303.80 Volume Pricing	14 In Stock
12.5	350 - 2200	250.00	#84-531	S\$362.60 Volume Pricing	5 In Stock
15.0	350 - 2200	100.00	#84-532	S\$340.20 Volume Pricing	20+ In Stock
15.0	350 - 2200	300.00	#84-534	S\$462.00 Volume Pricing	6 In Stock
20.0	350 - 2200	200.00	#84-536	S\$462.00 Volume Pricing	20+ In Stock
20.0	350 - 2200	125.00	#84-535	S\$394.80 Volume Pricing	20+ In Stock
20.0	350 - 2200	300.00	#84-537	S\$589.40 Volume Pricing	20+ In Stock
2.00	350 - 700	25.00	#72-725	S\$303.80 Volume Pricing	5 In Stock
2.00	350 - 700	50.00	#72-726	S\$312.20 Volume Pricing	5 In Stock
2.00	350 - 700	75.00	#72-727	S\$362.60 Volume Pricing	Contact Us
4.00	350 - 700	25.00	#72-728	S\$254.80 Volume Pricing	4 In Stock
4.00	350 - 700	50.00	#72-729	S\$277.20 Volume Pricing	5 In Stock
4.00	350 - 700	100.00	#72-730	S\$312.20 Volume Pricing	2 In Stock
5.00	350 - 700	30.00	#72-731	S\$267.40 Volume Pricing	5 In Stock
5.00	350 - 700	60.00	#72-732	S\$289.80 Volume Pricing	2 In Stock
5.00	350 - 700	120.00	#72-733	S\$334.60 Volume Pricing	2 In Stock
6.00	350 - 700	50.00	#72-734	S\$277.20 Volume Pricing	4 In Stock
6.00	350 - 700	75.00	#72-735	S\$303.80 Volume Pricing	3 In Stock
6.00	350 - 700	150.00	#72-736	S\$348.60 Volume Pricing	2 In Stock

8.00	350 - 700	50.00	#72-737	S\$312.20 Volume Pricing	3 In Stock
8.00	350 - 700	100.00	#72-738	S\$334.60 Volume Pricing	1 In Stock
10.00	350 - 700	75.00	#72-739	S\$345.80 Volume Pricing	3 In Stock
10.00	350 - 700	125.00	#72-740	S\$371.00 Volume Pricing	5 In Stock
10.00	350 - 700	175.00	#72-741	S\$394.80 Volume Pricing	2 In Stock
12.50	350 - 700	75.00	#72-742	S\$357.00 Volume Pricing	2 In Stock
12.50	350 - 700	150.00	#72-743	S\$385.00 Volume Pricing	2 In Stock
12.50	350 - 700	250.00	#72-744	S\$445.20 Volume Pricing	5 In Stock
15.00	350 - 700	100.00	#72-745	S\$431.20 Volume Pricing	Contact Us
15.00	350 - 700	300.00	#72-746	S\$553.00 Volume Pricing	Contact Us
20.00	350 - 700	200.00	#72-747	S\$476.00 Volume Pricing	5 In Stock
20.00	350 - 700	125.00	#72-748	S\$494.20 Volume Pricing	Contact Us
20.00	350 - 700	300.00	#72-749	S\$688.80 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com