

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

Kodak Wratten 2 Neutral Density Filters



- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Common Specifications

Optical Properties

Substrate:	Wratten 2	Coating:	Uncoated
Blocking Wavelength Range (nm):	400 - 700		

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Optical Density OD (Average)	Transmission (%)	Stock Number	Price	Buy
25.00	-	0.1	80.00	#28-998	S\$125.45 Volume Pricing	9 In Stock
25.00	-	0.3	50.00	#28-999	S\$125.45 Volume Pricing	5 In Stock
25.00	-	0.5	32.00	#29-000	S\$125.45 Volume Pricing	5 In Stock
25.00	-	1.0	10.00	#29-001	S\$125.45 Volume Pricing	5 In Stock
25.00	-	2.0	1.0	#29-002	S\$125.45 Volume Pricing	3 In Stock
25.00	-	3.0	0.1	#29-003	S\$125.45 Volume Pricing	1 In Stock
48.00	-	0.1	80.00	#29-004	S\$222.53 Volume Pricing	6 In Stock
48.00	-	0.3	50.00	#29-005	S\$222.53 Volume Pricing	2 In Stock
48.00	-	0.5	32.00	#29-006	S\$222.53 Volume Pricing	5 In Stock
48.00	-	1.0	10.00	#29-007	S\$222.53 Volume Pricing	3 In Stock
48.00	-	2.0	1.0	#29-008	S\$222.53 Volume Pricing	3 In Stock
48.00	-	3.0	0.1	#29-009	S\$222.53 Volume Pricing	4 In Stock
-	75 x 75	0.1	80.00	#54-453	S\$345.00 Volume Pricing	20+ In Stock
-	75 x 75	0.2	63.00	#53-702	S\$345.00 Volume Pricing	10 In Stock
-	75 x 75	0.3	50.00	#53-703	S\$345.00 Volume Pricing	20+ In Stock
-	75 x 75	0.4	40.00	#54-454	S\$345.00 Volume Pricing	4 In Stock
-	75 x 75	0.5	32.00	#54-455	S\$345.00 Volume Pricing	20+ In Stock

-	75 x 75	0.6	25.00	#53-704	S\$345.00 Volume Pricing	20+ In Stock
-	75 x 75	0.7	20.00	#54-456	S\$345.00 Volume Pricing	3 In Stock
-	75 x 75	0.8	16.00	#54-457	S\$345.00 Volume Pricing	9 In Stock
-	75 x 75	0.9	13.00	#54-458	S\$345.00 Volume Pricing	20+ In Stock
-	75 x 75	1.0	10.00	#53-705	S\$345.00 Volume Pricing	5 In Stock
-	75 x 75	2.0	1.00	#53-706	S\$345.00 Volume Pricing	20+ In Stock
-	75 x 75	3.0	0.1	#53-707	S\$345.00 Volume Pricing	9 In Stock
-	75 x 75	4.0	0.01	#54-459	S\$345.00 Volume Pricing	14 In Stock
-	100.0 x 300.0	0.1	80.00	#83-996	S\$761.69 Volume Pricing	Contact Us
-	100.0 x 300.0	0.2	63.00	#83-997	S\$761.69 Volume Pricing	10 In Stock
-	100.0 x 300.0	0.3	50.00	#83-998	S\$761.69 Volume Pricing	20+ In Stock
-	100.0 x 300.0	0.5	32.00	#84-000	S\$761.69 Volume Pricing	3 In Stock
-	100.0 x 300.0	0.6	25.00	#84-001	S\$761.69 Volume Pricing	6 In Stock
-	100.0 x 300.0	0.7	20.00	#84-002	S\$761.69 Volume Pricing	10 In Stock
-	100.0 x 300.0	1.0	10.00	#84-005	S\$761.69 Volume Pricing	20+ In Stock
-	100.0 x 300.0	2.0	1.0	#84-006	S\$761.69 Volume Pricing	16 In Stock
-	100.0 x 300.0	3.0	0.1	#84-007	S\$761.69 Volume Pricing	4 In Stock
-	100.0 x 300.0	4.0	0.01	#84-008	S\$761.69 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com