


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Light Pipes and Homogenizing Rods](#)

TECHSPEC® Fused Silica Light Pipe Homogenizing Rods



- Excellent Transmission in the UV
- Hexagonal Aperture Maximizes Throughput
- Perfect for Non-Uniform Light Sources
- [Additional Light Pipe Homogenizing Rods](#) Available

Common Specifications

Physical & Mechanical Properties

Parallelism (arcmin):	5.00
-----------------------	------


Optical Properties

Surface Quality:	60-40
------------------	-------

Aperture Tolerance (mm):	±0.10
--------------------------	-------

Image Orientation:	Light Homogenization
--------------------	----------------------

Technical Information



Products

Entrance and Exit Aperture (mm)	Length (mm)	Coating	Stock Number	Price	Buy
2.00	25.00	Uncoated	#63-092	S\$312.20 Volume Pricing	20+ In Stock
2.00	25.00	UV-VIS (250-700nm)	#26-548	S\$385.00 Volume Pricing	14 In Stock
2.00	25.00	VIS-NIR (400-1000nm)	#23-490	S\$385.00 Volume Pricing	5 In Stock
2.00	25.00	VIS-EXT (350-700nm)	#70-714	S\$385.00 Volume Pricing	4 In Stock
2.00	50.00	Uncoated	#65-828	S\$362.60 Volume Pricing	Contact Us
2.00	50.00	UV-VIS (250-700nm)	#26-549	S\$436.80 Volume Pricing	11 In Stock
2.00	50.00	VIS-NIR (400-1000nm)	#23-491	S\$436.80 Volume Pricing	2 In Stock
2.00	50.00	VIS-EXT (350-700nm)	#70-715	S\$436.80 Volume Pricing	1 In Stock
2.00	75.00	Uncoated	#65-829	S\$408.80 Volume Pricing	20+ In Stock
2.00	75.00	UV-VIS (250-700nm)	#26-550	S\$490.00 Volume Pricing	13 In Stock
2.00	75.00	VIS-NIR (400-1000nm)	#23-492	S\$490.00 Volume Pricing	5 In Stock
2.00	75.00	VIS-EXT (350-700nm)	#70-716	S\$490.00 Volume Pricing	5 In Stock
3.00	25.00	Uncoated	#23-666	S\$289.80 Volume Pricing	20+ In Stock
3.00	25.00	UV-VIS (250-700nm)	#26-551	S\$362.60 Volume Pricing	15 In Stock
3.00	25.00	VIS-NIR (400-1000nm)	#26-545	S\$362.60 Volume Pricing	1 In Stock
3.00	25.00	VIS-EXT (350-700nm)	#70-717	S\$362.60 Volume Pricing	4 In Stock

3.00	50.00	Uncoated	#23-667	S\$334.60 Volume Pricing	10 In Stock
3.00	50.00	UV-VIS (250-700nm)	#26-552	S\$408.80 Volume Pricing	6 In Stock
3.00	50.00	VIS-NIR (400-1000nm)	#26-546	S\$408.80 Volume Pricing	4 In Stock
3.00	50.00	VIS-EXT (350-700nm)	#70-718	S\$408.80 Volume Pricing	4 In Stock
3.00	100.00	Uncoated	#23-668	S\$380.80 Volume Pricing	14 In Stock
3.00	100.00	UV-VIS (250-700nm)	#26-553	S\$462.00 Volume Pricing	5 In Stock
3.00	100.00	VIS-NIR (400-1000nm)	#26-547	S\$462.00 Volume Pricing	Contact Us
3.00	100.00	VIS-EXT (350-700nm)	#70-719	S\$462.00 Volume Pricing	1 In Stock
4.00	25.00	Uncoated	#65-830	S\$267.40 Volume Pricing	20+ In Stock
4.00	25.00	UV-VIS (250-700nm)	#26-554	S\$340.20 Volume Pricing	13 In Stock
4.00	25.00	VIS-NIR (400-1000nm)	#23-493	S\$340.20 Volume Pricing	9 In Stock
4.00	25.00	VIS-EXT (350-700nm)	#70-720	S\$340.20 Volume Pricing	Contact Us
4.00	50.00	Uncoated	#63-093	S\$312.20 Volume Pricing	20+ In Stock
4.00	50.00	UV-VIS (250-700nm)	#26-555	S\$385.00 Volume Pricing	7 In Stock
4.00	50.00	VIS-NIR (400-1000nm)	#23-494	S\$385.00 Volume Pricing	3 In Stock
4.00	50.00	VIS-EXT (350-700nm)	#70-721	S\$385.00 Volume Pricing	3 In Stock
4.00	100.00	Uncoated	#65-831	S\$348.60 Volume Pricing	20+ In Stock
4.00	100.00	UV-VIS (250-700nm)	#26-556	S\$431.20 Volume Pricing	13 In Stock
4.00	100.00	VIS-NIR (400-1000nm)	#23-495	S\$431.20 Volume Pricing	2 In Stock

4.00	100.00	VIS-EXT (350-700nm)	#70-722	S\$431.20 Volume Pricing	4 In Stock
5.00	30.00	Uncoated	#65-832	S\$285.60 Volume Pricing	20+ In Stock
5.00	30.00	UV-VIS (250-700nm)	#26-557	S\$357.00 Volume Pricing	20+ In Stock
5.00	30.00	VIS-NIR (400-1000nm)	#23-496	S\$357.00 Volume Pricing	4 In Stock
5.00	30.00	VIS-EXT (350-700nm)	#70-723	S\$357.00 Volume Pricing	1 In Stock
5.00	60.00	Uncoated	#63-094	S\$334.60 Volume Pricing	20+ In Stock
5.00	60.00	UV-VIS (250-700nm)	#26-558	S\$408.80 Volume Pricing	9 In Stock
5.00	60.00	VIS-NIR (400-1000nm)	#23-497	S\$408.80 Volume Pricing	7 In Stock
5.00	60.00	VIS-EXT (350-700nm)	#70-724	S\$408.80 Volume Pricing	5 In Stock
5.00	120.00	Uncoated	#65-833	S\$394.80 Volume Pricing	20+ In Stock
5.00	120.00	UV-VIS (250-700nm)	#26-559	S\$476.00 Volume Pricing	11 In Stock
5.00	120.00	VIS-NIR (400-1000nm)	#23-498	S\$476.00 Volume Pricing	13 In Stock
5.00	120.00	VIS-EXT (350-700nm)	#70-725	S\$476.00 Volume Pricing	5 In Stock
6.00	50.00	Uncoated	#65-834	S\$312.20 Volume Pricing	12 In Stock
6.00	50.00	UV-VIS (250-700nm)	#26-560	S\$385.00 Volume Pricing	4 In Stock
6.00	50.00	VIS-NIR (400-1000nm)	#23-499	S\$385.00 Volume Pricing	5 In Stock
6.00	50.00	VIS-EXT (350-700nm)	#70-726	S\$385.00 Volume Pricing	5 In Stock
6.00	75.00	Uncoated	#63-095	S\$362.60 Volume Pricing	20+ In Stock
6.00	75.00	UV-VIS (250-700nm)	#26-561	S\$445.20 Volume Pricing	5 In Stock

6.00	75.00	VIS-NIR (400-1000nm)	#23-500	S\$445.20 Volume Pricing	8 In Stock
6.00	75.00	VIS-EXT (350-700nm)	#70-727	S\$445.20 Volume Pricing	5 In Stock
6.00	150.00	Uncoated	#65-835	S\$471.80 Volume Pricing	20+ In Stock
6.00	150.00	UV-VIS (250-700nm)	#26-562	S\$561.40 Volume Pricing	20+ In Stock
6.00	150.00	VIS-NIR (400-1000nm)	#23-501	S\$561.40 Volume Pricing	3 In Stock
6.00	150.00	VIS-EXT (350-700nm)	#70-728	S\$561.40 Volume Pricing	4 In Stock
8.00	50.00	Uncoated	#65-836	S\$362.60 Volume Pricing	14 In Stock
8.00	50.00	UV-VIS (250-700nm)	#26-563	S\$436.80 Volume Pricing	2 In Stock
8.00	50.00	VIS-NIR (400-1000nm)	#23-502	S\$436.80 Volume Pricing	5 In Stock
8.00	50.00	VIS-EXT (350-700nm)	#70-729	S\$436.80 Volume Pricing	4 In Stock
8.00	100.00	Uncoated	#63-096	S\$408.80 Volume Pricing	20+ In Stock
8.00	100.00	UV-VIS (250-700nm)	#26-564	S\$490.00 Volume Pricing	2 In Stock
8.00	100.00	VIS-NIR (400-1000nm)	#23-503	S\$490.00 Volume Pricing	5 In Stock
8.00	100.00	VIS-EXT (350-700nm)	#70-730	S\$490.00 Volume Pricing	Contact Us
8.00	150.00	Uncoated	#65-837	S\$572.60 Volume Pricing	5 In Stock
8.00	150.00	UV-VIS (250-700nm)	#26-565	S\$663.60 Volume Pricing	4 In Stock
8.00	150.00	VIS-NIR (400-1000nm)	#23-504	S\$663.60 Volume Pricing	5 In Stock
8.00	150.00	VIS-EXT (350-700nm)	#70-731	S\$663.60 Volume Pricing	5 In Stock
10.00	75.00	Uncoated	#65-838	S\$436.80 Volume Pricing	20+ In Stock

10.00	75.00	UV-VIS (250-700nm)	#26-566	S\$516.60 Volume Pricing	4 In Stock
10.00	75.00	VIS-NIR (400-1000nm)	#23-505	S\$516.60 Volume Pricing	5 In Stock
10.00	75.00	VIS-EXT (350-700nm)	#70-732	S\$516.60 Volume Pricing	3 In Stock
10.00	125.00	Uncoated	#63-097	S\$512.40 Volume Pricing	20+ In Stock
10.00	125.00	UV-VIS (250-700nm)	#26-567	S\$603.40 Volume Pricing	12 In Stock
10.00	125.00	VIS-NIR (400-1000nm)	#23-506	S\$603.40 Volume Pricing	3 In Stock
10.00	125.00	VIS-EXT (350-700nm)	#70-733	S\$603.40 Volume Pricing	1 In Stock
10.00	175.00	Uncoated	#65-839	S\$630.00 Volume Pricing	16 In Stock
10.00	175.00	UV-VIS (250-700nm)	#26-568	S\$721.00 Volume Pricing	Contact Us
10.00	175.00	VIS-NIR (400-1000nm)	#23-507	S\$721.00 Volume Pricing	3 In Stock
10.00	175.00	VIS-EXT (350-700nm)	#70-734	S\$721.00 Volume Pricing	5 In Stock
12.50	75.00	Uncoated	#70-759	S\$498.40 Volume Pricing	10 In Stock
20.00	125.00	Uncoated	#70-762	S\$716.80 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com