

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® C Series Fixed Focal Length Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C), FA Lens for Machine Vision
- 3.5mm to 100mm Focal Length

Common Specifications

General

Series: C Series

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Coating: 425 - 675nm BBAR

Coating Specification: 425 - 675nm BBAR


Sensor

Pixel Size (µm): 2.74

Threading & Mounting

Mount: C-Mount

Technical Information



Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
3.50	1/1.8"	f/2 - f/11	0 - ∞	C-Mount	#89-410	S\$426.00	20+ In Stock
4.50	1/1.8"	f/2 - f/11	25 - ∞	C-Mount	#86-900	S\$426.00	20+ In Stock
6.00	1/1.8"	f/1.4 - f/16	75 - ∞	C-Mount	#67-709	S\$343.00	20+ In Stock
8.50	2/3"	f/1.3 - f/16	100 - ∞	C-Mount	#58-000	S\$273.00	20+ In Stock
12.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#58-001	S\$273.00	20+ In Stock
16.00	2/3"	f/1.6 - f/16	100 - ∞	C-Mount	#59-870	S\$256.00	20+ In Stock
25.00	2/3"	f/1.4 - f/16	100 - ∞	C-Mount	#59-871	S\$256.00	20+ In Stock
35.00	2/3"	f/1.65 - f/22	165 - ∞	C-Mount	#59-872	S\$256.00	20+ In Stock
50.00	2/3"	f/2 - f/22	250 - ∞	C-Mount	#59-873	S\$343.00	20+ In Stock
75.00	2/3"	f/2.0 - f/16.0	500 - ∞	C-Mount	#33-310	S\$375.00	20+ In Stock
100.00	4/3"	f/2.8 - f/22	750 - ∞	C-Mount	#86-410	S\$426.00	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com