

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Specialty Mirrors](#)

Convex Spherical Mirrors



- Variety of Diameters and Focal Lengths Available
- Enhanced Aluminum and Protected Gold Coatings
- Ideal for Imaging Systems

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	90
---------------------	----

Optical Properties

Coating Type:	Metal
---------------	-------

Focal Length Tolerance (%):	± 2
-----------------------------	---------

Surface Quality:	60-40
------------------	-------

Technical Information

Products

Dia. (mm)	FL (mm)	Coating	Coating Specification	Wavelength Range (nm)	Stock Number	Price	Buy
12.00	-6.10	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-055	S\$61.98 Volume Pricing	13 In Stock
12.00	-7.75	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-056	S\$61.98 Volume Pricing	1 In Stock
12.00	-12.40	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-057	S\$61.98 Volume Pricing	3 In Stock
12.00	-15.50	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-058	S\$61.98 Volume Pricing	1 In Stock
12.00	-25.80	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-059	S\$61.98 Volume Pricing	1 In Stock
25.00	-7.75	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-060	S\$70.57 Volume Pricing	2 In Stock
25.00	-15.50	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-061	S\$70.57 Volume Pricing	10 In Stock
25.00	-25.80	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-062	S\$70.57 Volume Pricing	6 In Stock
50.00	-25.80	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-065	S\$86.62 Volume Pricing	7 In Stock
50.00	-45.20	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-066	S\$86.62 Volume Pricing	2 In Stock

50.00	-51.70	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-067	S\$86.62 Volume Pricing	Contact Us
50.00	-129.20	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	450 - 650	#64-068	S\$86.62 Volume Pricing	4 In Stock
12.00	-6.10	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-069	S\$70.57 Volume Pricing	2 In Stock
12.00	-7.75	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-070	S\$70.57 Volume Pricing	2 In Stock
12.00	-12.40	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-071	S\$70.57 Volume Pricing	11 In Stock
12.00	-15.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-072	S\$70.57 Volume Pricing	4 In Stock
12.00	-25.80	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-073	S\$70.57 Volume Pricing	20+ In Stock
25.00	-7.75	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-074	S\$78.41 Volume Pricing	2 In Stock
25.00	-15.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-075	S\$78.41 Volume Pricing	3 In Stock

25.00	-25.80	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-076	S\$78.41 Volume Pricing	Contact Us
50.00	-25.80	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-079	S\$94.84 Volume Pricing	1 In Stock
50.00	-45.20	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-080	S\$94.84 Volume Pricing	Contact Us
50.00	-51.70	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-081	S\$94.84 Volume Pricing	3 In Stock
50.00	-129.20	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	700 - 10000	#64-082	S\$94.84 Volume Pricing	14 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com