

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Cube Beamsplitters](#)

TECHSPEC® Broadband Polarizing Cube Beamsplitters



- Visible and NIR Coating Options Offered
- 500:1 Extinction Ratio
- AR Coated for <0.5% reflection per surface

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%): 90

Construction: Cube

Optical Properties

 Beam Deviation (arcmin): ± 3

Extinction Ratio: 500:1

P-Polarization Transmission (%): >90

S-Polarization Reflection (%): >99



 Substrate: [N-SF11](#)



Surface Quality: 40-20

Power (fringes) @ 632.8nm: 1.25

Irregularity (fringes) @ 632.8nm: 0.25

Technical Information





Products

Extinction Ratio	Dimensions (mm)	Wavelength Range (nm)	Stock Number	Price	Buy
500:1	5.0 x 5.0 x 5.0	420 - 680	#48-998	S\$400.40 Volume Pricing	1 In Stock
500:1	10.0 x 10.0 x 10.0	420 - 680	#48-999	S\$413.00 Volume Pricing	20+ In Stock
500:1	20.0 x 20.0 x 20.0	420 - 680	#49-001	S\$427.00 Volume Pricing	20+ In Stock
500:1	25.0 x 25.0 x 25.0	420 - 680	#49-002	S\$446.60 Volume Pricing	20+ In Stock
500:1	50.0 x 50.0 x 50.0	420 - 680	#65-603	S\$1,240.40 Volume Pricing	20+ In Stock
500:1	5.0 x 5.0 x 5.0	700 - 1100	#49-869	S\$400.40 Volume Pricing	8 In Stock
500:1	10.0 x 10.0 x 10.0	700 - 1100	#49-870	S\$413.00 Volume Pricing	20+ In Stock
500:1	20.0 x 20.0 x 20.0	700 - 1100	#49-871	S\$427.00 Volume Pricing	15 In Stock
500:1	25.0 x 25.0 x 25.0	700 - 1100	#49-872	S\$446.60 Volume Pricing	9 In Stock
500:1	50.0 x 50.0 x 50.0	700 - 1100	#65-606	S\$1,240.40 Volume Pricing	8 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com