

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [Standard Plano-Convex \(PCX\) Lenses](#)

Large PCX Condenser Lenses



- Large Sizes Available – 100 to 250mm Diameter
- Polished Surfaces for Superior Precision vs. Cast Optics
- Wavelength Range of 350-2200nm

Common Specifications

Physical & Mechanical Properties


Bevel:	Protective as needed
--------	----------------------

Optical Properties

Substrate:	N-BK7
------------	-----------------------

Surface Quality:	120-80
------------------	--------

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
100.00	150.00	136.16	Uncoated	N-BK7	#67-187	S\$194.60 Volume Pricing	20+ In Stock
100.00	200.00	189.00	Uncoated	N-BK7	#27-501	S\$176.40 Volume Pricing	20+ In Stock
100.00	300.00	291.00	Uncoated	N-BK7	#27-502	S\$151.20 Volume Pricing	20+ In Stock
100.00	400.00	393.00	Uncoated	N-BK7	#27-503	S\$151.20 Volume Pricing	20+ In Stock
125.00	250.00	237.00	Uncoated	N-BK7	#27-505	S\$194.60 Volume Pricing	20+ In Stock
125.00	375.00	366.00	Uncoated	N-BK7	#27-506	S\$194.60 Volume Pricing	20+ In Stock
125.00	500.00	492.00	Uncoated	N-BK7	#27-507	S\$194.60 Volume Pricing	20+ In Stock
150.00	200.00	177.09	Uncoated	N-BK7	#67-191	S\$327.60 Volume Pricing	20+ In Stock
150.00	300.00	284.00	Uncoated	N-BK7	#27-509	S\$327.60 Volume Pricing	20+ In Stock
150.00	450.00	439.00	Uncoated	N-BK7	#27-510	S\$306.60 Volume Pricing	6 In Stock
150.00	600.00	591.00	Uncoated	N-BK7	#27-511	S\$306.60 Volume Pricing	20+ In Stock
200.00	400.00	380.00	Uncoated	N-BK7	#27-513	S\$599.20 Volume Pricing	20+ In Stock
200.00	600.00	586.00	Uncoated	N-BK7	#27-514	S\$543.20 Volume Pricing	Contact Us
200.00	800.00	788.00	Uncoated	N-BK7	#27-515	S\$543.20 Volume Pricing	20+ In Stock
250.00	400.00	370	Uncoated	N-BK7	#67-199	S\$812.00 Volume Pricing	20+ In Stock
250.00	500.00	476.6	Uncoated	N-BK7	#67-200	S\$812.00 Volume Pricing	15 In Stock
100.00	150.00	136.16	MgF ₂ (400-700nm)	N-BK7	#19-904	S\$350.00 Volume Pricing	1 In Stock

100.00	200.00	189.00	MgF ₂ (400-700nm)	N-BK7	#19-905	S\$327.60 Volume Pricing	4 In Stock
100.00	300.00	291.00	MgF ₂ (400-700nm)	N-BK7	#19-906	S\$303.80 Volume Pricing	8 In Stock
100.00	400.00	393.00	MgF ₂ (400-700nm)	N-BK7	#19-907	S\$303.80 Volume Pricing	2 In Stock
125.00	250.00	237.00	MgF ₂ (400-700nm)	N-BK7	#19-908	S\$390.60 Volume Pricing	6 In Stock
125.00	375.00	366.00	MgF ₂ (400-700nm)	N-BK7	#19-909	S\$390.60 Volume Pricing	5 In Stock
125.00	500.00	492.00	MgF ₂ (400-700nm)	N-BK7	#19-910	S\$390.60 Volume Pricing	2 In Stock
150.00	200.00	177.09	MgF ₂ (400-700nm)	N-BK7	#19-911	S\$551.60 Volume Pricing	Contact Us
150.00	300.00	284.00	MgF ₂ (400-700nm)	N-BK7	#19-912	S\$551.60 Volume Pricing	4 In Stock
150.00	450.00	439.00	MgF ₂ (400-700nm)	N-BK7	#19-913	S\$534.80 Volume Pricing	5 In Stock
150.00	600.00	591.00	MgF ₂ (400-700nm)	N-BK7	#19-914	S\$534.80 Volume Pricing	3 In Stock
200.00	400.00	380.00	MgF ₂ (400-700nm)	N-BK7	#19-915	S\$994.00 Volume Pricing	Contact Us
200.00	600.00	586.00	MgF ₂ (400-700nm)	N-BK7	#19-916	S\$931.00 Volume Pricing	1 In Stock
200.00	800.00	788.00	MgF ₂ (400-700nm)	N-BK7	#19-917	S\$931.00 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com