

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#)

Gradient Index (GRIN) Rod Lenses




- Ideal for Fiber Coupling and Laser Diode Applications
- Comparable Performance to Conventional Aspherical Singlets
- Multiple Sizes and Wavelength Options
- [GRIN Lens Grippers and Table Mounts](#) Available

Common Specifications

Physical & Mechanical Properties			
Clear Aperture (%):		90.00	Length Tolerance (%): ±5
Optical Properties			
Substrate:		Aluminosilicate Glass Embedded with Silver Ions	Surface Quality: 40-20
Working Distance Tolerance (mm):		±0.02	

Technical Information



Products

Dia. (mm)	Substrate	Type	Coating	EFL (mm)	NA	Stock Number	Price	Buy
0.35	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.30	0.55	#88-355	S\$128.10 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.54	#64-515	S\$90.30 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.88	0.54	#64-517	S\$90.30 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.67	0.52	#64-519	S\$90.30 Volume Pricing	20+ In Stock
#64-520 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.52		S\$90.30 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.53	#64-521	S\$90.30 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.89	0.54	#64-523	S\$90.30 Volume Pricing	20+ In Stock

1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-524	S\$90.30 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.68	0.52	#64-525	S\$90.30 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.70	0.51	#64-526	S\$90.30 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.46	0.52	#64-527	S\$90.30 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-529	S\$90.30 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.51	#64-531	S\$90.30 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.45	0.54	#64-533	S\$107.10 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.88	0.54	#64-535	S\$107.10 Volume Pricing	Contact Us
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.67	0.52	#64-537	S\$107.10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.69	0.52	#64-538	S\$107.10 Volume Pricing	Contact Us
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.45	0.53	#64-539	S\$107.10 Volume Pricing	8 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.89	0.54	#64-541	S\$107.10 Volume Pricing	20+ In Stock

1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.68	0.52	#64-543	S\$107.10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.70	0.51	#64-544	S\$107.10 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.46	0.52	#64-545	S\$107.10 Volume Pricing	Contact Us
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.90	0.53	#64-547	S\$107.10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.71	0.51	#64-549	S\$107.10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.72	0.51	#64-550	S\$107.10 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com