

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

TECHSPEC® M25.5 and M30.5 Mounted Neutral Density Filters



- VIS and NIR ND Filters, Mounted for Imaging Lenses
- Variety of Optical Densities
- Stack Filters Together for Custom Transmission Profiles

Common Specifications

Physical & Mechanical Properties

Clear Aperture CA (mm):	22.0
-------------------------	------

Technical Information

Products

Dia. (mm)	Filter Thread	Optical Density OD (Average)	Transmission (%)	Wavelength Range (nm)	Stock Number	Price	Buy
28.00	M25.5 x 0.50	0.1	79.00	400 - 700	#66-699	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.15	70.00	400 - 700	#66-700	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.2	63.00	400 - 700	#66-701	S\$124.60 Volume Pricing	3 In Stock
28.00	M25.5 x 0.50	0.3	50.00	400 - 700	#66-702	S\$124.60 Volume Pricing	3 In Stock
28.00	M25.5 x 0.50	0.4	40.00	400 - 700	#66-703	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.5	32.00	400 - 700	#66-704	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.6	25.00	400 - 700	#66-705	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.7	20.00	400 - 700	#66-706	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.9	12.50	400 - 700	#66-707	S\$124.60 Volume Pricing	3 In Stock
28.00	M25.5 x 0.50	1.0	10.00	400 - 700	#66-708	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	1.3	5.00	400 - 700	#66-709	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	1.5	3.20	400 - 700	#66-710	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	2.0	1.00	400 - 700	#66-711	S\$124.60 Volume Pricing	14 In Stock
28.00	M25.5 x 0.50	2.5	0.30	400 - 700	#66-712	S\$124.60 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	3.0	0.10	400 - 700	#66-713	S\$124.60 Volume Pricing	2 In Stock
33.50	M30.5 x 0.50	0.1	79.00	400 - 700	#66-714	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	0.15	70.00	400 - 700	#66-715	S\$124.60 Volume Pricing	3 In Stock
33.50	M30.5 x 0.50	0.2	63.00	400 - 700	#66-716	S\$124.60 Volume Pricing	Contact Us

33.50	M30.5 x 0.50	0.3	50.00	400 - 700	#66-717	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	0.4	40.00	400 - 700	#66-718	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	0.5	32.00	400 - 700	#66-719	S\$124.60 Volume Pricing	7 In Stock
33.50	M30.5 x 0.50	0.6	25.00	400 - 700	#66-720	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	0.7	20.00	400 - 700	#66-721	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	0.9	12.50	400 - 700	#66-722	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	1.0	10.00	400 - 700	#66-723	S\$124.60 Volume Pricing	3 In Stock
33.50	M30.5 x 0.50	1.3	5.00	400 - 700	#66-724	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	1.5	3.20	400 - 700	#66-725	S\$124.60 Volume Pricing	Contact Us
33.50	M30.5 x 0.50	2.0	1.00	400 - 700	#66-726	S\$124.60 Volume Pricing	4 In Stock
33.50	M30.5 x 0.50	2.5	0.30	400 - 700	#66-727	S\$124.60 Volume Pricing	1 In Stock
33.50	M30.5 x 0.50	3.0	0.10	400 - 700	#66-728	S\$124.60 Volume Pricing	14 In Stock
28.00	M25.5 x 0.50	0.3	50.00	700 - 1200	#66-729	S\$225.40 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.5	32.00	700 - 1200	#66-730	S\$225.40 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.6	25.00	700 - 1200	#66-731	S\$225.40 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	0.9	12.50	700 - 1200	#66-732	S\$225.40 Volume Pricing	Contact Us
28.00	M25.5 x 0.50	1.0	10.00	700 - 1200	#66-733	S\$225.40 Volume Pricing	Contact Us

[#66-734 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

28.00	M25.5 x 0.50	1.3	5.00	700 - 1200		S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	--	---	------------

28.00	M25.5 x 0.50	1.5	3.20	700 - 1200	#66-735	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------

28.00	M25.5 x 0.50	2.0	1.00	700 - 1200	#66-736	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------

28.00	M25.5 x 0.50	2.5	0.30	700 - 1200	#66-737	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------

28.00	M25.5 x 0.50	3.0	0.10	700 - 1200	#66-738	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	0.3	50.00	700 - 1200	#66-739	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	-------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	0.5	32.00	700 - 1200	#66-740	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	-------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	0.6	25.00	700 - 1200	#66-741	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	-------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	0.9	12.50	700 - 1200	#66-742	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	-------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	1.0	10.00	700 - 1200	#66-743	S\$225.40 Volume Pricing	1 In Stock
-------	--------------	-----	-------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	1.3	5.00	700 - 1200	#66-744	S\$225.40 Volume Pricing	1 In Stock
-------	--------------	-----	------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	1.5	3.20	700 - 1200	#66-745	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------

33.50	M30.5 x 0.50	2.0	1.00	700 - 1200	#66-746	S\$225.40 Volume Pricing	Contact Us
-------	--------------	-----	------	------------	-------------------------	---	------------



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com