

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

Infrared (IR) Bandpass Filters



- Ideal for Gas Analysis
- Center Wavelengths of 2.7-12.4 μ m
- Single Substrate Interference Filter
- **Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our customer service team.**

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	1.00 $\pm$ 0.2
-----------------	----------------


Optical Properties

Angle of Incidence (°):	0
-------------------------	---

Optical Density OD (Average):	≥ 3.0
-------------------------------	------------

Coating:	Traditional Coated
----------	--------------------

Technical Information



Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Stock Number	Price	Buy
25.00	2,700.00	110.00	#84-069	S\$819.00 Volume Pricing	1 In Stock
25.00	2,950.00	110.00	#84-070	S\$819.00 Volume Pricing	Contact Us
25.00	3,460.00	140.00	#84-071	S\$819.00 Volume Pricing	1 In Stock
25.00	3,600.00	140.00	#84-072	S\$819.00 Volume Pricing	2 In Stock
12.50	4,000.00	2,000.00	#26-569	S\$436.80 Volume Pricing	1 In Stock
25.00	4,000.00	2,000.00	#11-998	S\$819.00 Volume Pricing	5 In Stock
50.00	4,000.00	2,000.00	#26-570	S\$1,743.00 Volume Pricing	1 In Stock
25.00	4,260.00	120.00	#84-073	S\$819.00 Volume Pricing	2 In Stock
25.00	4,670.00	150.00	#84-074	S\$819.00 Volume Pricing	5 In Stock
25.00	5,300.00	420.00	#84-075	S\$819.00 Volume Pricing	2 In Stock
25.00	6,000.00	500.00	#17-244	S\$1,134.00 Volume Pricing	3 In Stock
25.00	6,500.00	500.00	#17-245	S\$1,134.00 Volume Pricing	14 In Stock
25.00	7,000.00	500.00	#17-246	S\$1,134.00 Volume Pricing	14 In Stock

[#75-125 New](#)



New

25.00 7,500.00 500.00

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

S\$1,134.00
[Volume Pricing](#)

3 In Stock

25.00 8,000.00 500.00

[#17-248](#)

S\$1,134.00
[Volume Pricing](#)

Contact Us

[#70-192 Clearance](#)



Clearance

25.00 8,500.00 500.00

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

S\$1,134.00
[Volume Pricing](#)

4 In Stock

25.00 9,000.00 500.00

[#17-250](#)

S\$1,134.00
[Volume Pricing](#)

20+ In Stock

25.00 9,500.00 500.00

[#17-251](#)

S\$1,134.00
[Volume Pricing](#)

20+ In Stock

25.00 10,000.00 500.00

[#17-252](#)

S\$1,134.00
[Volume Pricing](#)

20+ In Stock

[#11-999 Clearance](#)



Clearance

25.00 10,000.00 4,000.00

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

S\$1,813.00

Contact Us

12.50 10,600.00 1,500.00

[#33-144](#)

S\$1,008.00

Contact Us

[#33-145 Clearance](#)



Clearance

25.00 10,600.00 1,500.00

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

S\$1,813.00

2 In Stock

50.00 10,600.00 1,500.00

[#33-146](#)

S\$4,130.00

Contact Us

[#25-723 Clearance](#)



Clearance

25.00 12,100.00 500.00

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

S\$1,134.00
[Volume Pricing](#)

2 In Stock

25.00 12,400.00 500.00

[#17-253](#)

S\$1,547.00
[Volume Pricing](#)

13 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com