

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Optical Diffusers](#)

Broadband Hybrid Diffusers



- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Common Specifications

Physical & Mechanical Properties

Grit: 120

Optical Properties

Coating: Uncoated

Substrate: White Diffusing Glass

Wavelength Range (nm): 400 - 1100

Technical Information

Products

Dia. (mm)	Coating	Dimensions (mm)	Grit	Thickness (mm)	Stock Number	Price	Buy
5.00	Uncoated	-	120	1.75	#36-603	S\$56.35 Volume Pricing	Contact Us
-	Uncoated	5.00 x 5.00	120	1.75	#36-604	S\$56.35 Volume Pricing	20+ In Stock
10.00	Uncoated	-	120	1.75	#36-608	S\$56.35 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	120	1.75	#36-609	S\$56.35 Volume Pricing	20+ In Stock
12.50	Uncoated	-	120	1.75	#36-610	S\$56.35 Volume Pricing	20+ In Stock
-	Uncoated	12.50 x 12.50	120	1.75	#36-611	S\$56.35 Volume Pricing	6 In Stock
15.00	Uncoated	-	120	1.75	#37-974	S\$69.30 Volume Pricing	20+ In Stock
-	Uncoated	15.00 x 15.00	120	1.75	#70-251	S\$69.30 Volume Pricing	20+ In Stock
20.00	Uncoated	-	120	1.75	#70-252	S\$69.30 Volume Pricing	20+ In Stock
-	Uncoated	20.00 x 20.00	120	1.75	#70-253	S\$69.30 Volume Pricing	20+ In Stock
25.00	Uncoated	-	120	1.75	#36-612	S\$70.00 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	120	1.75	#36-613	S\$70.00 Volume Pricing	20+ In Stock
30.00	Uncoated	-	120	1.75	#70-254	S\$69.30 Volume Pricing	20+ In Stock
-	Uncoated	30.00 x 30.00	120	1.75	#70-255	S\$69.30 Volume Pricing	20+ In Stock
35.00	Uncoated	-	120	1.75	#70-256	S\$72.10 Volume Pricing	20+ In Stock
-	Uncoated	35.00 x 35.00	120	1.75	#70-257	S\$72.10 Volume Pricing	20+ In Stock
40.00	Uncoated	-	120	1.75	#70-258	S\$75.60 Volume Pricing	20+ In Stock

-	Uncoated	40.00 x 40.00	120	1.75	#70-260	S\$75.60 Volume Pricing	20+ In Stock
50.00	Uncoated	-	120	1.75	#36-614	S\$79.80 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	120	1.75	#36-615	S\$79.80 Volume Pricing	20+ In Stock
75.00	Uncoated	-	120	1.75	#36-678	S\$93.10 Volume Pricing	12 In Stock
-	Uncoated	75.00 x 75.00	120	1.75	#36-616	S\$93.10 Volume Pricing	20+ In Stock
100.00	Uncoated	-	120	1.75	#36-617	S\$125.30 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	120	1.75	#36-618	S\$125.30 Volume Pricing	20+ In Stock
-	Uncoated	200.00 x 200.00	120	1.75	#36-619	S\$168.00 Volume Pricing	17 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com