

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Optical Diffusers](#)

White Diffusing Glass



- Semi-Opaque White Glass
- Highly Diffusive to Create Even Illumination
- Diffusive on Both Surfaces

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	1.25 ±0.1
-----------------	-----------


Optical Properties

Coating:	Uncoated
----------	----------

Substrate:	White Diffusing Glass
------------	-----------------------

Wavelength Range (nm):	400 - 700
------------------------	-----------

Technical Information



Products

Dia. (mm)	Coating	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
5.00	Uncoated	-	1.25	#34-467	S\$41.45 Volume Pricing	20+ In Stock
-	Uncoated	5.00 x 5.00	1.25	#34-468	S\$41.45 Volume Pricing	20+ In Stock
10.00	Uncoated	-	1.25	#34-469	S\$41.45 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	1.25	#34-470	S\$41.45 Volume Pricing	20+ In Stock
12.50	Uncoated	-	1.25	#34-471	S\$41.45 Volume Pricing	20+ In Stock
-	Uncoated	12.50 x 12.50	1.25	#34-472	S\$41.45 Volume Pricing	20+ In Stock
15.00	Uncoated	-	1.25	#37-975	S\$49.29 Volume Pricing	20+ In Stock
-	Uncoated	15.00 x 15.00	1.25	#70-242	S\$49.29 Volume Pricing	20+ In Stock
20.00	Uncoated	-	1.25	#70-243	S\$49.29 Volume Pricing	Contact Us
-	Uncoated	20.00 x 20.00	1.25	#70-244	S\$49.29 Volume Pricing	20+ In Stock
25.00	Uncoated	-	1.25	#34-473	S\$49.29 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	1.25	#34-474	S\$49.29 Volume Pricing	20+ In Stock
25.40	Uncoated	-	1.25	#29-422	S\$52.64 Volume Pricing	Contact Us
30.00	Uncoated	-	1.25	#70-245	S\$49.29 Volume Pricing	17 In Stock
-	Uncoated	30.00 x 30.00	1.25	#70-246	S\$49.29 Volume Pricing	20+ In Stock
35.00	Uncoated	-	1.25	#70-247	S\$52.64 Volume Pricing	20+ In Stock
-	Uncoated	35.00 x 35.00	1.25	#70-248	S\$52.64 Volume Pricing	20+ In Stock

40.00	Uncoated	-	1.25	#70-249	S\$55.63 Volume Pricing	20+ In Stock
-	Uncoated	40.00 x 40.00	1.25	#70-250	S\$55.63 Volume Pricing	20+ In Stock
50.00	Uncoated	-	1.25	#34-475	S\$61.98 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	1.25	#34-476	S\$61.98 Volume Pricing	20+ In Stock
75.00	Uncoated	-	1.25	#34-477	S\$70.57 Volume Pricing	20+ In Stock
-	Uncoated	75.00 x 75.00	1.25	#34-478	S\$70.57 Volume Pricing	20+ In Stock
100.00	Uncoated	-	1.25	#34-479	S\$90.35 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	1.25	#34-480	S\$90.35 Volume Pricing	13 In Stock
-	Uncoated	200.00 x 200.00	1.25	#34-481	S\$126.95 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com