

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Off-Axis Mirrors](#)

TECHSPEC® Aluminum Off-Axis Parabolic Mirrors




- Aluminum Coatings for UV, Visible, and NIR Applications
- Range of Surface Roughness, Including 50Å and 100Å
- 15°, 30°, 45°, 60°, or 90° Offset Angle Options
- Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available

Common Specifications

Optical Properties

Focal Length Tolerance (%) : ± 1	Coating Type: Metal
Surface Quality: 80-50	Substrate: Aluminum 6061-T6

Technical Information



Products

Dia. (mm)	EFL (mm)	Coating	Off- Set Angle (°)	Surface Roughness (Å)	Stock Number	Price	Buy
6.35	6.35	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-282	S\$268.83 Volume Pricing	20+ In Stock
6.35	6.35	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-288	S\$295.71 Volume Pricing	12 In Stock
6.35	12.70	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-283	S\$268.83 Volume Pricing	6 In Stock
6.35	12.70	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-289	S\$295.71 Volume Pricing	9 In Stock
6.35	25.40	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-284	S\$268.83 Volume Pricing	1 In Stock
6.35	25.40	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-290	S\$295.71 Volume Pricing	4 In Stock
6.35	50.80	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-285	S\$268.83 Volume Pricing	13 In Stock
6.35	50.80	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-291	S\$295.71 Volume Pricing	1 In Stock

[#37-292 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

6.35	76.20	Enhanced Aluminum (250-700nm)	90	<50 RMS		S\$200.06	3 In Stock
6.35	101.60	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-287	S\$268.83 Volume Pricing	9 In Stock
6.35	101.60	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-293	S\$295.71 Volume Pricing	2 In Stock
12.70	12.70	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-258	S\$286.75 Volume Pricing	Contact Us
12.70	12.70	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-264	S\$310.65 Volume Pricing	1 In Stock
12.70	12.70	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-481	S\$279.28 Volume Pricing	10 In Stock
12.70	25.40	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-259	S\$286.75 Volume Pricing	1 In Stock
12.70	25.40	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-265	S\$310.65 Volume Pricing	7 In Stock

12.70	25.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-482	S\$279.28 Volume Pricing	11 In Stock
12.70	50.80	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-260	S\$286.75 Volume Pricing	Contact Us
12.70	50.80	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-266	S\$310.65 Volume Pricing	3 In Stock
12.70	50.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-483	S\$279.28 Volume Pricing	6 In Stock
12.70	76.20	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-261	S\$286.75 Volume Pricing	2 In Stock
12.70	76.20	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-267	S\$310.65 Volume Pricing	4 In Stock
12.70	101.60	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-262	S\$286.75 Volume Pricing	4 In Stock
12.70	101.60	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-268	S\$310.65 Volume Pricing	Contact Us
12.70	203.20	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-263	S\$286.75 Volume Pricing	4 In Stock
12.70	203.20	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-269	S\$310.65 Volume Pricing	1 In Stock
25.40	25.40	Protected Aluminum (400-2000nm)	90	<50 RMS	#87-406	S\$356.95 Volume Pricing	7 In Stock
25.40	25.40	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-232	S\$373.38 Volume Pricing	20+ In Stock

25.40	25.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-500	S\$286.75 Volume Pricing	17 In Stock
25.40	27.22	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-514	S\$473.44 Volume Pricing	20+ In Stock
25.40	33.85	Protected Aluminum (400-2000nm)	60	<100 RMS	#35-496	S\$342.01 Volume Pricing	3 In Stock
25.40	50.80	Protected Aluminum (400-2000nm)	90	<50 RMS	#87-407	S\$356.95 Volume Pricing	2 In Stock
25.40	50.80	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-233	S\$373.38 Volume Pricing	20+ In Stock
25.40	50.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-502	S\$286.75 Volume Pricing	Contact Us
25.40	50.80	Protected Aluminum (400-2000nm)	60	<100 RMS	#35-498	S\$286.75 Volume Pricing	5 In Stock
25.40	54.45	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-490	S\$373.38 Volume Pricing	20+ In Stock
25.40	76.20	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-226	S\$356.95 Volume Pricing	5 In Stock
25.40	76.20	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-234	S\$373.38 Volume Pricing	5 In Stock
25.40	76.20	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-517	S\$286.75 Volume Pricing	5 In Stock
25.40	101.60	Protected Aluminum (400-2000nm)	90	<50 RMS	#87-408	S\$356.95 Volume Pricing	5 In Stock

25.40	101.60	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-235	S\$373.38 Volume Pricing	14 In Stock
25.40	101.60	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-504	S\$286.75 Volume Pricing	20+ In Stock
#37-227 Clearance							
Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	127.00	Protected Aluminum (400-2000nm)	90	<50 RMS		S\$310.58	2 In Stock
25.40	127.00	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-563	S\$473.44 Volume Pricing	2 In Stock
25.40	152.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-518	S\$286.75 Volume Pricing	3 In Stock
25.40	177.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#34-520	S\$628.76 Volume Pricing	1 In Stock
25.40	203.20	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-230	S\$356.95 Volume Pricing	3 In Stock
25.40	203.20	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-239	S\$373.38 Volume Pricing	9 In Stock

25.40	203.20	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-590	S\$286.75 Volume Pricing	9 In Stock
25.40	272.24	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-606	S\$881.17 Volume Pricing	3 In Stock
25.40	387.60	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-538	S\$380.84 Volume Pricing	11 In Stock
25.40	646.00	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-540	S\$380.84 Volume Pricing	3 In Stock
50.80	50.80	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-306	S\$698.96 Volume Pricing	5 In Stock
50.80	50.80	Protected Aluminum (400-2000nm)	90	<50 RMS	#87-409	S\$652.66 Volume Pricing	4 In Stock
50.80	50.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-506	S\$628.76 Volume Pricing	14 In Stock
50.80	54.45	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-492	S\$675.06 Volume Pricing	7 In Stock
50.80	59.51	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-550	S\$660.13 Volume Pricing	3 In Stock
50.80	76.20	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-984	S\$652.66 Volume Pricing	3 In Stock
50.80	76.20	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-993	S\$698.96 Volume Pricing	5 In Stock
50.80	76.20	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-508	S\$628.76 Volume Pricing	6 In Stock

50.80	81.79	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-607	S\$675.06 Volume Pricing	20+ In Stock
50.80	89.28	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-552	S\$660.13 Volume Pricing	3 In Stock
50.80	101.60	Protected Aluminum (400-2000nm)	90	<50 RMS	#87-410	S\$652.66 Volume Pricing	Contact Us
50.80	101.60	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-307	S\$698.96 Volume Pricing	10 In Stock
50.80	101.60	Protected Aluminum (400-2000nm)	60	<100 RMS	#35-516	S\$706.43 Volume Pricing	2 In Stock
50.80	101.60	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-510	S\$628.76 Volume Pricing	2 In Stock
50.80	108.89	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-494	S\$675.06 Volume Pricing	16 In Stock
50.80	136.12	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-609	S\$745.26 Volume Pricing	Contact Us
50.80	152.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-512	S\$628.76 Volume Pricing	5 In Stock
50.80	177.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-519	S\$628.76 Volume Pricing	6 In Stock
50.80	190.50	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-520	S\$628.76 Volume Pricing	3 In Stock
50.80	190.60	Protected Aluminum (400-2000nm)	90	<50 RMS	#37-988	S\$652.66 Volume Pricing	5 In Stock

50.80	190.60	Enhanced Aluminum (250-700nm)	90	<50 RMS	#37-996	S\$698.96 Volume Pricing	1 In Stock
50.80	272.24	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-610	S\$675.06 Volume Pricing	7 In Stock
50.80	310.08	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-542	S\$536.17 Volume Pricing	13 In Stock
50.80	387.60	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-594	S\$536.17 Volume Pricing	4 In Stock
50.80	516.81	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-544	S\$536.17 Volume Pricing	9 In Stock
76.20	50.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-521	S\$1,351.62 Volume Pricing	5 In Stock
76.20	76.20	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-522	S\$1,097.72 Volume Pricing	3 In Stock
76.20	89.28	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-586	S\$1,269.48 Volume Pricing	4 In Stock
76.20	101.60	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-565	S\$1,097.72 Volume Pricing	1 In Stock
76.20	127.00	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-523	S\$1,052.92 Volume Pricing	2 In Stock
76.20	152.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-524	S\$1,052.92 Volume Pricing	4 In Stock
76.20	177.80	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-564	S\$1,052.92 Volume Pricing	2 In Stock

76.20	178.53	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-588	S\$1,097.72 Volume Pricing	2 In Stock
76.20	272.23	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-580	S\$1,142.53 Volume Pricing	2 In Stock
76.20	646.00	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-597	S\$1,142.53 Volume Pricing	5 In Stock
101.60	101.60	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-566	S\$1,433.76 Volume Pricing	1 In Stock
101.60	119.03	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-628	S\$1,351.62 Volume Pricing	3 In Stock
101.60	152.40	Protected Aluminum (400-2000nm)	90	<100 RMS	#35-592	S\$1,433.76 Volume Pricing	5 In Stock
101.60	178.55	Protected Aluminum (400-2000nm)	45	<100 RMS	#35-629	S\$1,351.62 Volume Pricing	6 In Stock
101.60	326.69	Protected Aluminum (400-2000nm)	30	<100 RMS	#35-584	S\$1,433.76 Volume Pricing	3 In Stock
101.60	387.60	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-574	S\$1,351.62 Volume Pricing	7 In Stock
101.60	516.81	Protected Aluminum (400-2000nm)	15	<100 RMS	#35-576	S\$1,351.62 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com