

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Pinholes and Slits](#)

Acktar Blackened Pinholes

See More by [Acktar](#)



- Low Reflectance from the EUV to SWIR
- 99% Absorbance Blackening Coating
- Aperture Sizes from 20 to 1000 μm
- Available Unmounted and Mounted

Common Specifications

Physical & Mechanical Properties

Construction: Stainless Steel

Material Properties

Absorbance (%): 99

Technical Information

Products

Type	Outer Diameter (mm)	Construction	Fixed Aperture Diameter (µm)	Stock Number	Price	Buy
Unmounted	9.53	Stainless Steel	20	#15-386	S\$253.40 Volume Pricing	3 In Stock
Unmounted	9.53	Stainless Steel	25	#15-387	S\$253.40 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	50	#12-166	S\$253.40 Volume Pricing	1 In Stock
Unmounted	9.53	Stainless Steel	75	#15-388	S\$253.40 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	100	#12-167	S\$253.40 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	150	#15-389	S\$253.40 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	200	#12-168	S\$253.40 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	300	#15-390	S\$253.40 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	400	#15-391	S\$253.40 Volume Pricing	Contact Us
Unmounted	9.53	Stainless Steel	500	#12-169	S\$253.40 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	600	#15-392	S\$253.40 Volume Pricing	8 In Stock
Unmounted	9.53	Stainless Steel	800	#16-738	S\$253.40 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	1000	#12-170	S\$253.40 Volume Pricing	4 In Stock
Mounted	12.7	Stainless Steel	25	#16-821	S\$270.20 Volume Pricing	3 In Stock
Mounted	12.7	Stainless Steel	50	#16-822	S\$270.20 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	75	#16-823	S\$270.20 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	100	#16-824	S\$270.20 Volume Pricing	2 In Stock

Mounted	12.7	Stainless Steel	150	#16-825	S\$270.20 Volume Pricing	1 In Stock
Mounted	12.7	Stainless Steel	200	#16-826	S\$270.20 Volume Pricing	2 In Stock
Mounted	12.7	Stainless Steel	300	#16-827	S\$270.20 Volume Pricing	4 In Stock
Mounted	12.7	Stainless Steel	500	#16-828	S\$270.20 Volume Pricing	5 In Stock
Mounted	12.7	Stainless Steel	1000	#16-829	S\$270.20 Volume Pricing	Contact Us
Mounted	25.0	Stainless Steel	20	#15-393	S\$270.20 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	25	#15-394	S\$270.20 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	50	#12-171	S\$270.20 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	75	#15-395	S\$270.20 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	100	#12-172	S\$270.20 Volume Pricing	6 In Stock
Mounted	25.0	Stainless Steel	150	#15-396	S\$270.20 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	200	#12-173	S\$270.20 Volume Pricing	1 In Stock
Mounted	25.0	Stainless Steel	300	#15-397	S\$270.20 Volume Pricing	Contact Us
Mounted	25.0	Stainless Steel	400	#15-398	S\$270.20 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	500	#12-174	S\$270.20 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	600	#15-399	S\$270.20 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	800	#16-739	S\$270.20 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	1000	#12-175	S\$270.20 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com