

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Ultrafast Laser Mirrors](#)

TECHSPEC® High Performance Low GDD Ultrafast Mirrors



- Designed with High Reflectivity for Ultrafast Beam Steering
- Ion-Beam Sputtered Coating for Low Scatter and Absorption
- GDD as Low as $0 \pm 20 \text{fs}^2$ at Design Wavelength Range

Common Specifications

Physical & Mechanical Properties

Back Surface: Commercial Polish

Optical Properties

Substrate: [Fused Silica](#) (Corning 7980)

Technical Information

Products

Wavelength Range (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
241 - 271	12.70	6.35	45	#11-734	S\$294.00 Volume Pricing	6 In Stock
241 - 271	25.40	6.35	45	#11-735	S\$355.60 Volume Pricing	20+ In Stock
320 - 370	12.70	6.35	45	#12-463	S\$294.00 Volume Pricing	5 In Stock
320 - 370	25.40	6.35	45	#12-464	S\$355.60 Volume Pricing	Contact Us
320 - 370	50.80	9.52	45	#12-465	S\$798.00 Volume Pricing	7 In Stock
500 - 530	12.70	6.35	45	#17-551	S\$285.60 Volume Pricing	3 In Stock
500 - 530	25.40	6.35	45	#12-834	S\$333.20 Volume Pricing	Contact Us
700 - 900	12.70	6.35	45	#62-765	S\$317.80 Volume Pricing	20+ In Stock
700 - 900	25.40	6.35	45	#62-766	S\$436.80 Volume Pricing	10 In Stock
780 - 820	25.40	9.52	0	#36-407	S\$455.00 Volume Pricing	2 In Stock
780 - 820	25.40	9.52	45	#36-409	S\$455.00 Volume Pricing	Contact Us
1000 - 1060	12.70	6.35	45	#14-845	S\$315.00 Volume Pricing	20+ In Stock
1000 - 1060	25.40	6.35	45	#14-846	S\$399.00 Volume Pricing	6 In Stock
1000 - 1060	50.80	9.52	45	#14-847	S\$812.00 Volume Pricing	Contact Us
500 - 540, 1000 - 1070	12.70	6.35	45	#17-286	S\$249.20 Volume Pricing	20+ In Stock
500 - 540, 1000 - 1070	25.40	6.35	45	#17-287	S\$511.00 Volume Pricing	20+ In Stock
500 - 540, 1000 - 1070	50.80	9.53	45	#17-288	S\$1,008.00 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com