

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC® Uncoated Laser Window Substrates



- Up to 10-5 Surface Quality and $\lambda/10$ Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

Common Specifications

Physical & Mechanical Properties

Edges: Fine Ground

Optical Properties

Coating: Uncoated

Technical Information

Products

Coating	Substrate	Fused Silica Grade	Dia. (mm)	Thickness (mm)	Stock Number	Price	Buy
Uncoated	Fused Silica	7980 KrF 0A	12.50	3.00	#48-022	S\$190.40 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980	12.70	1.00	#11-749	S\$148.40 Volume Pricing	4 In Stock
Uncoated	Fused Silica	7979 0G	12.70	1.00	#11-752	S\$161.00 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	12.70	3.18	#37-693	S\$190.40 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	12.70	6.35	#38-055	S\$176.40 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	12.70	6.35	#37-688	S\$190.40 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	19.10	6.35	#38-056	S\$190.40 Volume Pricing	16 In Stock
Uncoated	Fused Silica	7980 0F	19.10	6.35	#38-911	S\$205.80 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 KrF 0A	25.00	3.00	#48-023	S\$236.60 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0G	25.40	1.00	#11-750	S\$176.40 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	25.40	1.00	#11-753	S\$189.00 Volume Pricing	10 In Stock
Uncoated	Fused Silica	7980 0F	25.40	3.18	#37-694	S\$229.60 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	25.40	6.35	#38-057	S\$221.20 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	25.40	6.35	#37-689	S\$229.60 Volume Pricing	16 In Stock
Uncoated	N-BK7	-	38.10	6.35	#11-450	S\$289.80 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	38.10	6.35	#38-912	S\$313.60 Volume Pricing	20+ In Stock

Uncoated	N-BK7	-	38.10	9.53	#38-058	S\$289.80 Volume Pricing	20+ In Stock
Uncoated	Fused Quartz	-	50.00	2.00	#37-666	S\$96.60 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	50.80	1.00	#11-751	S\$306.60 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	50.80	1.00	#11-754	S\$338.80 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	50.80	6.35	#37-690	S\$382.20 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	50.80	9.53	#38-059	S\$366.80 Volume Pricing	14 In Stock
Uncoated	Fused Silica	7980 0F	50.80	9.53	#38-060	S\$382.20 Volume Pricing	Contact Us
Uncoated	Fused Quartz	-	55.00	1.50	#37-667	S\$104.30 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0A	76.20	12.70	#14-844	S\$763.00 Volume Pricing	Contact Us
Uncoated	Fused Silica	7980 0G	134.00	3.00	#37-668	S\$313.60 Volume Pricing	3 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com