

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® HR Series Fixed Focal Length Lenses



- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 1.85µm Pixel Size Sensors
- High Resolution (HR), FA Lens for Machine Vision
- 8.5mm to 35mm Focal Length

Common Specifications

General

Imaging Lens Type:	High Performance Lens
--------------------	-----------------------

Physical & Mechanical Properties

Iris Option:	Variable
--------------	----------

Optical Properties

Maximum Image Circle (mm):	11.00
----------------------------	-------

Coating:	425 - 675nm BBAR
----------	------------------

Coating Specification:	425 - 675nm BBAR
------------------------	------------------

Sensor

Maximum Sensor Format:	2/3"
------------------------	------


Threading & Mounting

Mount:	C-Mount
--------	---------

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60
---------------------------	----------------------------

Technical Information



Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Optimized Working Distance (mm)	Mount	Stock Number	Price	Buy
	Edmund optics worldwide				C-Mount	#68-215	S\$887.00	12 In Stock
	12.00	2/3"	f/1.8 - f/16	100 - 1000 - ∞	C-Mount	#63-779	S\$887.00	20+ In Stock
	12.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#63-777	S\$887.00	20+ In Stock
	12.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#63-778	S\$887.00	9 In Stock
	16.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#85-865	S\$887.00	20+ In Stock
	16.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#85-866	S\$887.00	20+ In Stock
	25.00	2/3"	f/1.8 - f/22	200 - ∞	C-Mount	#63-780	S\$887.00	20+ In Stock
	#71-000 New							
								
	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
25.00	2/3"	f/2 - f/22	200 - ∞	350 - ∞	C-Mount		S\$887.00	8 In Stock
25.00	2/3"	f/1.8 - f/22	200 - ∞	400 - 2000	C-Mount	#63-781	S\$887.00	20+ In Stock
25.00	2/3"	f/1.8 - f/22	200 - ∞	1500 - ∞	C-Mount	#63-782	S\$887.00	7 In Stock
35.00	2/3"	f/1.8 - f/16	100 - ∞	125 - 600	C-Mount	#85-868	S\$887.00	9 In Stock
35.00	2/3"	f/1.8 - f/16	100 - ∞	400 - 2000	C-Mount	#85-869	S\$887.00	20+ In Stock