

[All Products](#) / [Optomechanics](#) / [Benchtop Optical Mounts](#) / [Optical Mirror Mounts](#)**TECHSPEC® Compact Mirror & Lens Mounts**

- Ideal for Mounting 0.5"-4" Dia. Optics at Uniform Optical Centerline Heights from 25.4mm to 63.5mm
- Compact Design Ideal for Space-Restricted Systems
- Options Include [C-, S-, and T-Mount Circular Optic Mount](#) and [ID \(SM\) Thread](#) Compatibility

**Common Specifications****General****Type of Optics:** Circular**Physical & Mechanical Properties****Construction:** Black Anodized Aluminum

## Technical Information

## Products

| Size of Compatible Optics (mm) | Barrel Thread             | Compatible Post | Optic Holding Style        | Stock Number            | Price                                      | Buy          |
|--------------------------------|---------------------------|-----------------|----------------------------|-------------------------|--|--------------|
| 12.7                           | -                         | M4 x 0.7        | Held by One Set Screw      | <a href="#">#13-598</a> | S\$25.90<br><a href="#">Volume Pricing</a> | 13 In Stock  |
| 12.7                           | -                         | 8/32            | Held by One Set Screw      | <a href="#">#13-599</a> | S\$25.90<br><a href="#">Volume Pricing</a> | 17 In Stock  |
| 25.4                           | -                         | M4 x 0.7        | Held by One Set Screw      | <a href="#">#13-590</a> | S\$28.00<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 25.4                           | -                         | 8/32            | Held by One Set Screw      | <a href="#">#13-591</a> | S\$29.40<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 50.8                           | -                         | M4 x 0.7        | Held by One Set Screw      | <a href="#">#17-712</a> | S\$42.70<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 50.8                           | -                         | 8/32            | Held by One Set Screw      | <a href="#">#17-713</a> | S\$42.70<br><a href="#">Volume Pricing</a> | 1 In Stock   |
| 76.2                           | -                         | M4 x 0.7        | Held by One Set Screw      | <a href="#">#18-701</a> | S\$84.00<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 76.2                           | -                         | 8/32            | Held by One Set Screw      | <a href="#">#18-702</a> | S\$84.00<br><a href="#">Volume Pricing</a> | 1 In Stock   |
| 12.5 - 12.7                    | SM05<br>(0.535" x 40 TPI) | M4 x 0.7        | One Retainer Ring Included | <a href="#">#13-789</a> | S\$27.30<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 12.5 - 12.7                    | SM05<br>(0.535" x 40 TPI) | 8/32            | One Retainer Ring Included | <a href="#">#13-790</a> | S\$27.30<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 25.0 - 25.4                    | SM1<br>(1.035" x 40 TPI)  | M4 x 0.7        | One Retainer Ring Included | <a href="#">#13-787</a> | S\$29.40<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 25.0 - 25.4                    | SM1<br>(1.035" x 40 TPI)  | 8/32            | One Retainer Ring Included | <a href="#">#13-788</a> | S\$29.40<br><a href="#">Volume Pricing</a> | 20+ In Stock |

|             |                             |                      |   |                         |   |              |
|-------------|-----------------------------|----------------------|---|-------------------------|---|--------------|
| 50.0 - 50.8 | SM2<br>(2.035" x<br>40 TPI) | M4 x 0.7,<br>8/32    | One<br>Retainer<br>Ring<br>Included                                   | <a href="#">#17-716</a> | S\$50.75<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 76.2        | SM3<br>(3.035" x<br>40 TPI) | M4 x 0.7,<br>8/32    | One<br>Retainer<br>Ring<br>Included                                   | <a href="#">#18-703</a> | S\$111.30<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 101.60      | SM4<br>(4.035" x<br>40 TPI) | M6 x 1.0, 1/4-<br>20 | One<br>Retainer<br>Ring<br>Included                                   | <a href="#">#18-704</a> | S\$142.80<br><a href="#">Volume Pricing</a> | 6 In Stock   |
| 16.0        | -                           | M4 x 0.7             | Requires S-<br>Mount<br>Circular<br>Optic<br>Mounts<br>(16mm<br>O.D.) | <a href="#">#13-791</a> | S\$32.20<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 16.0        | -                           | 8/32                 | Requires S-<br>Mount<br>Circular<br>Optic<br>Mounts<br>(16mm<br>O.D.) | <a href="#">#13-792</a> | S\$32.20<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 30.0        | -                           | M4 x 0.7             | Requires C-<br>Mount<br>Circular<br>Optic<br>Mounts<br>(30mm<br>O.D.) | <a href="#">#13-793</a> | S\$38.15<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 30.0        | -                           | 8/32                 | Requires C-<br>Mount<br>Circular<br>Optic<br>Mounts<br>(30mm<br>O.D.) | <a href="#">#13-794</a> | S\$38.15<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 48          | -                           | 8/32                 | Requires T-<br>Mount<br>Circular<br>Optic<br>Mounts<br>(48mm<br>O.D.) | <a href="#">#17-715</a> | S\$42.70<br><a href="#">Volume Pricing</a>  | 2 In Stock   |



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)