

[All Products](#) / [Cameras](#) / [USB Cameras](#)

IDS Imaging uEye LE USB 3.1 AF Autofocus Liquid Lens Board Level Cameras

See More by [IDS Imaging Development Systems](#)



- Compact M12 (S-Mount) and C/CS-Mount Board Level Cameras
- Integrated Liquid Lens Control
- Software Based Autofocus Functionality

Common Specifications

General							
Manufacturer:		IDS Imaging Development Systems		Camera Series:		uEye+ LE-AF	
Physical & Mechanical Properties							
Housing:		Board Level					
Sensor							
Image Buffer:		Not Specified					
Type of Sensor:		Progressive Scan CMOS		Pixel Depth:		12 bit	
Machine Vision Standard:		USB3 Vision					
Hardware & Interface Connectivity							
Interface:		USB 3.0					
Connector:		USB Type-C		Power Supply:		Power over USB	
GPIOs:		2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground		Synchronization:		Hardware Trigger (GPIO); Software Trigger	
Interface Port Orientation:		Back Panel (Right Angle)		GPIO Connector Type:		10-pin Wuerth connector (WR-WTB 1.00 mm)	
Threading & Mounting							
Mounting Threads:				No Mounting Threads/Tripod Adapter			
Environmental & Durability Factors							
Operating Temperature (°C):				0 to +55			
Storage Temperature (°C):				-20 to +80			

Technical Information

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Color Camera	U3-3041LE-C-HQ-AF	1/2.9"	1.50	USB Type-C	S-Mount (M12 x 0.5)	#24-086	S\$639.45	3 In Stock
Monochrome Camera	U3-3041LE-M-GL-AF	1/2.9"	1.50	USB Type-C	S-Mount (M12 x 0.5)	#24-088	S\$639.45	1 In Stock
Color Camera	U3-3044LE-C-HQ-AF	1/2.9"	1.50	USB Type-C	C/CS-Mount	#24-089	S\$639.45	1 In Stock
Monochrome Camera	U3-3044LE-M-GL-AF	1/2.9"	1.50	USB Type-C	C/CS-Mount	#24-090	S\$639.45	1 In Stock
Color Camera	U3-3271LE-C-HQ-AF	1/1.8"	3.10	USB Type-C	S-Mount (M12 x 0.5)	#24-092	S\$804.75	Contact Us
Monochrome Camera	U3-3271LE-M-GL-AF	1/1.8"	3.10	USB Type-C	S-Mount (M12 x 0.5)	#24-094	S\$804.75	1 In Stock
Color Camera	U3-3274LE-C-HQ-AF	1/1.8"	3.10	USB Type-C	C/CS-Mount	#24-123	S\$804.75	1 In Stock
Monochrome Camera	U3-3274LE-M-GL-AF	1/1.8"	3.10	USB Type-C	C/CS-Mount	#24-125	S\$804.75	2 In Stock
Color Camera	U3-3861LE-C-HQ-AF	1/2.8"	2.10	USB Type-C	S-Mount (M12 x 0.5)	#24-096	S\$645.25	2 In Stock
Monochrome Camera	U3-3861LE-M-GL-AF	1/2.8"	2.10	USB Type-C	S-Mount (M12 x 0.5)	#24-098	S\$658.30	1 In Stock
Color Camera	U3-3864LE-C-HQ-AF	1/2.8"	2.10	USB Type-C	C/CS-Mount	#24-127	S\$620.60	1 In Stock
Monochrome Camera	U3-3864LE-M-GL-AF	1/2.8"	2.10	USB Type-C	C/CS-Mount	#24-129	S\$658.30	1 In Stock

Color Camera	U3-3881LE-C-HQ-AF	1/1.8"	6.40	USB Type-C	S-Mount (M12 x 0.5)	#24-100	S\$639.45	Contact Us
Monochrome Camera	U3-3881LE-M-GL-AF	1/1.8"	6.40	USB Type-C	S-Mount (M12 x 0.5)	#24-102	S\$639.45	1 In Stock
Color Camera	U3-3884LE-C-HQ-AF	1/1.8"	6.40	USB Type-C	C/CS-Mount	#24-116	S\$639.45	Contact Us
Monochrome Camera	U3-3884LE-M-GL-AF	1/1.8"	6.40	USB Type-C	C/CS-Mount	#24-117	S\$639.45	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com